

The cost-effective Planar® PLL2251MW 22" Full HD LCD desktop monitor features wide viewing angles, VGA and HDMI video inputs, integrated TrueMedia™ speakers, and an ergonomically designed, height-adjustable stand.



SPECIFICATION	DETAIL
Product Name	PLL2251MW
Planar Part Number	998-0412-00
Viewable Size	21.5" diagonal (18.74" horizontal x 10.54" vertical)
Aspect Ratio	16:9
Contrast Ratio (typ)	3000:1
Viewing Angle (typ)	178° Horizontal and 178° Vertical (Specified at CR>10:1)
Response Time (typ)	12.5ms (GTG)
Brightness (Typical)	250 cd/m ²
Display Type	Edge-Lit LED LCD
Display Resolution	1920 x 1080, full HD
Tilt Range	-5° to 22°
Palette	16.7 million colors
Pixel Pitch	0.248
Refresh Rate	55-76Hz (60Hz recommended)
Dimensions (W x H x D)	19.9" x 15.0" x 8.9" (504 mm x 382.15 mm x 224.8 mm)
Dimensions without Stand	19.9" x 14.5" x 1.9" (504 mm x 367 mm x 49 mm)
Panel Depth	1.9" (49 mm)
Display Weight	10 lb (4.5 kg), 5.1 lb (2.3 kg) without base & stand
Shipping weight	12.8 lb (5.8 kg)
Video Inputs	HDMI, VGA
HDCP	Yes

External Connections	HDMI 19-pin, VGA 15-pin, 3.5 mm audio in
Audio Output	Integrated TrueMedia™ speakers, 1W/channel
Compatibility	PC and Mac® (adapter may be required for Mac)
Power Supply	Internal
Power Consumption (max)	16W Typical, (0.5W standby)
Power Requirements	AC 100/240 VAC
VESA Compatible/Location	Built-in 75 mm VESA, back
Product Approvals	FCC-B, UL/cUL, CE, WEEE, Rohs
Recommended Usage	Up to 16 hours per day
Service and Support	3-Year Customer First™ Warranty featuring FREE 2-Day Advance Replacement (US only). Please see warranty document for more details and for replacement procedures outside the US.
Options / Features	Wide viewing angle, Discreet branding, Anti-glare coating, Multi-language display, On screen display (OSD), Kensington® Security Slot, height adjustment: 5.1" (130cmm), Swivel range 90° (45° left, 45° right), pivot 90°
Blue Light Reduction	Yes
Flicker Free	Yes
In the Box	PLL2251MW LED LCD Monitor, Power cord, HDMI cable, User's guide
UPC	8 10689 00577 3

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 5/17/2018

© Copyright 2018 Planar Systems, Inc. All rights reserved