

IL-926W



Protect and preserve important documents with the Royal Sovereign 9", 2 Roller Pouch Laminator.



Highlights

- **Efficiency:** Laminates at 18.90 in. (480 mm.) per minute.
- **Protection:** 2 roller system prevents wrinkling, bubbling, and hazing.
- **Versatile:** Hot and Cold lamination for pouches 3-5 Mil. thick.
- **Convenience:** 60 second warmup time.
- **Jam Assistance:** Jam removal button located on the back of the unit.
- **Overheat Protection:** After 30 minutes of non-use the heater will shut off.

Perfect solution for home, office, or professional lamination!

IL-926W



9" ENTRY FEED

GLASS TOP
DESIGN

60 SECOND
WARMUP



SPECIFICATIONS

Power Supply Voltage	120V (60 Hz)	Individual Carton Dimensions	14.76" x 5.2" x 3.74" 375 mm x 132 mm x 95 mm
Power Consumption	500W	Individual Carton Weight	3.26 lbs. (1.48 kg)
Number of Rollers	2	Individual Carton UPC Code	849023090274
Speed	18.9 in. (480 mm.) per minute	Master Carton Dimensions	15.67" x 14.88" x 5.98" 398 mm x 378 mm x 152 mm
Maximum Entry Width	9 in. (230 mm.)	Master Carton Weight	13.67 lbs. (6.2 kg)
Pouch Mil. Thickness	3 Mil. – 5 Mil.	Master Carton Count	4
Warm-up Time	60 seconds	Master Carton UPC Code	50849023090279
Certification	cTUVus		
Dimensions	13.58" x 4.13" x 2.95" 345 mm x 105 mm x 75 mm		
Weight	2.65 lbs. (1.2 kg)		

1 Year Warranty