

ADVANCED SERIES IN2139WU

WXGA - 4500 LUMENS - 16:10 Aspect Ratio

Superior lens performance, brighter-than-ever images, comprehensive networking capabilities, and room-filling internal audio — all in a projector designed to work seamlessly with the devices you're already using.

Features

Customize your projector using TechStation

Connect your EZCASTPRO, Google ChromeCast, Amazon FireStick, Android TV, and others, the TechStation superpowers your projector and enables more effective learning by working seamlessly with the tools you already use. After connecting your device, close up the TechStation's lid to create a streamlined, all-in-one solution for streaming audio and video.

High Brightness

Get better, brighter images on any surface, in any light. The LightPro Advanced DLP Series Projector has up to 4500 lumens.

Quietest Projector in its Class

Make sure students always hear the lessons, not the fans. With only 21dB in eco mode, the LightPro Advanced DLP Series Projector was designed to be quieter, with Smooth Flow fan technology, a cooling-efficient enclosure, and silent bearings.

Industry-leading Lamp Life

The LightPro Advanced DLP Series Projector features up to an unprecedented 15,000 hours of lamp life when used in Dynamic Mode. With no filters to replace, these projectors are an unbeatable value.

Triple HDMI

An extra HDMI connection allows for multiple digital sources to be connected avoiding the need to change cables.

Zoom

The zoom ratio adds flexibility for installations using pre-existing mounts. Adjust the zoom to create the perfect image in the same space.

Image

Projection Technology	Texas Instruments DLP®
Panel Size	0.67 S600
Native Resolution	WUXGA
Pixels	1280x 800
Aspect Ratio	16:10
Contrast Ratio	28500:1
Brightness (Lumens)	4500
Light Source	UHP Lamp
Light Source Life Maximum Hours	15000
Maximum Supported Resolution	1920 x 1200
Horizontal Sync. Range (KHz)	31.5 - 97.6
Vertical Sync. Range (Hz)	56 - 120
Uniformity (%)	JBMA 80%, ANSI 75%

Optical

Lens	-
Lens Zoom Adjustment	Manual
Optional Lenses	-

Image Offset (%)	115%
Focal Length (mm)	-
F-Stop	2.43 / 2.78
Vertical Lens shift (%)	-
Horizontal Lens shift (%)	-
Keystone Adjustment	Manual
Vertical Keystone Correction	± 40
Horizontal Keystone Correction	±5
Projection Factor	1.18:1 - 1.54:1
Projection Distance (Meters/Feet)	1.0 - 7.7 / 3.3 - 25.3
Optical Zoom	1.3:1
Digital Zoom Demagnification / Magnification	0.8x ~ 2.0x
Focus Adjustment	Manual

Connectivity

Inputs

Mini D-sub 15-pin (VGA)	<input checked="" type="checkbox"/>
Composite Video	<input checked="" type="checkbox"/>
S-Video	-
HDMI™ 1.4	<input checked="" type="checkbox"/> <input checked="" type="checkbox"/> <input checked="" type="checkbox"/>
HDMI™ 2.0	-
USB-B 2.0	-
RJ45 - LAN 10/100/1000	<input checked="" type="checkbox"/>
3.5 mm Stereo Mini Jack	<input checked="" type="checkbox"/>
3.5 mm Stereo Mini Jack with Microphone	-

Outputs

Mini D-sub 15-pin (VGA)	<input checked="" type="checkbox"/>
3.5 mm Stereo Mini Jack	<input checked="" type="checkbox"/>
Powered USB-A for Wireless Dongle	<input checked="" type="checkbox"/>
3D Sync	-
Other	
RS232	<input checked="" type="checkbox"/>
RJ45 HDBaseT	-
All Major 3D Formats	<input checked="" type="checkbox"/>
USB-B 2.0 for Service	-
USB-A for Service	<input checked="" type="checkbox"/>
Micro USB for Service	-
Document Reader	-
Video Player	-
Photo Viewer	-
Music Player	-
12v Screen Trigger	-

Power

Power Supply	100 ~ 240 V AC; 50 ~ 60 Hz
Power Consumption Max (W)	330W
Power Consumption Min. (W)	220W
Power Consumption Network Standby (W)	1.8W
Power Consumption Standby (W)	<0.5W

General

Dimensions (W x H x D) (mm / in)	124.5 x 236.2 x 312.4 / 4.9 x 9.3 x 12.3
Product Weight (Kilograms/Pounds)	3.2 / 7.1
Fan Noise (dB)	21
Audio (W)	10
Operating Temperature (Celsius/Fahrenheit)	5 ~ 40 / 41 ~ 104
Operating Humidity (%)	10 ~ 85
Max Operating Altitude (meters / feet)	3048 / 10000
Storage Temperature (Celsius/Fahrenheit)	-10 ~ 60 / 14 ~ 140
Storage Humidity (%)	10 ~ 85
Security	Kensington Security Slot™
In the Box	Power cord, HDMI cable, Safety instructions, User documentation, Remote control (no batteries)
Safety and Regulatory	CB, CE, EAC, cTUVus, CCC, FCC, UKCA, NOM, PSB, BIS
Environmental	WEEE, EU RoHS, China RoHS, CEL, CECP

Copyright © 2022, InFocus and its logo is a registered trademark of InFocus Corporation. Maxnerva Technology Services Limited is the licensee of the registered trademark. All other product names and company names used herein are for identification purposes only and may be trademarks or registered trademarks of their respective owners. Errors and omissions excepted; all specifications are subject to change without notice. All images are for representation purposes only and may be simulated.