

# INV30

InFocus

Short Throw Whiteboard Projector

Part #: INV30

## Available only in Europe

The InFocus INV30 projector provides a bright high-resolution image on a short boom delivering high-definition, high-performance interactivity that is virtually shadow-free and glare-free.

The projector supports video and audio connections from a variety of devices including DVD and Blu-ray™ players, document cameras, and other high-definition sources, and can project media from these sources onto the interactive screen. All HDMI 1.4 inputs are HDCP compliant.

European availability only.

### Key Features

- ◆ XGA (1024 x 768) resolution
- ◆ 3000 lumens
- ◆ High 17000:1 contrast ratio
- ◆ HDMI 1.4 connectivity
- ◆ Accurate and vivid color reproduction with BrilliantColor™ technology



### Specifications\*

Projector	INV30
Resolution – Native	XGA (1024 x 768)
Display Technology	DLP
Video Standard Compatibility	NTSC, NTSC 4.43, PAL, PAL-M, PAL-N, SECAM, 480i, 480p, 576i, 576p, 720p, 1080p
Speakers	Mono 5W x 1
Lamp Brightness	3,000 lumens
Lamp Life	6,500 hours
Lamp Power	240W
Lamp Power – Eco Mode	190W
Contrast Ratio	17,000:1
Number of Colors	16.7 million
Aspect Ratio	4:3
Aspect Ratio Compatibility	16:9, 16:10
Connectors – Inputs	RS232, HDMI 1.4, Composite video, VGA x2, RJ-45 (Ethernet), 3.5mm audio input x2

Projector	INV30
Connectors – Outputs	3.5mm audio output, VGA
Audible Noise	< 38 dBA at 0°F / -17.8°C
Audible Noise – Eco Mode	< 32 dBA at 0°F / -17.8°C
Included Accessories	Power cord, Remote, Documentation
Power Consumption – Standby	0.5W max
Power Consumption – Low Power	240W max
Power Consumption	310W max
Power Standard	AC 100 to 240V, 50/60
Operating Conditions	41 to 104°F at 0 to 10000 ft / 5 to 40°C at 0 to 3048 m
Throw and Zoom	
Throw Distance – Minimum	1 m
Throw Distance – Maximum	1 m
Throw Ratio – Short-Throw Lens – Minimum	0.63
Throw Ratio – Short-Throw Lens – Maximum	0.63
Zoom Ratio – Short-Throw Lens	1.1:1
Shipping	

\* Product specifications, terms, and offerings are subject to change at any time without notice.