

4-Port HDMI over Cat6 Splitter/Extender, 4K 60 Hz, HDR, PoC, Multi-Resolution Support, 125 ft., TAA

MODEL NUMBER: **B127P-004-H**



Transmitter/splitter extends a 4K HDMI audio/video signal via Cat6 cable to 4 projectors, monitors or HDTVs up to 125 ft. away.

Features

Splitter Ideal for Digital Signage or Displaying Video in Schools or Trade Show Booths This four-port transmitter/splitter is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings and other digital signage applications where the source and display are farther apart than conventional A/V cables allow. The B127P-004-H extends 4K (at 60 Hz) video and stereo audio signals from an HDMI source device to four HDMI displays up to 125 feet (38.1 meters) away via user-supplied Cat6 cabling. It can also extend a 4K HDMI signal (at 30 Hz) up to 150 feet (45.7 meters) and a 1080p HDMI signal (at 60 Hz) up to 200 feet (61 meters) using B127P-100-H receiver.

Transmits Crystal-Clear 4K HDMI Video with Multi-Channel Audio and 4:4:4 Color The B127P-004-H supports Ultra HD video resolutions up to 4K x 2K (3840 x 2160) at 60 Hz with full, rich uncompressed DTS-HD, Dolby TrueHD and 7.1-channel digital audio. This transmitter is capable of carrying HDR signals, which provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks. It supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. HDCP 2.2 compliance allows you to stream iTunes and Netflix content with no complications.

Multi-Resolution Support Allows Mixing and Matching of Displays of Different Resolutions Say you have a brand new 4K (at 60 Hz) HDTV in the living room, but want to also connect your Blu-ray player or satellite box to the older 1080p TV in the bedroom. The B127P-004-H is backward compatible with 4K (at 30 Hz) and 1080p (at 60 Hz) resolutions via automatic switching. This splitter allows each connected television to display video at its maximum resolution. Most other splitters default all displays to the lowest common resolution (meaning you would only get a 1080p image on that new 4K TV).

Built-In PoC Technology Provides Power to Avoid Bulky External Power Bricks Built-in Power over Cable (PoC) technology powers the connected B127P-100-H or B127P-100-H-SR receiver over Cat6 cable. Green and orange LEDs will light up to indicate the unit is receiving power and a signal is being received. PoC lets you avoid the hassle of a bulky power brick and gives you the freedom to transfer power to the remote receivers and place them away from an AC outlet.

Plug-and-Play Operation for Quick Setup and Immediate Use The included transmitter works right out of the box with no software required. Mounting hardware is included for installing the unit on a wall, pole or

Highlights

- Works in tandem with B127P-100-H or B127P-100-H-SR remote receivers
- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear video
- Power over Cable (PoC) technology provides power to the receiver via Cat6 cable
- Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracy
- Supports multi-resolution output to allow for combination of different display types

Applications

- Connect a media server, Blu-ray player, cable/satellite box, Roku, gaming system or other home theater component to four large-screen 4K televisions or projectors
- Upgrade the video quality of your trade show presentation or digital signage installation in a commercial or educational setting to 4K x 2K
- Set up digital signage with a single video signal being transmitted to 4 monitors, each displaying its maximum resolution
- Mount a security camera in an out-of-the-way spot without the burden of placing it near an AC outlet

System Requirements

- Source device with HDMI output (Blu-ray player, cable box, laptop)
- B127P-100-H or B127P-100-H-SR remote receivers

Package Includes

- Transmitter unit
- External power supply with 4.5 ft. cord (Input: 100-240V, 50/60 Hz, 1.5A; Output: 24V 2A)
- (4) International plug adapters (North America, Europe, U.K. and Australia)
- Mounting hardware
- Owner's manual

19-inch rack. Connect the transmitter to the source with a user-supplied HDMI cable (such as P568- or P569-Series). Then, connect the transmitter to B127P-100-H or B127P-100-H-SR remote receivers using Cat6 patch cable (such as N202-Series cable).

Daisy-Chain Multiple Transmitters to Add More Displays An HDMI output is included for connecting up to three additional B127P-004-H transmitters, each of which splits the original HDMI signal into four. You can also connect an optional display to monitor the image connected to the receivers up to 125 feet away.

TAA-Compliant for GSA Schedule Purchases The B127P-004-H is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332239198
Product Type	Splitter; Extender Kit
Technology	HDMI; Cat5/5e; Cat6; POC
Host Connector	HDMI (FEMALE)
VIDEO	
Video Input	HDMI (FEMALE)
Video Output	HDMI (FEMALE)
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz
Max. Distance (Between any 2 Units)	6 ft. (2m)
Max Number of Ports (Entire Chain)	12
Max 1280 x 720 (720p) Range (ft)	200
Max 1920 x 1080 (1080p) Range (ft)	200
Max 1920 x 1200 Range (ft)	150
Max 2560 x 1600 Range (ft)	150
Max 3840 x 2160 (4K@30Hz) Range (ft)	150
Max 3840 x 2160 (4K@60Hz) Range (ft)	125
Transmitter Video Input	HDMI
Transmitter - Number of Video Outputs	4
Transmitter - Local Display Output	HDMI
Recommended Cabling	N202-Series Cat6 Solid Wire Cables
Max Supported Color Depth	24-bit True Color
HDR Support	Yes

3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	125
Maximum Signal Range (m)	38
AUDIO	
Audio Input	HDMI
Audio Specification	7.1 Channel Surround Sound, DTS-HD and Dolby TrueHD
INPUT	
AC Power Adapter Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.5A
AC Power Adapter Output Specs (V / A)	24V / 2A
AC Power Adapter Cord Length (ft.)	4.5
AC Power Adapter Cord Length (m)	1.37
Bus Powered	No
POWER	
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P; BS1363; CEE 7/16 Schuko; AS/NZS 3112
Power Source	Transmitter end only (Included)
Power Over Cable (PoC) Support	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	x6 ORANGE (OUTPUT, LOCAL, INPUT), GREEN (POWER), x4 GREEN (RJ45 CONNECTION) x4 ORANGE (RJ45 DATA)
PHYSICAL	
Color	Black
Material of Construction	Metal
Cable Length (ft.)	0
Cable Length (m)	0.00
Included Mounting Accessories	Wallmount
Number of Displays	1
Form Factor/Mounting Options	Box; Wall-mount
Rackmountable	Yes
Unit Dimensions (hwd / in.)	1.170 x 9.250 x 3.940

Unit Packaging Type	Box
Unit Weight (lbs.)	1.43
Unit Weight (kg)	0.65
Housing	Metal
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0% to 85% RH, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	125
Signal Range (m)	38
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(4) RJ45 (FEMALE)
Side B - Connector 2	HDMI (FEMALE)
Input x Output	1 x 4
Daisy-chainable / Cascadable	Yes
Daisy-chainable / Cascadable Details	Up to 4 Units
PORT EXPANSION	
Daisy-chainable or Cascadable	Daisy chainable
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
MST Support	No
Multi-Resolution Support	Yes
Built-In Equalizer	Yes

HDCP Specification	2.2
Driver Required	No
Recommended Category Cable	N202-Series Cat6 Solid Wire Cables
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CCC; CE; FCC; GS; TUV; UL; cUL
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty