



8-Outlet Surge Protector with 2 USB Ports (2.1A Shared) - 8 ft. (2.43 m) Cord, 1200 Joules, Black

MODEL NUMBER: TLP88USBB











8-outlet surge protector safeguards your home/office electronics against dangerous surges, spikes and line noise.

Features

8-Outlet Surge Protector with USB Safeguards Your Sensitive ElectronicsIdeal for your home or office workstation, this Protect It!® 8-outlet surge protector features a surge protection rating of 1200 joules to defend your sensitive electronic components against strong power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP88USBB protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

NEMA 5-15R Outlets Accept a Wide Range of Electronic DevicesPlug your PC, printer, wireless router, game console, television, sound system or other home/office electronics into eight NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. Three outlets are widely spaced to accommodate bulky power transformers without blocking adjacent outlets. Built-in safety covers prevent dust and debris from falling into unused outlets.

2 USB Ports Share 2.1 Amps of Charging PowerThis surge protector with 2 USB ports is ideal for keeping your devices at full capacity. Two USB-A ports are available for charging your smartphone, tablet and other USB mobile devices..

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Includes the Latest Safety FeaturesThe lighted on/off switch provides one-touch control over connected equipment. A green LED confirms your connected equipment is protected.

Versatile Surge Protector Provides Multiple Installation Options This surge protector with 8-ft. (2.43 m) cord and space-saving right-angle NEMA 5-15P plug helps you connect to a wall outlet located behind furniture placed flush against the wall. Keyhole slots incorporated into the bottom panel provide convenient wall or desk mounting options for the black plastic housing.

Highlights

- 8 NEMA 5-15R outlets distribute AC power to connected home/office equipment
- 1200 joules protect your valuable electronics against dangerous surges and spikes
- 2 USB ports share 2.1A for fast charging of phones, tablets and other mobile devices
- 8-ft. (2.43 m) cord with NEMA 5-15P plug allows flexibility in placing devices away from AC outlet
- Green LED reassures you at a glance that your valuable electronics are protected

Applications

- Protect computers, peripherals, home theater equipment and other valuable electronics against AC power surges and spikes
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against corruption stemming from unexpected surges
- Charge smartphones, tablets or other USB devices via USB ports

Package Includes

 TLP88USBB Protect It! 8-Outlet Surge Protector, Black



• Owner's manual

Specifications

OVERVIEW		
UPC Code	037332223449	
Product Type	Surge Protector	
Charging Form Factor	Strip	
Device Compatibility	Phone; Tablet; Amazon Kindle	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Gauge Type	14 gauge; SJT	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	35500	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	8	
Right-Angle Plug	Yes	
Input Cord Length (m)	2.44	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output (Watts)	1800	
Output Receptacles	(8) 5-15R	
Circuit Breaker (amps)	15	
Overload Protection	15A resettable illuminated combo switch / circuit breaker	
Transformer Accommodation	(6) Yes	
Outlet Orientation	Double row of 8 outlets total	
Right-Angle Outlets	Yes	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch	





Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1200	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression	
UL1449 Let Through Rating	500,500,500	
EMI / RFI Filtering	Yes	
Automatic Shut-Off	No	
CHARGING		
Charging Ports / Amps	(2) 2.1A	
Number of Charging Ports	2	
Charging Method	USB	
Charging Port Type	USB A (FEMALE)	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection	No No	
Cable (Coax) Protection	No No	
Network (Ethernet) Protection	No	
PHYSICAL		
Color	Black	
Antimicrobial Coating	No	
Color (AC Line Cord)	Black	
Housing Color	Black	
Integrated Keyhole Mounting Slots	Yes	
Material of Construction	Plastic	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	11.02 x 7.09 x 1.50	
Shipping Weight (kg)	0.84	
Unit Dimensions (hwd / cm)	23.11 x 9.60 x 3.30	
Unit Dimensions (hwd / in.)	9.10 x 3.78 x 1.30	
SPECIAL FEATURES		
Rotatable Outlets	No	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

STANDARDS & COMPLIANCE		
Canada	cUL	
Approvals	Exceeds IEEE 587 category A&B specifications	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd EDITION	
UL1363 (Power Tap)	UL1363	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies