

1500W Medium-Duty Compact Mobile Power Inverter with 2 AC/2 USB - 2.0A/Battery Cables

MODEL NUMBER: PINV1500



Converts 12V DC power from your vehicle's battery into 120V AC and 5V DC power to operate and charge electronics while on the road.

Features

Mobile Power Inverter Charges and Powers Multiple Electronic Devices in Your Vehicle You don't have to be near your computer or an AC power source to keep your mobile devices fully charged and your power tools and small appliances operating. This 1500W mobile inverter converts 12V DC power from your car, truck, fleet vehicle, boat or RV's battery into standard 120V AC power. Just connect the included battery cables between the inverter's DC input terminals and the positive and negative terminals on your vehicle's battery.

Dual AC Outlets Provide Portable Power for Your Mobile Applications This compact power inverter provides a modified sine wave for use at remote locations, such as campgrounds, construction sites and mobile offices. Two NEMA 5-15R outlets deliver a continuous output of 1500 watts and a peak output of 3000 watts. That's plenty to operate a variety of appliances and power tools, such as low-power lights, camping accessories, battery rechargers for small battery-operated power tools, and mobile office equipment.

Dual USB Charging Ports Keep Your Devices at Full Strength Two 5V USB ports share 2.0 amps of charging capacity and remain active even when the inverter's on/off switch is set to Off. This allows you to charge your smartphone, tablet, laptop, MP3 player or GPS unit without draining too much power from the vehicle's battery.

Includes the Latest Safety Features to Protect Your Equipment and Battery An on/off switch offers one-touch control over both AC outlets. If the power input from the vehicle's battery drops below 10 volts or exceeds 16 volts, the mobile power inverter will automatically shut down. Green and red LEDs indicate normal and improper operation. Two load-controlled fans begin cooling automatically when the internal temperature rises to a certain level during extended use. An audible alarm sounds during excessively high or low voltage conditions.

Brackets Included for Permanent Mounting The compact power inverter's durable aluminum housing is designed to withstand the rigors of road trips, campouts, business trips and family vacations. Use the built-in mounting brackets and your own hardware to install the inverter permanently in a horizontal position.

Specifications

OVERVIEW

Highlights

- Provides portable power for mobile devices, including phones and laptops
- Ideal for areas without regular power outlets, such as campsites or construction sites
- Dual NEMA 5-15R outlets deliver continuous output of 1500W for powering devices
- Dual USB charging ports keep smartphones, tablets and laptops at full capacity
- Rugged aluminum housing built to withstand rigors of travel and outdoor use

Applications

- Power multiple electronic devices and tools from your car, truck, fleet vehicle, boat or RV

Package Includes

- PINV1500 1500W Medium-Duty Compact Car Inverter
- Battery cable, red/black, 3 ft.
- Grounding cable, 3 ft.
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332225177
INPUT	
Recommended Electrical Service	12VDC
Input Connection Type	DC terminal post for battery cables with ring terminals
Voltage Compatibility (VAC)	120
Voltage Compatibility (VDC)	10VDC ~ 16VDC
Input Cord Length (ft.)	3
Input Cord Length (m)	0.91
OUTPUT	
Frequency Compatibility	60 Hz
Pure Sine Wave Output	No
Output (Watts)	1500
Nominal Output Voltage(s) Supported	115V; 120V
Output Receptacles	(2) 5-15R
Continuous Output Capacity (Watts)	1500
Peak Output Capacity (Watts)	3000
Output Voltage Regulation	Maintains PWM sine wave output voltage of 120VAC (+/- 10%)
Output Frequency Regulation	60 Hz (+/- 3 Hz)
Overload Protection	Yes
BATTERY	
Expandable Battery Runtime	User-Supplied 12V DC battery system
DC System Voltage (VDC)	12
Battery Access	Terminal Post
Battery Pack Accessory (Optional)	User-Supplied; 98-121 ; BP260
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	Single multi-color status LED for operation (Green) and fault conditions (RED)
Switches	ON/OFF Rocker Switch
Audible Alarm	Low Battery, Short Circuit, Over-temperature, High DC Voltage, Low DC Voltage and Overload protection
CHARGING	
Charging Ports / Amps	(2) 2A
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Form Factors Supported	Horizontal Floor, Wall-Mount
Material of Construction	Aluminum, Steel
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	6.89 x 5.70 x 2.55
Shipping Weight (kg)	0.69
Unit Dimensions (hwd / cm)	15/14 x 10.59 x 5.99
Unit Dimensions (hwd / in.)	3.00 x 5.04 x 7.28
Unit Weight (kg)	1.22
Unit Weight (lbs.)	2.69
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
Operating Temperature	0C-40C (32F~104F)
SPECIAL FEATURES	
TVSS Grounding	Grounding lug grounds the inverter to vehicle or earth ground; ground cable included
STANDARDS & COMPLIANCE	
Certifications	Tested to UL458:2015 6TH EDITION; CAN/CSA-C22.2 NO.107.1:2016 4TH EDITION
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>