

# Lenovo 300e Windows 2nd Gen **81M9007UUS**

**Product**

Lenovo 300e Windows 2nd Gen

**Region**

NA

**Country/Region**

USA

**Machine Type**

81M9

**TopSeller**

TopSeller

**Processor**

Intel Celeron N4120 (4C / 4T, 1.1 / 2.6GHz, 4MB)

**Graphics**

Integrated Intel UHD Graphics 600

**Chipset**

Intel SoC Platform

**Memory**

4GB Soldered LPDDR4-2400

**Storage**

128GB SSD M.2 2242 PCIe NVMe 3.0x2

**Display**

11.6" HD (1366x768) IPS 250nits Anti-glare

**Touchscreen**

10-point Multi-touch

**Pen**

Lenovo Integrated Pen

**Optical**

None

**Media Reader**

MicroSD Card Reader

**Ethernet**

None

**WLAN + Bluetooth**

Intel 9560 11ac, 2x2 + BT5.0

**Case Material**

PC / ABS

**Camera**

720p

**Microphone**

Mono

**Color**

Black

**Surface Treatment**

Texture

**Keyboard**

Non-backlit, English

**Fingerprint Reader**

None

**TPM**

dTPM

**Battery**

Integrated 42Wh

**Power Adapter**

45W USB-C

**Operating System**

Windows 10 Pro (National Academic License), English

**Bundled Software**

Office Trial

**Base Warranty**

1-year, Mail-in

**Bundled Service**

None

**EAN / UPC / JAN**

195042210446

**End of Support**

2026-04-11

**Announce Date**

2019-11-22

---

**Recommended Services****Best**

3Y Depot + Accidental Damage Protection (School Year Term)  
(5PS0N75610)

**Better**

3Y Depot + Accidental Damage Protection One (School Year Term)  
(5PS0Z44683)

**Good**

3Y Depot (School Year Term) (5WS0N75691)

**Notes:****California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>



**WWW.LENOVO.COM**

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

# Lenovo 300e Windows 2<sup>nd</sup> Gen Platform Specifications

Product Specifications Reference (PSREF)

Processor	Intel® Celeron® Processor or Intel Pentium® Silver Processor								Camera	720p HD, fixed focus, single microphone
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Frequency	Cache	Memory Type	Processor Graphics	Audio support	optional 5MP World Facing camera, single microphone
	Cel N4100	4	4	1.1 GHz	2.4 GHz	4MB	LPDDR4 2400	Intel UHD Graphics 600	Realtek ALC3287, stereo speakers, 2Wx 2, single microphone, headphone / microphone combo jack	
	Cel N4120				2.6 GHz					
	Pen N5000				2.7 GHz					
Pen N5030	3.1 GHz									
Graphics	Intel UHD Graphics 600 or 605 in processor								Keyboard	6-row, spill-resistant, Anti-pry Key Caps
Chipset	Intel SoC (System on Chip) platform								Touchpad	One-piece touchpad
Memory	4GB or 8GB / 2400MHz LPDDR4 / soldered to systemboard, no sockets								Security	Power-on password, supervisor password, security keyhole
Display	11.6" (295mm) HD (1366x768), WVA, anti-glare, LED backlight, 250 nits, 16:9 aspect ratio								Security chip	Discrete TPM 2.0, TCG Certified
Multi-touch	Capacitive-type multi-touch, anti-fingerprint, support 10-finger gesture, pencil touch								Fingerprint reader	None
Hinge	Yoga hinge, 360 degree								Battery type	Integrated Li-ion 42Wh battery
Convertible mode	Laptop, tent, stand and tablet								Max battery life	Up to 10hrs
Pen	Optional: Garaged AES pen, on-board rechargeable									* Battery life varies significantly with hardware configurations, settings, usage, & other factors.
Storage	eMMC 5.1 (embedded Multi Media Card) flash memory or M.2 SSD on board								AC adapter	45W USB-C AC adapter
Optical	None								Preload (opt)	Preloaded operating system
Ethernet	None									• Windows® 10 Home 64
WLAN + Bluetooth™	One of the following, configurable by model:									• Windows 10 Home in S mode
	• Intel Wireless-AC 9560, Wi-Fi 2x2 802.11ac + Bluetooth 5.0, M.2 card									• Windows 10 Pro 64
WWAN	None									• Windows 10 Pro in S mode
										• Windows 10 Pro (National Academic License)
										* Windows 10 Pro (National Academic License) is for K-12 Education Customers only.
										Any request please contact Lenovo Sales Representative for more information.
										Preloaded applications (only some listed)
										• Microsoft Office Trial (with 30-day license)
										• Microsoft Office 365 Personal
										• Microsoft Office Home and Student 2019
Dimensions	WxDxH: 11.42" x 8.03" x 0.82"; 290mm x 204mm x 20.85mm								Limited warranty	One of the following, configurable by model:
Weight	1.31 kg (2.9 lb)									• 1-year mail-in repair service
Case color	Black									• 1-year depot repair service
Case material	PC/ABS plastic									• 1-year depot with 2-year system board repair service
										• 2-year/1-yr battery depot repair service
Media reader	MicroSD card reader								Mil-Spec test	MIL-STD-810G military testing
Ports	One USB-C 3.1 Gen 1 (with the function of power delivery and data transfer), two USB-A 3.1 Gen 1 (one Always On), HDMI, headphone / microphone combo jack, MicroSD card reader, security keyhole								Environment	EPEAT™ Silver; TCO Certified; RoHS-compliant
	* Depending on many factors, actual data transfer speed may be lower than theoretical speed.									

Note: The specifications above may not be available in all regions.

Lenovo  
July 2020

Lenovo™

# Lenovo 300e Windows 2nd Gen

