

Dell 22 Monitor P2217



The smart choice to help boost productivity with more comfort and convenience.

Enhanced productivity

Help boost your productivity with this 22" 16:10 aspect ratio monitor.

- Enjoy a better visual experience with a slim border design — great for multi-monitor setups.
- Efficiently auto apply predefined colour settings for various applications via Dell Auto Mode.
- Reduce desk clutter with integrated power and cable management.

Improved comfort

Work the way you like, comfortably.

- Adjust your view with flexible adjustability features including tilt, pivot, swivel and height-adjustable stand.
- See images clearly with consistent colours across an ultrawide viewing angle.
- Optimise eye comfort with a flicker-free screen and ComfortView feature⁶ which minimises blue light emission.
- Enjoy added convenience and usability thanks to two easily accessible USB 3.0 ports located on the side of the monitor.

Smart investment

You're ready now and for the future with this smart choice.

- Future proof your connectivity with a wide range of digital ports.
- Choose an eco-conscious design which meets latest regulatory and environmental standards.
- Get a variety of mounting options and accessories to flexibly configure your office.

Reliable

Comes with Dell's high reliability promise.


- Enjoy great reliability from the #1 monitor brand worldwide.*
- Experience peace of mind from Dell's commitment to quality and customer satisfaction with the Premium Panel⁵ Guarantee.
- Minimise down time with Dell's standard 3-Year Advanced Exchange Service.³
- Upgrade to 24x7 phone support and Advanced Exchange Service with optional Dell ProSupport.⁷



For more information visit
www.dell.com/monitors

Thank you
for making
Dell Monitors
#1
worldwide*

Easily adjust the panel to your preferred viewing position.



Connectors



A Power cable connector **E** USB upstream
B HDMI **F** USB downstream
C DisplayPort **G** Stand lock feature
D VGA



What's in the box?

Components

- Monitor panel
- Stand (riser and base)

Cables

- Power cable (varies by country)
- VGA, DisplayPort, USB 3.0 upstream cables

Documentation

- Drivers and documentation media (CD)
- Quick Setup Guide
- Safety and regulatory information

Dell 22 Monitor | P2217

Display

Model number	P2217
Viewable image size (diagonal)	55.9 cm (22 inches)
Active display area	
Horizontal	473.76 mm (18.65 inches)
Vertical	296.10 mm (11.66 inches)
Maximum resolution	1680 x 1050 at 60 Hz
Aspect ratio	16:10
Pixel pitch	0.282 mm x 0.282 mm
Brightness (typical)	250 cd/m ²
Colour gamut (typical)	84% ¹
Colour depth	16.7 million colours
Contrast ratio (typical)	1000:1
Mega dynamic contrast ratio	4 million:1
Viewing angle (typical)	
(vertical/horizontal)	160°/170°
Response time (typical)	5 ms black-to-white (typical)
Panel technology	TN
Backlight	LED
Bezel colour	Black

Connectivity

Connectors	DisplayPort 1.2, HDMI 1.4, VGA, 2 x USB 3.0 (side), 2 x USB 2.0 (bottom)
------------	--

Features

Stand	Tilt (Typical: 5° forward or 21° backward), pivot (90°), swivel (45°), height adjustable (130 mm)
Security	Security lock slot (security lock not included)
VESA mounting support (wall mount kit sold separately)	Dell Quick Release feature (100 x 100 mm)
Other	ComfortView

Power

AC input voltage/frequency/current (typical)	100 to 240 VAC / 50 or 60 Hz ± 3 Hz / 1.5 A (typical)
Power consumption (normal operation)	18 W (typical, without USB load) 45 W (Max.)
Power consumption (active-off mode)	< 0.3 W

Dimensions (with stand)

Height (compressed ~ extended)	367.4 mm ~ 497.4 mm (14.46 inches ~ 19.58 inches)
Width	503.4 mm (19.82 inches)
Depth	180.0 mm (7.09 inches)

Weight

Weight (panel only – no stand)	3.00 kg (6.61 lb)
Weight (with stand)	5.33 kg (11.75 lb)
Shipping weight	7.03 kg (15.49 lb)

Standard service plan

- 3 years Premium Panel Guarantee⁵
- 3 years Advanced Exchange Service³ and Limited Hardware Warranty⁴

Environmental compliance

ENERGY STAR®, EPEAT® Gold², TCO Certified Displays, CEL, CECP, RoHS, WEEE, ErP (EuP) Standards, Korea E-Standby

Optional service upgrade

- Dell ProSupport⁷

¹Dell monitors are #1 worldwide for 3 consecutive years! Source: IHS Global Inc. Desktop Monitor Market Tracker (2013 to 2015) ID# G16000073

²**Registered in US and Canada only.

³ Colour gamut (typical) is based on CIE1976 (84%) and CIE1931 (72%) test standards.

⁴ EPEAT Gold registered in the U.S. EPEAT registration varies by country. See www.epeat.net for registration status by country.

⁵ Advanced Exchange Service: Replacement part/unit dispatched, if needed, following completion of phone/online diagnosis. Fee charged for failure to return defective unit. Availability varies. Other conditions apply.

⁶ For a copy of the Limited Hardware Warranty, write Dell Products, Dell House, The Boulevard, Cain Road, Bracknell, Berkshire, RG12 1LF, UK or see dell.com/warranty.

⁷ In the event you discover even one bright pixel during the Limited Hardware Warranty period, a free panel exchange is guaranteed. (see pixel panel info located on Dell.com web page for complete details): <http://support.dell.com/support/topics/global.aspx/support/kcs/document?docid=414288>

⁸ ComfortView feature reduces blue light emission and brightness onscreen.

⁹ Includes 24x7 in-region phone support and replacement monitor shipped to you the next business day.

Product availability varies by country. Please contact your Dell representative for more information.
Based on ID# G16000071 dell.co.uk/monitors

