

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SmartPro 230V 1500VA 1350W Line-Interactive Sine Wave UPS, 2U, Extended Run, WEBCARDLX, LCD, USB, DB9

MODEL NUMBER: SMX1500XLRT2UN











Line-interactive UPS offers complete power protection for professional applications, including retail, casino and hotel management.

Features

1.5kVA/1.35kW/230V Battery Backup for PC Networks, Security Systems or Digital Signage
The SmartPro® line-interactive SMX1500XLRT2UN UPS system with AVR provides reliable battery backup and AC power protection against blackouts, brownouts, overvoltages, surges and line noise that can damage valuable electronics or destroy data. The eight-outlet 230V battery backup with 0.9 power factor is ideal protection for small networks, wiring closets, security systems, telecom, high-end PC gaming, digital signage equipment and other professional applications, including retail, casino and hotel/motel management.

Reliable, Expandable Battery Backup Keeps You Operational Through Power Outages

The field-replaceable, hot-swappable internal battery provides 13.6 minutes of support at half load (675W) and 4.9 minutes at full load (1350W), allowing you to work through short power failures and giving you enough time to safely save files and shut down your system in case of a prolonged blackout. For mission-critical applications demanding scalable extended runtime, the UPS supports external battery packs, such as Tripp Lite's BP36V15-2U (sold separately).

WEBCARDLX Network Interface Offers 24/7 Remote Access for Monitoring and Control

The Java-free HTML5-based WEBCARDLX enables full remote access for site power and UPS status monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network. Automated alerts help prevent accidental overloads, power loss and downtime. WEBCARDLX allows you to use the Auto Probe feature, which can prevent costly service calls by automatically rebooting non-responsive network devices.

8 Outlets Protect Your Connected Components

Eight C13 outlets provide battery backup, 350 joules of surge protection and voltage regulation for your crucial components. Two independently switched two-outlet load banks enable both scheduled and real-time remote rebooting and load shedding.

Automatic Voltage Regulation (AVR) Corrects Low- and High-Voltage Conditions

AVR protects your equipment from incremental hardware damage, data loss and performance problems caused by brownouts and overvoltages. The SMX1500XLRT2UN can correct brownouts as low as 158V and overvoltages as high as 278V back to nominal 230V power continuously, all while keeping the battery fully charged and ready to take over in case of power failure.

Highlights

- Protects equipment against blackouts, brownouts, overvoltages, surges and line
- Keeps AC power running during blackouts to allow time for file saves and safe shutdown
- Maintains continuous 230V nominal output during brownouts and overvoltages
- Included WEBCARDLX network interface allows you 24/7 remote access from anywhere
- Easy-to-read LCD allows realtime monitoring of voltage,
 battery status and other data

Applications

- Protect your small network server and other network components against power surges, line noise, brownouts, overvoltages and blackouts
- Operate essential equipment during short-term power outages using battery backup power
- Shut down desktop PCs and other equipment without data loss during long-term power outages
- Connect high-end security systems, casino gaming machines or digital signage in a small network

Package Includes

SMX1500XLRT2UN 230V
 1500VA 1350W Line-Interactive



Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This UPS system filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Designed for High Efficiency to Help You Save Money and Protect the Environment

A 97% efficiency rating reduces BTU emissions, energy consumption and, ultimately, your energy costs.

Silenceable Alarm and Easy-to-Read LCD Keep You Informed Around the Clock

The front-panel LCD lets you monitor important data, such as load level, power factor, voltage, battery charge and estimated runtimes. It rotates for comfortable viewing in both rack and tower configurations. The audible alarm sounds for power failure, low battery and overloads. You may silence it using the built-in switch or disable it.

Advanced Communications Ports Allow for Automatic Saves and Shutdowns

RS-232 and HID-compliant USB ports connect to a computer running Tripp Lite's free downloadable PowerAlert® software to enable safe unattended file saves and system shutdown in case of a prolonged power failure. The EPO port supports emergency shutdown in large facilities. Cables are included.

Versatile Installation Options

Hardware is included for mounting the Tripp Lite SmartPro UPS system in 2U of space in an EIA-standard 19-inch 4-post rack. Using optional mounting accessories (sold separately), you can adapt the SMX1500XLRT2UN for 2-post (2POSTRMKITWM), front-rail (UPSHDEARKIT), 4-post short-depth (4POSTRAILKITWM), tower (2-9USTAND) or wall mounting (2POSTRMKITWM).

UPS with 8 Outlets

- WEBCARDLX network management card
- USB cable
- DB9 cable
- EPO cable
- (2) C13-to-C14 AC power cords
- Rack-mounting hardware
- Owner's manual

Specifications

OVERVIEW		
UPC Code	037332256423	
UPS Type	Line-Interactive	
INPUT		
Rated input current (Maximum Load)	6.9A	
Nominal Input Voltage(s) Supported	230V AC	
UPS Input Connection Type	C14 inlet	
UPS Input Connection Description	IEC320-C14 input connection accepts a variety of detachable cordsets to match country or site-specific wall receptacles	
Input Circuit Breakers	10A	
Input Phase	Single-Phase	
ОИТРИТ		
Output Volt Amp Capacity (VA)	1500	
Output kVA Capacity (kVA)	1.5	
Output Watt Capacity (Watts)	1350	
Output kW Capacity (kW)	1.35	
Power Factor	0,9	



Nominal Voltage Details	230V nominal output in battery mode
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Line Mode)	+6% / -15%
Output Voltage Regulation (Battery Mode)	+/- 5%
Included Output Power Cables	Set of 2 C13 to C14 power cables included
Load Management Receptacles	Two switchable two-outlet C13 load banks
Hot-Swap PDU options	PDUBHV10 (2U / 8 C13 outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Output Capacity Details	Output is reduced to 1200W maximum when used with external battery packs
Nominal Output Voltage(s) Supported	220V; 230V; 240V
Output Receptacles	(8) C13
Individually Controllable Load Banks	Yes
BATTERY	
Full Load Runtime (min.)	4.9 min. (1350w)
Half Load Runtime (min.)	13.6 min. (675w)
Expandable Battery Runtime	Extended runtime supported via optional external battery packs
External Battery Pack Compatibility	BP36V15-2U (limit 1); BP36V42-3U (multi-pack compatible); BP36V27-2US (multi-pack compatible)
DC System Voltage (VDC)	36
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90% (typical, full load discharge)
Internal UPS Replacement Battery Cartridge	RBC93-2U
Battery Access	Front panel battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
Expandable Runtime	Yes
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 158 to 278
Overvoltage Correction	Input voltages between 244 and 278 are reduced by 12%
Undervoltage Correction	Input voltages between 182 and 206 are boosted by 12%





	+
Severe Undervoltage Correction	Input voltages between 158 and 182 are boosted by 24%
USER INTERFACE, ALERTS & CON	TROLS
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	350
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Cooling Method	Fan
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM); 2-4 post front rail rackmount (UPSHDEARKIT); 4 post rackmount short-depth (2-9USTAND); Wallmount (2-9USTAND enables upright tower UPS placement; 2POSTRMKITWM enables wall-mount and 2-post rackmount installation; 4POSTRAILKITWM enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); UPSHDEARKIT enables installation in 2 or 4-post racks using front vertical rails only, without rear support
Primary Form Factor	Rackmount



Primary UPS Depth (mm)	343	
Primary UPS Height (mm)	89	
Primary UPS Width (mm)	442	
Rack Height	2U	
Shipping Dimensions (hwd / in.)	8.80 x 19.90 x 23.30	
Shipping Weight (kg)	25.72	
UPS Housing Material	Steel	
UPS Power Module Dimensions (hwd, in.)	3.5 x 17.4 x 13.5	
UPS Power Module Weight (kg)	19.55	
UPS Power Module Weight (lbs.)	43.1	
ENVIRONMENTAL		
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius	
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius	
Relative Humidity	0 to 95%, non-condensing	
AC Mode BTU / Hr. (Full Load)	139	
Battery Mode BTU / Hr. (Full Load)	689	
AC Mode Efficiency Rating (100% Load)	97%	
Audible Noise	45 dBA maximum, front side 1m	
COMMUNICATIONS		
Network Management Cards	WEBCARDLX	
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions	
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert	
Communications Cable	USB and DB9 cabling included	
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications	
Communications Interface	DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface; USB	
LINE / BATTERY TRANSFER		
Transfer Time	6 ms. (AC to DC) / 1 ms. (DC to AC)	
Low Voltage Transfer to Battery Power (Setpoint)	158	
High Voltage Transfer to Battery Power (Setpoint)	278	
SPECIAL FEATURES		



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

Grounding Lug	Back panel grounding lug		
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported		
High Availability UPS Features	Hot swappable batteries; Auto Probe Monitoring and Reboot (included)		
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks		
STANDARDS & COMPLIANCE			
UPS Certifications	CE; Tested to GOST (Russia)		
UPS Certification Details	EN62040-1, 62040-2 (Class A)		
WARRANTY			
Product Warranty Period (Worldwide)	2-year limited warranty		

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies