

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

# USB Dock, Triple Display - 4K HDMI & mDP, VGA, USB 3.2 Gen 1, USB-A/C Hub, GbE, 60W PD Charging, Black

# MODEL NUMBER: U442-DOCK16-B



USB-C dock with PD Charging connects up to 3 displays to your tablet or Windows laptop and transmits video to all 3 simultaneously.

### Features

### USB-C Docking Station Turns Your Device's USB-C or Thunderbolt 3 Port into a Workstation

This multiport USB-C dock with PD Charging expands the potential of your Windows laptop, Chromebook, tablet or other device with a USB-C or Thunderbolt 3 port. It's ideal for transmitting 4K video and digital audio to multiple large displays, adding a thumb drive and other USB peripherals, powering and charging a PD Charging-compliant mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

### Supports USB-C DisplayPort Alternate Mode for Transmitting Audio/Video Signals

By connecting the built-in USB-C cable to a source device that supports USB DisplayPort Alt Mode, you can output 4K video and digital audio to a compatible monitor, television or projector without installing special software drivers. Note: only one 4K display can be extended in an application. See the owner's manual for various configurations and maximum resolutions.

### Transmits Crystal-Clear 4K Video and Digital Audio

The HDMI and Mini DisplayPort (mDP) outputs support true 4K resolutions up to 4096 x 2160 at 30 Hz. The VGA port supports HD resolutions up to 1920 x 1200, including 1080p, at 60 Hz.

### Extends High-Definition Video Across All 3 External Displays at the Same Time

By connecting the self-storing USB-C cable to a source that supports DisplayPort MST (Multi-Stream Transport) mode, you may connect up to three monitors simultaneously. With a Windows source device, you can display the same image on all connected monitors, extend the host desktop across them with different windows open on each, or combine them into one large display as a video wall. Note: Mac OS laptops or computers will only extend to one monitor. The other monitors will be mirrored. See the owner's manual for various configurations and maximum resolutions.

### USB Ports Connect Keyboards, Thumb Drives and Other Peripherals

A USB-A port and a USB-C port accept USB peripherals, such as flash drives, mice, keyboards and printers. Both support fast USB 3.2 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with USB 2.0 and USB 1.1 devices.

### PD Charging Port Charges the Connected Notebook, Tablet or Other Device

The USB-C Power Delivery port supports power output up to 20V 3A (60W), which is sufficient for

## Highlights

- Connects 3 displays at the same time for easy multitasking and increasing productivity
- Converts audio/video signals from sources supporting USB-C DisplayPort Alt Mode
- Supports 20V 3A (60W) power output for fast-charging largecapacity mobile devices
- Joins a wired 10/100/1000
  Gigabit Ethernet network when no Wi-Fi is available
- USB-C and USB-A data ports allow connection of flash drives and other peripherals

## Applications

- Extend or mirror your laptop or PC monitor on multiple displays to aid in multitasking and increase productivity
- Transfer data to and from a USB flash drive or external hard drive
- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Connect a microphone/headset to record a podcast or listen to music

### **System Requirements**

 Source device with USB-C or Thunderbolt 3 port that supports



charging and powering the connected source device, such as an Android smartphone or Chromebook. Just connect the device's AC wall charger to the USB-C PD port. This port, as mentioned above, can also be used for transferring data up to 5 Gbps.

### Accesses a Wired Gigabit Ethernet Network

The RJ45 port offers access to a Gigabit Ethernet network when Wi-Fi is unavailable or when a wired connection offers faster speeds. Connect using a UTP cable (Tripp Lite N201-Series Cat6 cables sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

#### Self-Storing USB-C Connector Attaches in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time. The built-in cable fits within the base of the dock for convenient storage.

### Ready to Use Right Out of the Package

The plug-and-play USB-C dock is specifically designed for use with Windows laptops and other notebooks, smartphones, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software or external power source. It's slightly larger than an average smartphone, but compact enough to fit easily into your desk space without taking up much valuable room.

# **Specifications**

OVERVIEW		
UPC Code	037332253620	
BATTERY		
Battery Charging (1.2 Port)	No	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	White (Power)	
CHARGING		
Charging Ports / Amps	(1) 3A	
USB Power Delivery (PD) Charging Support	Yes	
Charging Watts	60	
USB Power Delivery (PD) Charging Specification	3.0	
PHYSICAL		
Color	Gray	
Material of Construction	Aluminum	
Unit Dimensions (hwd / in.)	1.31 x 3.86 x 0.45	
Unit Packaging Type	Box	
Unit Weight (kg)	0.07	
Unit Weight (Ibs.)	0.15	

USB DisplayPort Alternate Mode

Display device with Mini
 DisplayPort, VGA and/or HDMI
 input

### **Package Includes**

- U442-DOCK16-B USB-C Dock, Triple Display, Black
- Owner's manual



ENVIRONMENTAL		
Operating Temperature Range	32 to 122°F (0 to 50°C)	
Storage Temperature Range	-4 to 158°F (-20 to 70°C)	
Operating Humidity Range	10% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 95% RH, Non-Condensing	
Power Provided to Connected Device(s)	USB-C PD Port: 20V/3A (60W), USB2.0-A Ports: 5V/0.5A (2.5W)	
COMMUNICATIONS		
Network Speed	1Gbps	
CONNECTIONS		
Ports	7	
Side A - Connector 1	USB Type-C (MALE)	
Side B - Connector 1	3.5MM (FEMALE); HDMI (FEMALE); MICRO SD (FEMALE); SD (FEMALE); USB Type-C (FEMALE)	
Side B - Connector 2	USB A (FEMALE)	
FEATURES & SPECIFICATIONS		
Max Supported Video Resolution	HDMI/mDP: 4096 x 2160 @30Hz; VGA: 1920 x 1080 @60Hz	
Displayport Specification	1.2	
HDMI Specification	1.4	
HDCP Specification	1.4	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)	
Audio Specification	Stereo Audio	
Driver Required	No	
Recommended Category Cable	Cat6	
Max Supported Color Depth	36-bit Deep Color	
Technology	HDMI; PD Charging; Stereo Audio; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)	
Chroma Sub Sampling	4:2:0; 4:2:2; 4:4:4	
STANDARDS & COMPLIANCE		
Certifications	CE, FCC, RoHS, REACH	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does



not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <u>https://www.tripplite.com/products/product-certification-agencies</u>