

## Cat6a 10G-Certified Snagless Shielded STP Ethernet Cable (RJ45 M/M), PoE, Blue, 30 ft. (9.14 m)

MODEL NUMBER: N262-030-BL



Snagless Cat6a cable with Power over Ethernet (PoE) connects 10G equipment in your high-speed 10GBase-T network.

### Features

**High-Speed Cat6a UTP Patch Cable Ideal for Your 10GBase-T Ethernet Network** Designed for fast transmission and excellent signal quality, this 30-ft. (9.14 m) Cat6a cable ensures peak performance throughout your local area network (LAN). It transmits 10 Gbps data, voice and video through high-speed 10G equipment, including network switches, modems, routers, adapters, hubs and patch panels. It reduces impedance and structural return loss compared to standard 100 MHz wire.

**Supports Power over Ethernet (PoE) to Cut Down on Power Supplies** Because this Cat6a shielded cable supports PoE, it can supply the power to operate compatible PoE devices, such as security cameras, VoIP telephones, point-of-sale kiosks and access control devices. This saves you the expense and effort of purchasing, connecting and installing individual power supplies for each device.

**Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better** Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. The N262-030-BL shields against disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

**Snagless RJ45 Male Connectors Add Extra Protection During Installation** The RJ45 connectors' snagless design protects the locking tabs from being damaged or broken off during installation. The ends are shielded to minimize near-end crosstalk (NEXT) levels. Integral strain relief gives the N262-030-BL extra flexibility, reduces stress, and helps the cable move freely without cracking or breaking loose from the connector.

**Color-Coded to Avoid Misidentification That Can Cause Costly Downtime** This Cat6a UTP patch cable features a blue PVC jacket. The color-coding allows easy, fast identification in a crowded rack or workstation, preventing technicians from accidentally disconnecting the wrong cable.

### Highlights

- Cat6a UTP patch cord rated for high-speed 10 Gbps communications
- Supports PoE to save you expense and effort of powering PoE devices individually
- Disperses EMI/RFI line noise that can destroy data and affect equipment performance
- Snagless RJ45 connectors prevent tabs from being damaged during installation
- Color-coded blue for fast, easy identification in a crowded rack or workstation

### Applications

- Connect 10GBase-T networks or digital signage in a high-density data center
- Deliver power to PoE devices mounted in areas that are difficult to reach or have no electrical outlets
- Replace an old or missing RJ45 cable
- Provide universal connectivity for LAN network components, such as switches, servers, modems, routers, adapters, VoIP phones, security cameras and point-of-sale kiosks

### Package Includes

- N262-030-BL Cat6a 10G-Certified Snagless Shielded STP Network Patch Cable (RJ45 M/M), Blue, 30-ft. (9.14



m)

## Specifications

OVERVIEW	
UPC Code	037332239655
Technology	Cat6a
PHYSICAL	
Color	Blue
Cable Shielding	STP
Cable Jacket Material	PVC
Cable Jacket Rating	FT4
Cable Outer Diameter (OD)	6.2mm
Number of Conductors	4 Pair
Conductor Material	Stranded Copper
Conductor Gauge	26 AWG
Cable Length (ft.)	30
Cable Length (m)	9.1
Cable Length (in.)	360
Cable Length (cm)	914.4
Shipping Dimensions (hwd / cm)	2.54 x 20.32 x 27.30
Shipping Dimensions (hwd / in.)	1.00 x 8.00 x 10.75
Shipping Weight (kg)	0.41
Shipping Weight (lbs.)	0.90
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)
Relative Humidity	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
Bandwidth per TIA Standard	500 MHz
Maximum Bandwidth as Tested	600 MHz
Maximum Data Rate	10Gbps



Network Speed	10Gbps
IEEE Standards Supported	802.3at
<b>CONNECTIONS</b>	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Connector Type	Molded
Wiring Configuration	EIA/TIA 568B
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cable Style	Shielded; Molded
<b>SPECIAL FEATURES</b>	
IP68 Rated	No
Snagless Connector	Yes
Antibacterial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>