

D-Link®

COVR

Covr your Whole Home in Seamless Wi-Fi



Expandable Coverage



Fast, Reliable Wi-Fi



Smarter with Voice Controls

COVR

AC1200 Dual Band Wi-Fi Router



Features

Performance and Connectivity

- Dual-band Wireless AC Wave II up to 1200 Mbps¹
- Wi-Fi MU-MIMO technology creates a powerful, fast, and highly efficient Wi-Fi network
- Two Gigabit Ethernet ports per unit to give you high-speed wired connectivity
- Smart Steering automatically directs your devices to the optimal wireless band

Setup and Management

- Setup and configure your network using the free D-Link Wi-Fi mobile app
- Intuitive setup wizard to guide you through the configuration process
- Effortless plug and play setup

Voice Assistant Compatibility

- Command your router's functionality² with your voice through Amazon Alexa and Google Assistant
- Enable and disable your Wi-Fi guest zone, check login credentials, and reboot the system hands-free

Introducing COVR-C1210 AC1200 Dual Band Wi-Fi Router, the whole-home Wi-Fi router that gives you stable, consistent, and truly seamless Wi-Fi. It features a high-performance Wi-Fi router that covers up to 2,000 sq. ft. – perfect as a stand-alone router for a small apartment. Featuring integrated voice assistant compatibility for Amazon Alexa and Google Assistant, you can control your network with voice commands. You can rest assured that D-Link has got you Covr'd with the COVR-C1210.

Create or Expand your Covr Network

Gone are the days of only being able to use Wi-Fi in certain areas of your home. The COVR-C1210 AC1200 Dual Band Wi-Fi Router covers up to 2000 square feet and allows you to easily expand your Covr mesh network just by adding on a COVR-C1210 unit wherever you need more Wi-Fi coverage. Thanks to revolutionary Smart Roaming technology, the Covr AC1200 Dual Band Wi-Fi Router continually scans the wireless signal strength to your devices, automatically connecting them to the strongest signal available. The Covr AC1200 Dual Band Wi-Fi Router handles the transfer seamlessly, allowing you to walk from room to room without experiencing dropped VoIP calls or frozen video streams. Unlike other whole home Wi-Fi systems that use only two receiving antennas, Covr has three receiving antennas to detect and receive more data from all your devices. You enjoy seamless connectivity no matter where you are in the house. From 1-storey apartments to 4-storey houses, and from basements to back decks, Covr's got you covered.

High-Speed Wired and Wireless Connectivity

With COVR-C1210 you can bring the full potential of Wireless AC speeds of up to 1200 Mbps¹ to any area in your home, including dead spots. The COVR-C1210 creates its own exclusive high-speed Wi-Fi zone for communication with your wireless devices, allowing you to fully experience demanding multimedia applications from anywhere in your home. In addition, the Gigabit Ethernet ports give you solid, dependable wired performance for devices such as Network Attached Storage (NAS), media centers, and gaming consoles.

MU-MIMO and Smart Steering Technology

The Covr AC1200 Dual Band Wi-Fi Router features multi-user multiple input, multiple output (MU-MIMO) Wi-Fi, which transmits multiple separate data streams to each wireless device simultaneously to increase speed and efficiency. Enjoy increased throughput and seamless high-definition streaming media, Internet phone calls, online gaming, and content-rich web surfing throughout your entire home or office with Covr.

Additionally, the COVR-C1210 is equipped with dual-band radios and intelligent Smart Steering. Don't worry if you don't know your 2.4 Ghz from your 5 Ghz, Covr automatically places your device on the optimal wireless band depending on network traffic conditions. With Covr, this happens seamlessly without dropouts, lag, or interruption to your wireless connection, and most importantly - without you ever lifting a finger.


Always Up-to-Date with the Latest Features

Tired of having to visit the website or manually going to the router's UI every so often to check for the latest firmware? The COVR-C1210 will automatically check daily for updates to make sure that the device always has the latest features and the most secure firmware, and will install the update silently in the background. For an extra peace of mind, in the event of failure during the firmware update, the router will store a backup system image in the memory before proceeding with the update.

Simple Setup and Configuration

The Covr AC1200 Dual Band Wi-Fi Router provides you with a home networking solution that is quick and easy to set up. The COVR-C1210 works straight out of the box, so you just need to plug it in to get started. Configure your network in no time with the free D-Link Wi-Fi app on your Android or iOS compatible device, or by using the intuitive web-based interface. Connecting wireless devices to your COVR-C1210 is also a snap thanks to the Wi-Fi Protected Setup (WPS) button, which establishes an instant connection to new devices without the need to enter settings or create passwords.

Hardware Overview



COVR-C1210 Technical Specifications

General

Device Interfaces (per unit)	<ul style="list-style-type: none"> • IEEE 802.11 ac/n/g/a wireless WAN 	<ul style="list-style-type: none"> • 2 x Gigabit Ethernet ports
LEDs	<ul style="list-style-type: none"> • COVR Status LED 	
Antenna Type	<ul style="list-style-type: none"> • 3 x internal antennas 	
Data Signal Rate	<ul style="list-style-type: none"> • 2.4 GHz <ul style="list-style-type: none"> • Up to 300 Mbps¹ • 5 GHz <ul style="list-style-type: none"> • Up to 866 Mbps¹ 	<ul style="list-style-type: none"> • Ethernet <ul style="list-style-type: none"> • 10/100/1000 Mbps (auto-negotiation)
Standards	<ul style="list-style-type: none"> • IEEE 802.3i • IEEE 802.3u • IEEE 802.3ab • Supports auto-negotiation • Supports auto-MDI/MDIX 	<ul style="list-style-type: none"> • IEEE 802.11ac Wave II • IEEE 802.11n • IEEE 802.11g • IEEE 802.11a

Functionality

Wireless Encryption	<ul style="list-style-type: none"> • 128-bit AES data encryption 	<ul style="list-style-type: none"> • WPA/WPA2 wireless encryption
Advanced Features	<ul style="list-style-type: none"> • Covr Wi-Fi <ul style="list-style-type: none"> • Auto-configuration • Wireless roaming • Wireless band steering • Wireless Air Time Fairness (ATF) • D-Link Wi-Fi App Setup and Configuration • Quality of Service (QoS) • MU-MIMO (Wi-Fi) 	<ul style="list-style-type: none"> • Single button Wi-Fi Protected Setup (WPS) • Bridge Mode • VLAN • Guest Zone • Parental Control • Load Balance • Ethernet Backhaul • Voice Control

Physical

Dimensions (L x W x H)	<ul style="list-style-type: none"> • 109 x 117 x 51 mm (4.29 x 4.61 x 2.01 in) 	
Weight (per unit)	<ul style="list-style-type: none"> • 250 g (0.55 lbs) 	
Power Input	<ul style="list-style-type: none"> • 100 V to 240 V/AC, 50/60 Hz 	
Power Consumption	<ul style="list-style-type: none"> • 8.7 W 	
Temperature	<ul style="list-style-type: none"> • Operating: 0 to 40 °C (32 to 104 °F) 	<ul style="list-style-type: none"> • Storage: -20 to 70 °C (-4 to 158 °F)
Humidity	<ul style="list-style-type: none"> • Operating: 10% to 90% non-condensing 	<ul style="list-style-type: none"> • Storage: 5% to 90% non-condensing
Certifications	<ul style="list-style-type: none"> • FCC • CE • IC • RCM 	<ul style="list-style-type: none"> • RoHS • UL • ErP • CB

COVR-C1210

AC1200 Dual Band Wi-Fi Router

Order Information	
<i>Part Number</i>	<i>Description</i>
COVR-C1210	AC1200 Dual Band Wi-Fi Router

¹ Maximum wireless signal rate derived from the IEEE 802.11ac and 802.11n standards specifications. Actual data throughput will vary. Network conditions and environmental factors, including volume of network traffic, building materials and construction, and network overhead, may lower actual data throughput rate. Environmental factors will adversely affect wireless signal range.

² Not all functionality is supported for voice control

Updated 01/07/2019