

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

4-Port HDMI Splitter - 4K @ 60 Hz, 4:4:4, Multi-Resolution Support, HDR, HDCP 2.2, TAA

MODEL NUMBER: B118-004-HDR



Splitter with multi-resolution support transmits 4K video and audio from an HDMI source to four HDMI displays at the same time.

Features

HDMI Splitter Transmits 4K Video + Audio to 4 HDMI Displays at the Same TimeRecommended for home theaters or short-distance digital signage applications in classrooms, offices, churches, restaurants, bars, hotels and trade shows, this Ultra High Definition (UHD) HDMI splitter is quick and easy to install. It connects to an HDMI source device, such as a computer or Blu-ray player, and transmits a 4K audio/video signal to four HDMI monitors, projectors or televisions simultaneously. You can cascade up to three levels of splitters, which expands the total number of connected displays to 64. *Note: The B118-004-HDR sends the same image to all connected displays. If you would like to extend an image over multiple displays, you will need an MST hub, such as the B156-002-HD-V2.*

Supports UHD 4K x 2K Signals up to 15 ft. via HDMI CablingUsing standard 28 AWG HDMI cable, the B118-004-HDR distributes a 4K audio/video signal (at 60 Hz) up to 15 feet (4.6 meters). Be sure the HDMI cables connecting the splitter to the source and displays are no longer than 15 feet. For best performance, we recommend using Tripp Lite's P569-Series HDMI cables.

Multi-Resolution Support Allows Mixing and Matching of Displays of Different ResolutionsSay you have a brand new 4K (at 60 Hz) HDTV in the living room, but want to also connect your Blu-ray player or satellite box to the older 1080p TV in the bedroom. The B118-004-HDR is backward compatible with 4K (at 30 Hz) and 1080p (at 60 Hz) resolutions via automatic DIP switching. This splitter allows each television to display video at its maximum resolution. Most other splitters default each television to the lowest common resolution (meaning you would only get a 1080p image on that new 4K TV).

Supports Up-To-Date Features and FormatsThe B118-004-HDR supports a wide range of audio formats, including DTS-HD, Dolby TrueHD, Dolby Digital Plus and LPCM 7.1-channel surround sound. It also features lip sync pass-through, xvYCC and x.vColor, and video amplifier bandwidth of 600 MHz/6 Gbps per channel (18 Gbps total). To ensure compatibility with the latest hardware, this splitter is compliant with HDCP 2.2 and is capable of carrying High Dynamic Range (HDR) signals for more contrast, brightness and colors. It supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor, as well as 36-bit Deep Color (12 bits per channel).

Ready to Use Right Out of the PackageThe plug-and-play B118-004-HDR requires no additional software or drivers. Connect your devices to the HDMI ports with user-supplied HDMI cables (such as Tripp Lite's P569-Series), and plug the included external power supply (with four international plug adapters to ensure use all over the world) into an AC power source to get started. A green LED indicates the unit is receiving power, and orange LEDs indicate connected HDMI inputs. Use the included hardware to install the unit on a desktop or mount it to a wall.

TAA-Compliant for GSA Schedule PurchasesThe B118-004-HDR is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Transmits up to 15 ft. for digital signage in bars, offices, classrooms, trade shows, etc.
- Supports UHD resolutions up to true 4K @ 60 Hz (4:4:4) for crystal-clear video
- Supports multi-resolution output to allow for combination of different display types
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Watch 4K video content from a notebook, Blu-ray player, cable/satellite box, video game console or media server on multiple televisions or projectors
- Connect a MacBook Pro to give a video presentation on multiple 4K screens
- Attach multiple 4K monitors to your PC to allow easier multitasking or more convenient video editing
- Play online or PC video games that display optimal graphics
- Send Ultra HD content to digital signs or point-of-sale displays
- Connect a security camera or other A/V surveillance equipment to multiple displays



System Requirements

- Source device with HDMI output
- Display device(s) with HDMI input

Package Includes

- B118-004-HDR 4-Port HDMI Splitter with Multi-Resolution Support
- External power supply (Input: 100–240V, 50/60 Hz, 0.35A; Output: 5V 2A)
- International plug adapters (North America, Europe, U.K. and Australia)
- Owner's manual

Specifications

OVERVIEW		
UPC Code	037332238023	
AC Adapter	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A, 4 ft	
Technology	НДМІ	
VIDEO		
Max Supported Video Resolution	4K @ 60Hz (4096 x 2160)	
Max. Distance (Between any 2 Units)	10ft	
Max Number of Ports (Entire Chain)	64	
Max Supported Color Depth	36-bit Deep Color	
HDR Support	Yes	
3D Video Supported	Yes	
AUDIO		
Audio Specification	DTS-HD, Dolby TrueHD, Dolby Digital Plus and LPCM 7.1 Channel Surround Sound	
INPUT		
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240	



External Power Supply Plug(s)	NEMA 5-15P North America; CEE 7/16 Schuko; BS 1363 UK; AS/NZS 3112 Australia	
Bus Powered	No	
Product Length (in.)	5.04	
Product Length (ft.)	0.42	
POWER		
External Power Supply Input Specs (V / Hz / A)	100-240V, 50/60HZ, 0.35A	
External Power Supply Output Specs (V / A)	5V / 2A	
External Power Supply Cord Length (ft.)	4.0	
External Power Supply Cord Length (m.)	1.2	
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve	
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; CCC; PSE; C-Tick; GS; RoHS	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	(x1) Green (Power), (x4) Orange (Signal)	
PHYSICAL		
Color	Black	
Material of Construction	Metal	
Rackmountable	Yes	
Unit Dimensions (hwd / cm)	2.97 x 12.80 x 10.00	
Unit Dimensions (hwd / in.)	1.17 x 5.04 x 3.94	
Unit Packaging Type	Box	
Unit Weight (kg)	0.36	
Unit Weight (lbs.)	0.79	
ENVIRONMENTAL		
Operating Temperature Range	32 to 104 °F (0 to 40 °C)	
Storage Temperature Range	5 to 122 °F (-15 to 50 °C)	
Relative Humidity	0% to 85% RH, Non-Condensing	
COMMUNICATIONS		
EDID Compatible	Yes	
CONNECTIONS		



Ports	4	
Side A - Connector 1	HDMI (FEMALE)	
Side B - Connector 1	(4) HDMI (FEMALE)	
Connector Plating	Nickel	
FEATURES & SPECIFICATIONS		
HDCP Specification	2.2	
Driver Required	No	
STANDARDS & COMPLIANCE		
Certifications	CE, FCC, RoHS, REACH, ISO9001	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies