



ⓘ Discontinued

## Overview

Lead time	Usually in Stock
-----------	------------------

## General

Provided equipment	User manual
Number of tare power	28 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
UPS size	WS

## Physical

Cable length	1.22 m
Colour	Black
Depth	39 cm
Height	19 cm
Mounting preference	No preference
Net weight	7.6 kg
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No
Width	14 cm

## Input

Network frequency	50/60 Hz +/- 5 Hz auto-sensing
Plug standard	IEC 60320 C14
Input voltage limits	140...300 V

Number of cables	1
Input voltage	230 V
Cos phi	0.54

## Output

Rated power in W	650 W
Maximum configurable power in W	650 W
Output frequency	50/60 Hz +/- 1 Hz sync to mains
UPS type	Line interactive
Wave type	Stepped approximation to a sine wave
Nb of power socket outlets	3
Curve equation	Efficiency
Curve fixed loss	0.0247
Curve load maximum	100 %
Curve load minimum	3 %
Curve proportional loss	0
Curve square loss	0.0026
Curve X-axis maximum	100 %
Curve test cond ID	Curve fit of data measured in accordance with the ENERGY STAR Test Method for Uninterruptible Power Supplies. All measurements taken in normal mode(s), at typical environmental conditions, with 230V/50Hz electrical input and balanced resistive load (PF = 1.0) output.
Curve X-axis minimum	0 %
Curve X-axis title	Load
Curve X-axis units	Percentage
Curve Y-axis maximum	100 %
Curve Y-axis minimum	50 %
Curve Y-axis title	Efficiency
Curve Y-axis units	Percentage
Full load runtime	00:01:00 650 W
Graph display	1
Half load runtime	00:05:00 300 W
Output voltage	230 V
Maximum configurable power in VA	1200 VA
Rated power in VA	1200 VA
Transfer time	6 ms typical : 10 ms maximum

## Conformance

Product certifications	CE CB
Standards	EN/IEC 62040-1 EN/IEC 62040-2 CE
Equipment protection policy	Lifetime : 50000 euros

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 ft
Ambient air temperature for storage	-15...40 °C
Storage altitude	0.00...914.40 m
Acoustic level	40 dBA
Show note OP temperature	No
IP degree of protection	IP20

## Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	8 h
Liquid value	0
Battery curve	C
Battery power in VAH	95 VAh runtime 108 VAh capacity
Battery life	1...2 year(s)
Extended runtime	0

## Communications & Management

Control panel	LED Status display with on line : on battery
Alarm	Alarm when on battery : distinctive low battery alarm

## Surge Protection and Filtering

Surge energy rate	273 J
Data line protection	RJ45 10/100/1000 Base-T Ethernet protection

## Packing Units

Package 1 Weight	8.6 kg
Package 1 Height	29.7 cm
Package 1 width	23.5 cm
Package 1 Length	49.5 cm
SCC14	10731304410765

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------