

## Cisco-Compatible SFP-10G-SR-S SFP+ Transceiver - 10GBase-SR, DDM, Multimode LC, 850 nm, 300M (984.25 ft.)

MODEL NUMBER: N286-10G-SR-S



Links a multimode Gigabit Ethernet network cable to a Cisco router, server or switch's SFP port.

### Features

**SFP+ Transceiver Designed for Connection to Your Cisco Network Switch or Server** This SFP+ transceiver allows you to connect a 50/125 multimode fiber optic cable to a 10 Gbps network router, server or switch. It transmits data up to 300 meters (984 feet) and supports bi-directional Gigabit Ethernet communication up to 11.1 Gbps. The metal housing protects against electromagnetic interference (EMI) and excessive power dissipation.

**Functionally Equivalent to Cisco SFP-10G-SR-S Transceiver Module** The MSA-compliant N286-10G-SR-S functions just like the equivalent Cisco SFP-10G-SR-S transceiver module and is manufactured to meet or exceed Cisco specifications. You can use this transceiver with any compatible Cisco router, server or switch and receive the same performance as the SFP-10G-SR-S.

**Hot-Swappable for Installation Without Network Interruption** This input/output device is fully hot-swappable, so you can install it without a potentially costly 10 Gbps network shutdown or device reboot. Just plug the SFP+ end of the transceiver into your Cisco network device. The other end has an LC duplex connector to link with multimode fiber optic cable (sold separately). A convenient bail clasp latch helps you carefully remove the module from the device.

**Supports Digital Diagnostic Monitoring (DDM) for Real-Time Status Monitoring** DDM support lets you keep track of various operating statuses in real time, including transceiver temperature, input and output power, and supply voltage.

**S-Class Transceiver Highly Recommended for Enterprise Network** This S-Class fiber transceiver module is ideal for enterprise network runs of shorter distances than other standard modules. The S-Class N286-10G-SR-S supports only Ethernet protocol and operates only within commercial temperature ranges (0 to 70°C).

## Specifications

### Highlights

- SFP+ transceiver module 100% compatible with Cisco's equivalent module
- Provides 10 Gbps throughput up to 300 m (984 ft.) via multimode fiber cabling
- LC duplex female connector supports 10GBase-SR signal at 850 nm wavelength
- Hot-swappable interface lets you install and uninstall without shutting down
- Supports DDM for monitoring temperature and other real-time operating parameters

### Applications

- Install an additional LC duplex port on a Cisco router, server or switch for the purpose of connecting a multimode Gigabit Ethernet network cable

### System Requirements

- Cisco or other compatible network router, server or switch

### Package Includes

- N286-10G-SR-S Cisco-Compatible SFP-10G-SR-S SFP+ Transceiver
- Quick Start Guide

<b>OVERVIEW</b>	
UPC Code	037332249265
Brand Compatibility	Cisco
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	0.490 x 2.300 x 0.550
Unit Weight (lbs.)	0.064
Unit Weight (kg)	0.03
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	23° to 185°F (-5° to 85°C)
Storage Temperature Range	-40° to 185°F (-40° to 85°C)
Relative Humidity	5% to 85% RH, Non-Condensing
Operating Temperature	23 to 185 F (-5 to 85 C)
<b>COMMUNICATIONS</b>	
Network Compatibility	10 Gbps
Wavelength	850nm
Transmission Distance	300 m
<b>CONNECTIONS</b>	
Side A - Connector 1	SFP+ (MALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Data Transfer Rate	10 Gbps
Multi-Source Agreement (MSA) Compliant	Yes
Optical Port	LC
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.