


SPEC SHEET



Physical Characteristics

- Conductor:** 23 AWG Solid Bare Annealed Copper
- Insulation:** FEP (Fluorinated Ethylene Propylene)
- Conductor Color Code:**
Pair 1: Blue - White/Blue, **Pair 2:** Orange - White/Orange
Pair 3: Green - White/Green, **Pair 4:** Brown - White/Brown
- Spline:** FR Polyolefin
- Rip Cord:** Applied longitudinally under jacket
- Jacket:** Plenum PVC (Low-Smoke, Flame-Retardant and RoHS compliant)
- Jacket Legend:**
0000FT CAT 6 PLUS 4 PR 23 AWG E507576 (UL) CMP c(UL)us FT6 75C (RoHS)
UL VERIFIED TO TIA-568C.2 CAT 6 ##### RM# A B C D E F 1 2 3 4 5 6 7 8 9
- Nominal Cable Diameter (in) :** 0.232
- Nominal Cable Net Weight (lbs/1000ft) :** 33.10
- Minimum Bend Radius (in) :** 1.0
- Maximum Pulling Force (lbs):** 25
- Temperature Rating (°F):**
Installation: +32 to + 140 **Storage & Operation:** -4 to + 167
- Operating Voltage:** 300V

Applications

- IEEE802.3: 1000BASE-T, 100 BASE-TX, 10 BASE-T, ANSI/TIA/EIA 854: 1000BASE-TX, 155Mp/s, 1.2 Gb/s ATM, ANSI X3.263: 100Mb/s, IEEE 802.3af DTE Power (PoE), Digital Video

Standard Compliance

- ANSI/TIA-568-C.2
- ANSI/TIA-862 (Building Automation)
- IEC 11801 Ed.2.0 (Class E)
- ICEA S-102-700 (Category 6)
- NEC/CEC Type CMP (NFPA 262) for Plenum
- UL 444
- RoHS Compliant Directive 2011/65/EU

Certifications



Certifications for Management System

- ISO9001: 2008, ISO14001: 2004, OHSAS 18001

Electrical Characteristics

Max. Capacitance (nF/100m @ 1 kHz)	Max. DC Resistance (Ω/100m @ 68°F)	Dielectric strength (DC-kV, 2s)	Characteristic Impedance (Ω 1~100 MHz)
5.6	9.38	2.5	100 ± 15

Frequency	Insertion Loss	NEXT	PSNEXT	ACRF	PSACRF	Return Loss	PD	PD Skew
MHz	Max. dB/100m	Min. dB/100m	Min. dB/100m	Min. dB/100m	Min. dB/100m	Min. dB/100m	Max. ns/100m	Max. ns/100m
1	2.0	74.3	72.3	67.8	64.8	20.0	570	45
4	3.8	65.3	63.3	55.8	52.8	23.0	552	45
10	6.0	59.3	57.3	47.8	44.8	25.0	545	45
16	7.6	56.2	54.2	43.7	40.7	25.0	543	45
20	8.5	54.8	52.8	41.8	38.8	25.0	542	45
31.25	10.7	51.9	49.9	37.9	34.9	23.6	540	45
62.5	15.4	47.4	45.4	31.9	28.9	21.5	539	45
100	19.8	44.3	42.3	27.8	24.8	20.1	538	45
250	32.8	38.3	36.3	19.8	16.8	17.3	536	45
350	39.8	36.1	34.1	16.9	13.9	16.3	536	45
450	46.0	34.5	32.5	14.7	11.7	15.5	536	45
550	51.8	33.2	31.2	13.0	10.0	14.9	536	45

* Spec meets ANSI/TIA/EIA 568 C.2 standard. Performance above 250MHz is only information value. All values are dB/ 100 m (328ft)