

ideapad 5 (14", 15")

REFINED FOR LIFE.

The Lenovo™ **IdeaPad™** 5 brings you more for less, by blending performance, connectivity, entertainment, and affordability with a sleek design and feel, Dolby Audio™, and up to AMD Ryzen™ 4000 series mobile processing options with Radeon™ graphics.



MORE CORES MEANS MORE PRODUCTIVITY.

With the most cores* available for ultrathin laptops and responsiveness that leaps into action for productivity, gaming, and content creation, AMD Ryzen™ 4000 series mobile processors give you the performance to do more, from anywhere – faster than ever before.

* Ultrathin laptop processors defined as 15W typical TDP. As of December 20, 2019, demonstrated by Ryzen™ 4000 U-series mobile processor having up to 8-cores, while comparable competitive product (Intel® 10th generation mobile processors) offer up to 6-cores.




WHY YOU SHOULD BUY THE LENOVO IDEAPAD 5 (14", 15")



The smart choice

The last thing you need is a hacker peeking into your life through your webcam, so the physical privacy shutter blocks the camera when you don't want to be seen. Using a Post-it note is so 'ok boomer'. It's the simple things like being able to power up and log in with just a single touch with an optional fingerprint reader on the power button that you can set to wake up when it detects your biometric signature that make the **IdeaPad 5** the smart choice.



Take down the borders

Step into the world of your favorite movies and shows with up to an IPS display panel designed to maximize your viewing experience. By increasing the amount of screen compared to the size of the surrounding borders, and the **IdeaPad 5** has an incredible 90% Active Area Ratio.



A touch of class

This isn't your typical laptop that you carry around—it's a fashion statement. The **IdeaPad 5** is built with a new level of attention to detail, making this machine soft and comfortable to the touch with a durable paint that creates a better user-experience and multiple color options, so you can find the one that best fits you.



Options galore

The **IdeaPad 5** comes with a host of options including a USB-C port with power delivery to charge your devices right from your laptop, and Quick Charging to get your battery charged as quickly as possible with speedy SSD drives, and bountiful memory options, this PC is more than just an everyday laptop, it's an accessory to your lifestyle.

Lenovo™



WWW.LENOVO.COM

ideapad 5 (14", 15")

SPECIFICATIONS

Lenovo IdeaPad 5-14ARE*, Lenovo IdeaPad 5-15ARE*

PERFORMANCE

Processor

Up to AMD Ryzen™ 7 4800U Mobile Processor with Radeon™ Graphics¹

Operating System

Windows 10 Home

Graphics

UMA : AMD Integrated Graphics; 25W

Camera

1 MP HD 720p with Microphone; Dual Array; Bump Camera

Memory

DDR4 : 4 GB / 8 GB / 16 GB

Storage

IdeaPad 5-14ARE

HDD SATA : Up to 1 TB

SSD PCIe M.2 : Up to 1 TB QLC

IdeaPad 5-15ARE

HDD SATA : Up to 1 TB

SSD PCIe M.2 : Up to 1 TB, 512 GB has TLC / QLC Option

Dual Storage : 128 GB / 256 GB + 1 TB

Audio

2 x 2W Speakers with Dolby Audio™ (User-facing)

Battery²

IdeaPad 5-14

Up to 11 Hours; (TBD)

Up to 95W Adapter; 15 min - 3 hrs rapid charge

IdeaPad 5-15

Up to 15 Hours; (TBD)

Up to 95W Adapter; 15 min - 3 hrs charge, with Rapid Charge Pro

¹ Embargo: January 6, 2020, 6:00 pm. ET.

² All battery life claims are approximate and based on results using the MobileMark™ 2014 battery life benchmark test. Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

³ Weight will vary depending on configuration.

⁴ Available on certain models only.

⁵ Two microphones configuration only.

⁶ Only on 15" model.

⁷ Not all configurations will allow for these I/O ports.

⁸ The actual transfer speed of the USB 3.1 Gen 1 will vary and, depending on many factors, such as the processing capability of host and peripheral devices, file attributes and other factors related to system configuration and your operating environments, will be slower than a speed of 5 Gbit/s.

⁹ Metal version Type-C™ only (no round DC-in port).

DESIGN

Display

IdeaPad 5-14

14" FHD (1920 x 1080) IPS, 16:9, 300 nits, sRGB 100% (Metal)

14" FHD (1920 x 1080) IPS, 16:9, 300 nits, 45% NTSC

14" FHD (1920 x 1080) TN, 16:9, 250 nits, 45% NTSC

14" HD (1366 x 768) TN, 16:9, 220 nits, 45% NTSC

Narrow Border, 90% AAR (Top: <7 mm, L/R: 4.3 mm, Bottom: <10 mm)

IdeaPad 5-15

15.6" FHD (1920 x 1080) IPS, 16:9, 300 nits, sRGB 100% (Metal)

15.6" FHD (1920 x 1080) IPS, 16:9, 300 nits, 45% NTSC

15.6" FHD (1920 x 1080) IPS, 16:9, 300 nits, 45% NTSC, On-Cell Touch

15.6" FHD (1920 x 1080) TN, 16:9, 250 nits, 45% NTSC

Narrow Border, 90% AAR (Top: <7 mm, L/R: 4.3 mm, Bottom: <10 mm)

Weight³

IdeaPad 5-14

Starting at 1.52 kg (3.35 lbs)

IdeaPad 5-15

Starting at 1.66 kg (3.65 lbs)

PRELOADED SOFTWARE

- Windows 10 S
- McAfee LiveSafe™
- Microsoft Office
- Lenovo Utility
- Lenovo Vantage
- Alexa⁴
- Mirkat

Dimensions (W x D x H)

IdeaPad 5-14

Plastic

(mm) : 321.69 x 211.84 x as thin as 17.9

(inches) : 12.66" x 8.34" x as thin as 0.70

Metal

(mm) : 321.69 x 211.84 x as thin as 16.9

(inches) : 12.66" x 8.34" x as thin as 0.66

IdeaPad 5-15

Plastic

(mm) : 356.67 x 233.13 x as thin as 17.9

(inches) : 14.04" x 9.17" x as thin as 0.70

Metal

(mm) : 356.67 x 233.13 x as thin as 16.9

(inches) : 14.04" x 9.17" x as thin as 0.66

Hinge

135°, One Hand Open

Wow Features

Standard

Privacy Shutter

Windows Cortana⁵

Optional

Backlit Keyboard (White)

Fingerprint Reader (on power button)

Touch Screen Display⁶

Colors

Platinum Grey Silky

Graphite Grey Soft

Light Teal Silky

CONNECTIVITY

WLAN

Up to 2x2 WiFi 6 (802.11 ax/ac/a/b/g/n)

Bluetooth⁷

Bluetooth® up to 5.1

I/O (Input/Output) Ports⁷

2 x USB 3.1 Gen 1⁸

1 x USB Type-C™ Gen 1 (PD 3.0 + DisplayPort™ 1.2)

HDMI™ 1.4b

SD Card Reader

Audio Jack

DC-In (round or Type-C)⁹

OPTIONS & ACCESSORIES



Lenovo 520
Wireless Mouse




Lenovo USB-C
3-in-1 Hub



Lenovo 100
In-Ear Headphone

* Example of Lenovo IdeaPad catalogue naming convention



AMD platform codes

Bristol Ridge-L: ABL, Beema: ABM, Bristol Ridge: ABR, Carrizo-L: ACL, Carrizo: ACZ, Godavari: AGR, Kaveri: AKV, Stony Ridge: ASR, Stony Ridge: AST (NB), Summit Ridge: ASU, Raven Ridge: ARR, Picasso: API, Renoir: ARE



WWW.LENOVO.COM



Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, ideapad, ideacentre, yoga and yoga home. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Battery life (and recharge times) will vary based on many factors including system settings and usage. Visit www.lenovo.com/lenovo/us/en/safecomp/ periodically for the latest information on safe and effective computing. ©2020 Lenovo. All rights reserved.

Lenovo™