

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OMNI900LCD is not for sale in Colorado, Vermont and Washington state. Customers in these states should purchase the recommended ENERGY STAR® 2.0 model instead: OMNISMART750MX. Learn more about <u>ENERGY STAR 2.0 and sales restrictions</u> in these states.

OmniSmart LCD 120V 900VA 475W Line-Interactive UPS, Tower, LCD display, USB port

MODEL NUMBER: OMNI900LCD











Highlights

- 900VA tower 120V line interactive UPS with LCD display
- Corrects brownouts as low as 89V without using battery power
- LCD screen reports input voltage, battery charge and UPS status
- USB port, Surge-only outlets, 97% efficiency
- NEMA 5-15P input plug and 8 NEMA 5-15R outlets

Package Includes

- OMNI900LCD UPS System
- Instruction manual

Description

Tripp Lite's OMNI900LCD Line-Interactive Digital UPS System offers voltage regulation, surge suppression and long lasting battery support for personal computers, home entertainment systems and media centers. Internal UPS circuits support entry level PCs for up to 50 minutes or individual VCR/DVR components for as long as 2.5 hours during power failures. Prevents data loss, viewing interruptions, lost recordings and loss of component programming. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 89 volts back to usable levels without using battery power. 97% line-mode efficiency saves energy and reduces BTU heat output. Offers complete power protection in an attractive black tower configuration. Includes 4 battery-supported and surge-protected outlets, plus 4 additional surge suppression-only outlets for items not requiring battery support. USB port enables optional unattended system shutdown without data loss in the case of extended power failure. PowerAlert software available via free download. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Built-in audible alarm and large LCD front panel voltage display indicates line power status, battery power status, battery low/replace status and voltage boost operation. The LCD display includes a dimmer switch and can be rotated for easy viewing in any application. 900VA/475 watt power handling ability supports entry-level PCs, home entertainment systems, network workstations, audio/video components. Offers 3 minutes battery runtime with a full load of 900VA/475 watts and 10 minutes with a half load of 450VA/237 watts. Supports battery replacement via built-in access panel. \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- LCD Display with dimmer switch indicates input voltage, battery capacity and a variety of operating conditions. Display is rotatable for easy viewing whether UPS is in vertical or horizontal position
- OMNI900LCD Digital Uninterruptible Power Supply offers voltage regulation, surge suppression and



long lasting battery support during blackouts

- Supports entry level PCs up to 50 minutes or single VCR/DVR components for up to 2.5 hours during blackouts
- 97% line-mode efficiency saves energy and reduces BTU heat output
- Regulates brownouts as low as 89 volts back to usable levels without using battery power
- 4 UPS battery-supported and surge-protected outlets, plus 4 additional surge suppression-only outlets
- USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert (user supplies cable)
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- 900VA/475 watt power handling ability supports a variety of sensitive computer, home theater and other equipment
- 3 minutes full load runtime (900VA/475 watts), 10 minutes half load runtime (450VA/237 watts)
- Cabinet adapts to tower format or rackmount shelf format. Rackmount (2U) format requires an optional shelf, available separately
- Supports battery replacement via built-in access panel
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW			
UPC Code	037332125156		
UPS Type	Line-Interactive		
INPUT			
Rated input current (Maximum Load)	12A		
Nominal Input Voltage(s) Supported	120V AC		
UPS Input Connection Type	5-15P; Right-Angled		
UPS Input Cord Length (ft.)	6		
UPS Input Cord Length (m)	1.8		
Recommended Electrical Service	15A 120V		
Input Phase	Single-Phase		
OUTPUT			
Output Volt Amp Capacity (VA)	900		
Output Watt Capacity (Watts)	475		
Nominal Voltage Details	115v nominal output in battery mode		
Frequency Compatibility	60 Hz		
Output Voltage Regulation (Battery Mode)	+/- 5%		





UPS Output Receptacles (Surge Suppression Only)	4 UPS outlets, 4 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(8) 5-15R
Individually Controllable Load Banks	No
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Full Load Runtime (min.)	3 min. (475w)
Half Load Runtime (min.)	10 min. (240w)
Expandable Runtime	No
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	Less than 16 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	RBC51 RBC51 RBC51 RBC51 RBC51



EMI / RFI AC Noise Suppression	Yes	
PHYSICAL		
Primary Form Factor	Tower	
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop	
Primary UPS Depth (mm)	183	
Primary UPS Height (mm)	300	
Primary UPS Width (mm)	94	
Shipping Dimensions (hwd / cm)	39.37 x 11.94 x 26.67	
Shipping Dimensions (hwd / in.)	15.50 x 4.70 x 10.50	
Shipping Weight (kg)	7.48	
Shipping Weight (lbs.)	16.50	
UPS Housing Material	ABS	
UPS Power Module Dimensions (hwd, cm)	29.97 x 9.40 x 18.29	
UPS Power Module Dimensions (hwd, in.)	11.8 x 3.7 x 7.2	
UPS Power Module Weight (kg)	6.85	
UPS Power Module Weight (lbs.)	15.1	
ENVIRONMENTAL		
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius	
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius	
Relative Humidity	0 to 95%, non-condensing	
AC Mode BTU / Hr. (Full Load)	61	
Battery Mode BTU / Hr. (Full Load)	485	
AC Mode Efficiency Rating (100% Load)	97%	
COMMUNICATIONS		
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at https://www.tripplite.com/poweralert	
Communications Cable	User supplies USB cable	
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications	
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite	
Network Management Card Description	Network management not supported	
Communications Interface	USB (HID enabled)	





LINE / BATTERY TRANSFER		
Transfer Time	4 milliseconds (AC to Battery); 3 milliseconds (Battery to AC)	
Low Voltage Transfer to Battery Power (Setpoint)	89	
High Voltage Transfer to Battery Power (Setpoint)	139	
FEATURES & SPECIFICATIONS		
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported	
High Availability UPS Features	Automatic Voltage Regulation (AVR); Hot swappable batteries; Surge/noise protection	
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS	
STANDARDS & COMPLIANCE		
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); ROHS (Restriction of Hazardous Substances)	
WARRANTY		
Product Warranty Period (U.S. & Canada)	3-year limited warranty	
Product Warranty Period (Latin America)	3-year limited warranty	
Product Warranty Period (International)	2-year limited warranty	
Product Warranty Period (Mexico)	3-year limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 Ultimate Lifetime Insurance	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies