

CHERRY MC 4900



Models may vary from the image shown

Easy Log-On and Authentication By Fingerprint

The integrated FingerTip sensor means the CHERRY MC 4900 wired mouse stands for easy log-on. Fast and secure user authentication by means of your own fingerprint.

Key Benefits

- Fingerprint reader in the mouse
- Easy log-on using fingerprint
- Windows Hello
- 3-button mouse
- SDK for integration into other applications
- Optical sensor (1375 dpi)
- Symmetrical mouse
- 6 ft cable with USB connection

Technical Data:

Weight (product):

approx. 150 g / approx. 5.29 oz

Total Weight (with packaging):

approx. 185 g / approx. 6.53 oz

Cable Length:

approx. 1.80 m / approx. 5.91 ft

Storage Temperature:

-20°C to 65°C / -4° F to 149° F

Operating Temperature:

0°C to 40°C / 32° F to 104° F

Interface:

- USB

Product Approvals:

- CE
- FCC
- cTUVus
- IGEL Ready



System Requirements:

- USB plug and USB supporting operating system
- Windows Biometric Framework driver (WIN 8.1, 10) for Windows Hello can be downloaded from our website.
- See our website for information on software development kits for other Windows, Linux, Android and Mac operating systems.

Dimensions (product):

approx. 115 x 65 x 40 mm / approx. 4.53 x 2.56 x 1.57 in

Packaging Dimensions:

approx. 135 x 90 x 48 mm / approx. 5.31 x 3.54 x 1.89 in

Mouse:

- Scanning: Optical
- Resolution: 1375 dpi
- Number of Keys: 3
- Mouse Wheel Design: Scroll wheel with key function
- Design: Symmetrical
- Connection: USB
- Housing Color: silver/black
- Key Color: silver

Fingerprint Reader:

- Reading Principle: Capacitive (surface)
- Resolution: 508 dpi
- Sensor Surface: 10.4 x 14.4 mm / .41 x .57 in
- Hardware Interface: USB

Packaging Unit:

- Number of products in the master package: 10

Warranty:

3-year limited manufacturer's guarantee
For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty:

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.



CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery delays may occur. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

| | Product Name | Order Number | EAN Code |
|---|---------------------|---------------------|-----------------|
| 1 | CHERRY MC 4900 | JM-A4900 | 4025112088285 |