

## High-Speed Armored HDMI Fiber Active Optical Cable (AOC) with Hooded Connectors - 4K @ 60 Hz, HDR, IP68, M/M, Black, 70 m

MODEL NUMBER: P568FA-70M-WR



Fiber HDMI cable with durable TPU jacket carries 4K video/audio in industrial environments where protection against dust and moisture is needed.

### Features

#### 4K HDMI Cable Connects Industrial and Outdoor Security and Digital Signage Components

This high-speed HDMI cable securely connects HDMI-enabled laptops, tablets, Blu-ray players, game consoles, media servers or security cameras to 4K-ready HDTVs, HD monitors, projectors or home theater receivers. Because the cable uses optical fiber, it can transmit HDMI signals longer distances with no latency or loss. It also eliminates any EMI/RFI line noise that can interfere with your audio/video signal and disrupt the performance of your connected equipment.

#### Transmits Crystal-Clear 4K Video with HDR and 4:4:4 Color

The P568FA-70M-WR is rated up to 18 Gbps and supports Ultra HD resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, as specified in HDMI 2.0. High Dynamic Range (HDR) provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. The cable also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor, as well as other current HDMI standards, including 3D, 48-bit Deep Color and Dolby 5.1-channel surround sound.

#### IP68-Rated Ends Resist Dust and Water

Both HDMI connectors are protected by molded, dust-resistant, IP68-rated watertight hoods, shells and caps. The IP68 rating means the connectors can endure immersion in 1.5 meters of water for up to 60 minutes with no damage or decline in performance. The P568FA-70M-WR is ideal for industrial areas, such as factories and warehouses, and unforgiving outdoor installations, including malls, bus stops and stadiums, where dust, debris and water are present.

#### Armored Cable Jacket Ideal for Areas Where Extra Protection Is Needed

The thermoplastic polyurethane (TPU) jacket offers added protection against the elements, making the P568FA-70M-WR a recommended cable for outdoor applications, such as digital signage and surveillance systems. The TPU jacket is resistant to crushing, cuts and abrasion and is recommended for industrial spaces, including warehouses and medical facilities.

#### Advanced Fiber Cable Is Easier to Install than Copper

Because the fiber cable is slimmer and more flexible than standard copper HDMI cables, the P568FA-70M-WR is easier to install around corners and in hard-to-reach spaces behind equipment. It draws power from the connected device, so no external power supply is needed to transmit the HDMI signal across the longer distances unique to fiber optic cabling. **Note:** the cable must be installed in the correct direction to function properly, so please check the Source and Display labels on the connectors before installation.

### Highlights

- Reel of cable supports 4K @ 60 Hz video resolutions (4:4:4) as specified in HDMI 2.0
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Fiber optic strands transmit audio/video over longer distances than standard copper
- IP68-rated ends resist dust and endure immersion in 1.5 m of water up to 60 min.
- Armored cable with TPU jacket for outdoor use resists crushing, cutting and abrasions

### Applications

- Connect digital signage in factories, warehouses, recycling plants, machine shops and other industrial environments
- Provide 4K video connectivity in outdoor environments susceptible to rain, such as malls, bus stops and theater marquees
- Build high-speed A/V and Ethernet infrastructure in basements, factories, warehouses and other indoor areas prone to flooding
- Watch 4K video content from a Blu-ray player, game console, laptop or tablet on an Ultra HD television, monitor or projector
- Connect a security camera or other A/V surveillance equipment to a central 4K



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.triplite.com

display

**Package Includes**

P568FA-70M-WR High-Speed  
Armored HDMI Fiber Active Optical  
Cable on Reel, M/M, Black, 70 m  
(230 ft.)

## Specifications

OVERVIEW	
UPC Code	037332261489
Product Type	Active Optical Cable (AOC)
Technology	HDMI; HDR; Armored
VIDEO	
Video Input	HDMI (MALE)
Video Output	HDMI (MALE)
Max Supported Video Resolution	3840x2160 (4K @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	230
Max 1920 x 1080 (1080p) Range (ft)	230
Max 1920 x 1200 Range (ft)	230
Max 2560 x 1600 Range (ft)	230
Max 3840 x 2160 (4K@30Hz) Range (ft)	230
Max 3840 x 2160 (4K@60Hz) Range (ft)	230
Signal Range (ft)	230
Signal Range (m)	70
Max Supported Color Depth	48-bit
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	230
Maximum Signal Range (m)	70
PHYSICAL	
Color	Black



Cable Jacket Material	TPU
Cable Jacket Rating	Armored
Cable Outer Diameter (OD)	5.8mm
Cable Length (ft.)	230
Cable Length (m)	70
Material of Construction	TPU
Number of Displays	1
Form Factor/Mounting Options	Cable
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 122°F (0 to 50°C)
Storage Temperature Range	-40 to 158 °F (-40 to 70 °C)
Operating Humidity Range	10% to 80% RH, Non-Condensing
Storage Humidity Range	10% to 80% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
Driver Required	No
Ingress Protection (IP) Rating	IP68
<b>SPECIAL FEATURES</b>	
EMI/RFI Line Noise Protection	Yes
IP68 Rated	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	CE, FCC, RoHS, REACH
Protection Rating	IP68
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<https://www.tripplite.com/products/product-certification-agencies>