

# SmartRack Heavy-Duty 16U 2-Post Open Frame Rack

MODEL NUMBER: SR2POST16HD



Compact 2-post rack houses and organizes 19 in. equipment, such as servers and switches, and can be secured to any flat surface.

## Features

### Compact 16U 2-Post Rack Houses Equipment up to 24 in. Deep

This SmartRack® EIA-310 open frame rack is designed to house 16U of equipment, including servers, UPS systems, switches, cable managers and PDUs. It's recommended for mounting equipment in retail locations, classrooms, back offices, audio/video editing bays and radio/television studios. Constructed from heavy-duty steel with a durable black powder-coated finish, the 2-post rack has a maximum load capacity of 350 pounds (159 kilograms).

### Bolts Down Almost Anywhere to Protect Equipment and Save Space

The special cantilever design allows the SR2POST16HD to house heavy equipment up to 24 inches (61 centimeters) deep without the risk of tipping over. Securement brackets and rubber feet are included for anchoring the rack to a flat surface with user-supplied hardware. The rack offers a small footprint and is able to fit almost anywhere in virtually any environment. You can position the open frame rack on any flat surface, including a floor, shelf or workbench.

### Open Frame Design Allows Easy Access

The SR2POST16HD gives you instant access to equipment and cabling in both the front and rear. Install equipment using the 12-24 threaded and numbered mounting positions. Keyhole slots on the sides accept toolless 0U mounting of PDUs and cable managers.

## Highlights

16U 2-post rack made from powder-coated steel that stands up to tough environments  
 Stable cantilever design allows mounting of heavy equipment without threat of tipping  
 Keyhole slots accept toolless 0U vertical mounting of PDUs and cable managers  
 Heavy-duty open frame rack allows maximum equipment load up to 350 lb.  
 Easy to assemble with included hardware for immediate mounting of rack equipment

## Applications

Store and organize rack-mount network components up to 350 lb. on a flat surface, such as a floor, shelf or workbench

## Package Includes

Base(2) Upright brackets  
 Support bar(2)  
 Securement brackets(16)  
 M5 x 12 mm screws(4)  
 Rubber feet  
 Installation guide

## Specifications

OVERVIEW	
UPC Code	037332258557
Device Compatibility	Network Switch; PDU; Patch Panel; Server; UPS
Rack Type	Heavy-Duty; Open-Frame; Floor-Standing
PHYSICAL	
Color	Black



EIA Mounting Rails	12-24 threaded and numbered vertical mounting rails
Maximum Device Depth (cm)	60.96
Maximum Device Depth (in.)	24.00
Maximum Device Depth (mm)	610
Rack Height	16U
Shipping Dimensions (hwd / in.)	7.87 x 34.25 x 17.52
Shipping Weight (kg)	11.70
Unit Dimensions (hwd / cm)	80.289 x 52.553 x 29.718
Unit Dimensions (hwd / in.)	31.610 x 20.630 x 11.700
Unit Weight (kg)	11.34
Unit Weight (lbs.)	25.00
Weight Capacity - Stationary (kg)	159
Weight Capacity - Stationary (lbs.)	350
Rack Depth	Standard
Number of Vertical Mounting Rails	2
<b>SPECIAL FEATURES</b>	
Built-in Cable Management	No
Extra Wide	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	CAN/CSA-C22.2 No. 62368-1-14, UL62368-1, TUV
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>