



PXN2400

24" LCD Monitor

The Planar® PXN2400 24" full HD IPS LED LCD monitor that features a frameless bezel, thin profile, modern design, wide viewing angles, numerous inputs and integrated TrueMedia™ speakers. The Planar PXN2400 is a great fit in either home or office applications.



SPECIFICATION	DETAIL
Product Name	PXN2400
Planar Part Number	998-2121-00
Viewable Size	23.8" diagonal (20.75" horizontal x 11.67" vertical)
Aspect Ratio	16:9
Contrast Ratio (typ)	1000:1
Viewing Angle (typ)	178° Horizontal and 178° Vertical (Specified at CR>10:1)
Response Time (typ)	5 ms (GTG)
Brightness (Typical)	250 cd/m ²
Display Type	IPS LCD Active Matrix Flat Panel Display (TFT)
Display Resolution	1920 x 1080, full HD
Tilt Range	-5° to +20°
Palette	16.7 million colors
Pixel Pitch	0.2745 mm
Refresh Rate	55~76 Hz (60 Hz recommended)
Dimensions (W x H x D)	21.24" x 15.5" x 8.26" (539.5 mm x 393.5 mm x 209.9 mm)
Dimensions without Stand	21.24" x 12.80" x 1.53" (539.5 mm x 325.3 mm x 38.8 mm)
Panel Depth	1.53" (38.8 mm)
Display Weight	8.6 lb (3.9 kg); Weight without stand: 7.5 lb (3.4 kg)
Shipping weight	10.8 lb (4.9 kg)
Video Inputs	HDMI, DisplayPort, VGA
HDCP	Yes

Audio Output	2W x 2, headphone out
External Connections	HDMI 19-pin, DisplayPort 20-pin, VGA 15-pin, 3.5 mm audio in, 3.5mm headphone out
Compatibility	PC and Mac® (adapter may be required for Mac)
Power Supply	Internal
Power Consumption (max)	25 Watt Typical (<0.5 Watt standby)
Power Requirements	AC 100/240 VAC
Operating Temperature	0° to +40°C (32° to 104°F)
Humidity	10 - 90% RH (non-condensing)
Mount	Built-in 100 mm VESA, back
Product Approvals	FCC-B, CE, UL/cUL, RoHS
Recommended Usage	Up to 16 hours per day
Service and Support	3-Year Customer First™ Warranty featuring FREE 2-Day Advance Replacement (US only). Please see warranty document for more details and for replacement procedures outside the US.
Options / Features	IPS Wide color consistent viewing angle, Nearly Borderless bezel, Discreet branding, Anti-glare coating, Multi-language display, On screen display (OSD), Kensington® Security Slot
Blue Light Reduction	Yes
Flicker Free	Yes
In the Box	PXN2400 23.8" LED LCD Monitor, Power Cord, VGA Cable, HDMI Cable, Audio Cable, User's Guide
UPC	8 10689 00800 2

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 11/4/2021

© Copyright 2021 Planar Systems, Inc. All rights reserved