

ThinkVision E22-20 62A4MAR4US

Product

ThinkVision E22-20

Machine Type

62A4

Region

NA, LA

Display Size

21.5"

View Area

476.06x267.79 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.248x0.248 mm

Dot / Pixel Per Inch

102 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

14ms

Refresh Rate

60 Hz

Brightness

250 nits

Contrast Ratio

1000:1

Color Gamut

72% NTSC

Multiple Input

HDMI, DP, VGA

USB Port

None

Camera

None

Speaker

2x 1.5w

Power Consumption (Typical / Maximum)

18W / 24W

Power Adapter

Integrated

Stand

Tilt, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

15 mm

Dimensions with Stand (HxWxD)

443.4x508.0x178.6 mm

Weight (Including Stand)

8.6lbs / 3.9kg

Monitor Cable

HDMI

ENERGY STAR

Yes

TCO

TCO 8.0

EPEAT

Silver

Low Blue Light / Eye Comfort

Eye Comfort

Base Warranty

3-year

Operating System

Support Windows 7, Windows 10

Presets / User Settings

26 / 25

On Screen Display

OSD, 8 Languages

Sync Technology

None

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Announce Date

2020-06-17



WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



ThinkVision E22-20



DISPLAY	Dynamic Contrast Ratio (typical) 3M:1	ENERGY STAR Power Consumption (P_{on}/E_{TEC}) 11.24W / 35.64kWh	DIMENSION	CERTIFICATION
Panel Size 21.5-inch	Color Gamut 72% NTSC (CIE 1931)	Power Supply Internal	Size Packed (D x H x W, mm/inch) 131.0 x 405.0 x 610.0 mm 5.16 x 15.94 x 24.02 inches	ENERGY STAR Certification Yes
Screen Dimensions 476.06 mm x 267.79 mm	Color Support (typical) 16.7 Million	Voltage Required AC 90 to 264 V (47-63 Hz)	Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position) 178.6 x 301.6 x 508.0 mm 7.03 x 11.87 x 20.00 inches	CCC Yes
Panel Type In-Plane Switching	Color Depth 8-bit		MECHANICAL	TCO 8.0
Backlight WLED	Anti-glare Yes	Tilt Angle (front/back) -5° / 22°	Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position) 178.6 x 443.4 x 508.0 mm 7.03 x 17.46 x 20.00 inches	TCO Edge 2.0
Aspect Ratio 16:9		Lift (max range) 155 mm	Size Unpacked w/o Stand (head only) (D x H x W, mm/inch) 43.4 x 307.9 x 508.0 mm 1.71 x 12.12 x 20.00 inches	EPEAT Silver
Resolution 1920 x 1080		Pivot -90° / 90°	Weight Packed (kg/lbs.) 5.40 kg / 11.90 lbs.	RoHS (2011/65/EU) Yes
Pixel Pitch 0.2480 x 0.2480 mm			Weight Unpacked (kg/lbs.) 3.90 kg / 8.60 lbs.	Windows Certification Windows 7, Windows 10
Dot/Pixel Per Inch (DPI/PPI) 102		VESA Mount Capability Yes (100 x 100 mm)	Weight (Monitor Head Only) (kg/lbs.) 2.20 kg / 4.85 lbs.	China Energy Efficiency Standard Tier 1
Viewing angle (H x V @ CR 10:1) 178° / 178°		Kensington Lock Slot Yes		TÜV Rheinland Eye Comfort Yes
Response Time 14ms	Integrated Speakers Yes (2 x 1.5W)	Bezel Color Raven Black		
Refresh Rate 60 Hz		Bezel Width (side) 15 mm		
Brightness (typical) 250 cd/m ²	Power Consumption (typ./max) 18W / 24W	Bezel Width (top/bottom) 17.25 / 21.15 mm		
Contrast Ratio (typical) 1000:1	Power Consumption Sleep/Off Mode < 0.5W			
	Power Consumption Switch Off-Mode < 0.5W			
			WHAT'S IN THE BOX	
			Monitor with stand 1 x Power cable (1.8 m) 1 x HDMI cable (1.8 m) Quick setup guide	



Depends on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments.

© 2020 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

ThinkVision E22-20

Lenovo

