



# **Highlights**

- Storage built to Western Digital's high standards of quality and reliability
- Manufactured with Western Digital's awardwinning desktop and mobile hard drive technology
- · Available in a broad range of capacities1
- Tested in our F.I.T. Lab<sup>™</sup> for ultimate compatibility
- Free Acronis<sup>™</sup> True Image<sup>™</sup> WD Edition software available for download

# WD™ Blue 2.5-inch PC HDD

# Western Digital Quality

Built to the high standards of quality and reliability of the WD brand, these drives offer the features and capacity ideal for everyday computing needs.

### The Original

WD Blue 2.5-inch PC Hard Drives are designed and manufactured with the proven technology found in WD's original award-winning hard drives.

### Compatible

Our latest generation of 7 mm 2.5-inch mobile drives is designed for thin and light mobile applications, and is also compatible with most standard 9.5 mm bays.

### SATA 6 Gb/s Interface

Safely positions the recording head off the disk surface to protect your data.

# **Low Power Consumption**

State-of-the-art seeking algorithms and advanced power management features help ensure low power consumption.

## Quiet

In a notebook drive, silence is golden. Western Digital's exclusive noise reducing technologies yield some of the quietest 2.5-inch hard drives on the market.

# **Upgrading Your Drive is Easy**

Acronis™ True Image™ Western Digital Edition software is available as a free download on the Western Digital Support site enabling you to copy all your data to a new drive. You don't have to reinstall your operating system to get all the benefits of a new drive.

PRODUCT BRIEF 2.5-INCH PC HARD DRIVES

# **Specifications**

	2TB	1TB	500GB	320GB	320GB
Model Number <sup>1</sup>	WD20SPZX	WD10SPZX	WD5000LPZX	WD3200LPCX	WD3200LPVX
Recording Technology <sup>2</sup>	SMR	SMR	SMR	CMR	CMR
Formatted capacity <sup>3</sup>	2TB	1TB	500GB	320GB	320GB
Form factor	2.5-inch	2.5-inch	2.5-inch	2.5-inch	2.5-inch
Advanced Format (AF)	Yes	Yes	Yes	Yes	Yes
RoHS compliant <sup>4</sup>	Yes	Yes	Yes	Yes	Yes
Performance					
Interface transfer rate (max) <sup>5</sup> Buffer to host	6 Gb/s				
Host to/from drive (sustained)	149 MB/s (max.)	150 MB/s (max.)	150 MB/s (max.)	147 MB/s (max.)	147 MB/s (max.)
Cache (MB)	128	128	128	16	8
Performance Class	5400 RPM				
Reliability/Data Integrity					
Load/unload cycles <sup>6</sup>	600,000	600,000	600,000	600,000	600,000
Non-recoverable read errors per bits read	<1 in 10 <sup>14</sup>				
Limited warranty (years) <sup>7</sup>	2	2	2	2	2
Power Management <sup>8</sup>					
Average power requirements (W)					
Read/Write	1.7	1.5	1.5	1.4	1.4
Idle	0.5	0.5	0.5	0.55	0.55
Standby and Sleep	0.1	0.1	0.1	0.16	0.13
Environmental Specifications					
Temperature (°C)					
Operating	0 to 60				
Non-operating	-40 to 65				
Acoustics (dBA)					
Idle	23	19	19	17	17
Seek (average)	24	21	21	22	22
Physical Dimensions					
Height (in./mm, max)	0.28/7.0	0.28/7.0	0.28/7.0	0.27/6.8	0.27/6.8
Length (in./mm, max)	3.94/100.20	3.94/100.20	3.94/100.20	3.94/100.20	3.94/100.20
Width (in./mm, ± .01 in.)	2.75/69.85	2.75/69.85	2.75/69.85	2.75/69.85	2.75/69.85
Weight (lb/kg, ± 10%)	0.20/0.09	0.20/0.09	0.20/0.09	0.20/0.09	0.20/0.09

<sup>1</sup> Not all products may be available in all regions of the world.

## Western Digital.

 $<sup>^{\</sup>rm 2}$  Implementation of SMR for the following products using SMR recording technology is device-managed SMR.

<sup>&</sup>lt;sup>3</sup> As used for storage capacity, one gigabyte (GB) = one billion bytes and one terabyte (TB) = one trillion bytes. Total accessible capacity varies depending on operating environment.

<sup>&</sup>lt;sup>4</sup> This drive is in compliance with the European Union Directive 2011/65/EU and Directive (EU) 2015/863 on the restriction of the use of certain hazardous substances (RoHS) in electrical and electronic equipment.

<sup>5 1</sup> MB/s = 1 million bytes per second. Based on internal testing; performance may vary depending upon host device, usage conditions, drive capacity, and other factors.

<sup>6</sup> Controlled unload at ambient condition.

<sup>&</sup>lt;sup>7</sup> The term of the limited warranty depends on the country in which the Product was purchased. Visit our website at http://support.wdc.com/warranty/policy.asp for the detailed terms and conditions of our limited warranty and for a list of the specific countries in these regions.

<sup>8</sup> Power measurements at room-ambient temperature