




SPECIFICATIONS

Model Name	GeForce RTX™ 3060 Ti VENTUS 3X
Graphics Processing Unit	NVIDIA® GeForce RTX™ 3060 Ti
Interface	PCI Express® Gen 4
Core Clocks	Boost: 1665 MHz
CUDA® CORES	4864
Memory Speed	14 Gbps
Memory	8GB GDDR6
Memory Bus	256-bit
Output	DisplayPort x 3 (v1.4a) HDMI x 1 (Supports 4K@120Hz as specified in HDMI 2.1)
HDCP Support	Y
Power consumption	200W
Power connectors	8-pin x 1
Recommended PSU	600W
Card Dimension (mm)	305 x 120 x 42 mm
Weight (Card / Package)	760g / 1233g
DirectX Version Support	12 API
OpenGL Version Support	4.6
Maximum Displays	4
VR Ready	Y
G-SYNC® technology	Y
Adaptive Vertical Sync	Y
Digital Maximum Resolution	7680 x 4320

CONNECTIONS



1. DisplayPort
2. HDMI

FEATURES




Triple Fan

Three fans and a huge heatsink ensure a cool and quiet experience for you.



TORX FAN 3.0

The award-winning MSI TORX Fan 3.0 design creates high static pressure and pushes the limits of thermal performance.



Thermal Padding

An abundance of thermal pads use any chance for additional heat transfer directly from the components.



Custom PCB

The custom PCB has been engineered with hardened circuits and optimized trace routing for performance and reliability.




Dragon Center

MSI's exclusive Dragon Center software lets you monitor, tweak and optimize MSI products in real-time.



Afterburner

Take full control with the most recognized and widely used graphics card overclocking software in the world.



Zero Frozr

The fans completely stop when temperatures are relatively low, eliminating all noise.