







Medical Grade Barcode Scanner for Healthcare

The D755 is a Bluetooth barcode scanner designed and built for health care environments. The D755 is built with medical grade plastic to withstand daily cleaning and harsh disinfectant solutions to help prevent the spread of germs. Its environmental seal is IP54 rated to protect the unit from dust, water, blood, alcohol and bacteria. Its durable design was built to be dropped hundreds of times. The scan button was tested to handle over five million presses in environments needing frequent scanning. The D755 scans small barcodes such as the ones used on vials and syringes. It scans barcodes displayed on a screen or printed, on curved and reflective surfaces.

It is Apple Certified and can be fully integrated and controlled by your iOS or Android application.

The D755 is small and light enough to always be carried, and it is ergonomically designed to fit perfectly in your hand. It can slip in your pocket or be worn with a wrist strap or holster. The Bluetooth wireless technology allows freedom of movement all workday, with battery friendly technology lasting an entire 12-hour shift.

From patient admissions, to bedside point of care, to the pharmacy, the D755 is a perfect solution for applications that are used in hospitals, blood banks, pharmacies, residential care facilities and home care organizations.
















Patient Tracking




Features

- Medical Grade Housing IP54 sealing and designed to resist the harmful effects of harsh cleaning agents. Allows safe wipe-down with a wide variety of harsh chemicals to help prevent the spread of germs.
- Scanning High-performance 1D, 2D and PDF 417 barcode scanning with safe LED aimer. Scans omni-directional, allowing intuitive rapid scanning.
- **Certified by Apple® for iOS devices –** Guaranteed Compatibility.
- Native App Support Socket Mobile's Capture SDK enables easy native app integration in your applications to improve business productivity.
- **Exceptional Ergonomics** Small, light and fits perfectly in the hand for comfortable use over extended periods of
- User Feedback Audible tones and hand pulsation. Set the scanner hand pulsation only when you do not want to disturb others with scanning sounds.
- **User Indicators** Intuitive LEDs, Bluetooth connection, battery level and scanning status.
- **Long-Lasting, Replaceable, Rechargeable Battery -** Designed to last over an entire busy 12-hour shift, with an LED indicator that alerts the user when a battery charge is needed.
- **Rugged Design -** withstands 2,500 drops to Linoleum from 5' and 5,000,000 scan presses.
- Bluetooth Wireless Technology Dependable Bluetooth connection to iOS, Android and Windows 10 devices. Auto-reconnection maintains connection even in different environments.
- Wearable Wrist strap included. Optional: Holster and Durable Retractable Clip available.
- Designed and Made in the USA.
- 1-Year Warranty.
- **Extended Warranty -** Our optional flexible service plans keeps your scanner up and running in like-new condition with coverage for accidental damage and everyday wear-and-tear.

PHYSICAL CHARACTERISTICS





SINGLE PACKAGE INCLUDES

- (1) DuraScan D755, 2D/1D Barcode Imager
- (1) Charging Cable
- (1) Wrist Strap
- (1) Get Started Insert









Socket Mobile Companion Download for Free!

Scanner (SKU# CX3799-2559)
Scanner w/ Charging Cradle (SKU# CX3558-2882)

The D755 is available in 2 packages:

OPTIONAL ACCESSORIES



Default Barcode Symbologies: **1D Symbologies:** Codabar, Code 39, Code 93, Code 128, EAN-13/JAN, EAN-8/JAN, GS1 Databar, GS1 Databar Expanded, GS1 Databar Limited, GS1-128, Interleaved 2 of 5, ISBT 128, UPC A, UPC EO

2D Symbologies: Aztec, Data Matrix, Maxicode, Micro PDF417, PDF417

Postal Codes: Australia Post

Supported Barcode Symbologies:

1D Symbologies: Bookland EAN, Chinese 2 of 5, Codabar, Code 11, Code 39, Code 93, Code 128, Composite CC-A/B, Composite CC-C, Composite TLC, Discrete 2 of 5, EAN-13/JAN, EAN-8/JAN, GS1 Databar, GS1 Databar Expanded, GS1 Databar Limited, GS1-128, Interleaved 2 of 5, ISBT 128, ISSN EAN, Matrix 2 of 5, MSI, UPC/EAN/JAN, UPC A, UPC EO

2D Symbologies: Aztec, Data Matrix, Maxicode, Micro PDF417, MicroQR, PDF417, QR Code **Postal Codes:** Australia Post, Han Xin, Japan Postal, KIX Code, Maxicode, Netherlands, UPU FICS Posta, US Planet, US Postnet, USPS 4CB/One Code/Intelligent Mail


48° (Horizontal) - 30° (Vertical)

Sensor Resolution: 1280 horizontal x 800 vertical pixels

Print Contrast: Down to 25%-20%

Reading Distance:

Scan Angle:



4.1 to 91.7 cm (1.6 to 35.1 in.) Depends on barcode size, symbology, label media

Decode Ranges:

	Near	Far
3 mil Code 39	3.0 in/5.8 cm	7.6 in/14.7 cm
5 mil Code 128	2.3 in/5.8 cm	9.8 in/24.9 cm
5 mil PDF 417	3.0 in/7.6 cm	7.9 in/20.1 cm
6.67 mil PDF 417	2.5 in/6.3 cm	10.1 in/25.7 cm
10 mil DataMatrix	2.1 in. / 5.3 cm	11.0 in. / 27.8 cm
100% UPC A	1.6 in/4.1 cm*	24.9 in/63.2 cm
15 mil Code 128	2.4 in. / 6.1 cm	27.8 in. / 70.6 cm
20 mil Code 39	1.6 in/4.1 cm*	36.1 in/91.7 cm
20 mil QR Code	1.1 in. / 2.8cm	17.5 in. / 44.5 cm

Battery Type: Replaceable 1400 mAh Lithium - Ion Battery

Charge Time: 6 Hours

Battery Life - Standby time: over 20 hours

Per Full Charge: Active Scan Time: 85,000 scans within 9 hours (based on 2 scans every 1 second)

17,000 scans within 19 hours (based on 1 scan every 4 seconds)

Note: Battery life varies depending on ambient temperature, ambient light and age of battery.

For more battery information <u>click here</u>.

Number of Batteries Used: 1 Weight of Battery: 35g

Percentage Lithium: 26.5%
Battery mAh: 1400 mAh

Number of Cells Per Battery: 1

Watt Hours Per Battery: 5.55

Type of Cell (ex. AA): Proprietary

Chemical Composition

(ex. Alkaline):

Lithium-polymer

Lithium Content: 9.32g Battery Voltage: 3.7v

Hazmat UN Number: UN3481, P.I. 967

ROHS Compliance Indicator: Yes, included with scanner

Battery Country of Origin: China

Commodity Code: 8507.60.0000

BLUETOOTH (WIRELESS CONNECTION)

Bluetooth Radio: Class 2 Bluetooth, version 2.1 + EDR (Enhanced Data Rates) with 56-bit data encryption

Bluetooth Range: Up to 10 meters (33 ft.) depending on environment, range limit is usually due to the Host Device

(phone, tablet or notebook)

Bluetooth Profiles: Basic Mode - Human Interface Device (HID)*, Application Mode - Serial Port Profile (SPP) and

Application Mode - MFi-SPP. Some Operating Systems or smartphone/tablet models may support

only one profile.

*By default, the scanner is set to Basic Mode (HID).

SCANNER TYPE

Technology: 2D/1D Barcode Imager

Light Source: one (1) warm-white LED

Aimer: 525 nm green LED

USER ENVIRONMENT

Ambient Light: From 0 to 100 000 lux, From pitch black to direct sun light

Operating 0° to 45° C (32° to 113° F)

Temperature:

Storage Temperature:

-5° to 70° C (-22° to 158° F)

Relative Humidity: 95% at 60° C (140° F) (non-condensing)

Sealing: IP54 (Ingress Protection rating for dust and water) EN60529

Drop Specifications: 6 drops to concrete - 1 on each side at 6.6 ft. (2 m)

Tumble Specifications: 2,500 cycles at 3.3 ft. (1 m) to metal plate, IEC6008-2-31, IEC60068-2-32 3)

OPERATING SYSTEM COMPATIBILITY

Android OS - Basic Mode (HID)* & Application Mode

Mac OS and Linux - Basic Mode (HID)* only

Apple iOS - Basic Mode (HID)* & Application Mode (MFi-SPP)

Windows OS - 10, 8, and 7 - Basic Mode (HID)* & Application Mode (SPP)

Compatible with devices supporting Basic Mode (HID)* protocol. Supported keyboard languages - ANSI, English UK, English, French, German, Italian, Japanese, Polish, Spanish and Swedish

*By default, the factory settings of the Socket Mobile Scanners are set to Basic Mode (keyboard emulation: HID). In order to use the scanner with an application using Capture SDK, the scanner must be configured in Application Mode (Bluetooth Serial Port Profile: SPP)

Certified by Apple for iOS devices (iPad, iPhone, iPod Touch) and compatible with Android and Windows.











CERTIFICATION & REGULATORY

Bluetooth SIG: Declaration ID: D030473 OD ID: 82009

Electrical Safety: Certified to IEC 60950-1, UL 60950-1, CAN/CSA C22.2

Environmental: Environmental: RoHS EN 50581

EMI / RFI: FCC Part 15 Class C, RSS 210, iCES 003, C-Tick, CISPR 22, CE EN55022, EN55024, TELEC

> FCC ID: T9J-RN41-3 IC ID: 6514A-RN413 Telec ID: **R** 201-135280

LED Safety: IEC 62471, EN 62471 (EXEMPT GROUP)



















WARRANTY

Standard one year limited warranty Scanner:

Accessories: 90 days (batteries, charging cable, wrist strap)

Extended Warranty: www.socketmobile.com/socketcare

(sold separately)



Admitting / Discharge	Specimen Collection / Tracking	Patient ID Wristbands
Medication Administration	Pharmacy Inventory	Document Tracking
Retail/Point of Sale	Warehouse management	Transportation
Office use	Shipping & Receiving	Mobile Tracking
Healthcare	Field Sales/Service	Inventory

+8190 9808 0518

Switzerland Toll-Free:

© 2020 Socket Mobile, Inc. All rights reserved. Socket®, the Socket Mobile logo, DuraScan®, DuraScan®, Battery Friendly® are registered trademarks or trademarks of Socket Mobile, Inc. Microsoft® is a registered trademark of Microsoft Corporation in the United States and other countries. Apple®, iPad®, iPad Mini®, iPhone®, iPod Touch®, and Mac iOS® are registered trademarks of Apple, Inc., registered in the U.S. and other countries. The Bluetooth® Technology word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by Socket Mobile, Inc. is under license. Other trademarks and trade names are those of their respective owners.