

## PERFORMANCE

### Processor

Intel® Core™ i5-1135G7 (4C / 8T, 2.4 / 4.2GHz, 8MB)

### Graphics

Integrated Intel Iris® Xe Graphics functions as UHD Graphics

### Chipset

Intel SoC Platform

### Memory

1x 8GB SO-DIMM DDR4-3200

### Memory Slots

One DDR4 SO-DIMM slot

### Max Memory

Up to 32GB DDR4-3200

### Storage

256GB SSD M.2 2242 PCIe® 3.0x4 NVMe®

### Storage Support

Up to two drives, 2x M.2 SSD

- M.2 2242 SSD up to 512GB
- M.2 2280 SSD up to 1TB

### Card Reader

No card reader

### Optical

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

### Speakers

Stereo speakers, 2W x2, Dolby® Audio™, Harman Speakers

### Camera

720p with Privacy Shutter

### Microphone

2x, Array

### Battery

Integrated 45Wh

### Max Battery Life

MobileMark® 2014: 11.9 hr

MobileMark 2018: 8.7 hr

### Power Adapter

65W USB-C (2-pin)

## DESIGN

### Display

14" FHD (1920x1080) IPS 250nits Anti-glare

### Touchscreen

None

### Keyboard

Backlit, English

### Case Color

Black

### Case Material

Aluminium (Top), Aluminium (Bottom)

### Dimensions (WxDxH)

324 x 220 x 17.9 mm (12.76 x 8.66 x 0.7 inches)

### Weight

1.64 kg (3.62 lbs)

## SOFTWARE

### Operating System

Windows® 10 Pro 64, English

### Bundled Software

None

## CONNECTIVITY

### Ethernet

100/1000M

### WLAN + Bluetooth®

Intel AX201 11ax, 2x2 + BT5.2

### WWAN

None

### SIM Card

None

### NFC

None

### Standard Ports

- 1x USB 2.0
- 1x USB 3.2 Gen 1 (Always On)
- 1x Thunderbolt™ 4 / USB4™ 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)
- 1x HDMI® 1.4b
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)

### Docking

Various docking solutions supported via Thunderbolt.

For more compatible docking solutions, please visit [Docking for ThinkPad® E14 Gen 2 \(Intel\)](#)

### Monitor Cable

None

## SECURITY & PRIVACY

### Smart Card Reader

None

### Security Chip

Discrete TPM 2.0

### Fingerprint Reader

Touch Style

### Physical Locks

Kensington® Security Slot

### Other Security

Camera privacy shutter

## MANAGEABILITY

### System Management

Non-vPro

## SERVICE

### Base Warranty

1-year, Depot

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications

- EPEAT™ Gold
- ENERGY STAR® 8.0
- ErP Lot 3
- TCO Certified
- RoHS compliant

### Other Certifications

TÜV Rheinland® Low Blue Light

### Mil-Spec Test

MIL-STD-810H military test passed

## MODEL

TopSeller : Yes

Announce Date : 2020-11-10

EAN / UPC / JAN : 195348604499

End of Support : 2027-06-10

· Lenovo reserves the right to change specifications or other product information without notice.

· Battery life is an estimated maximum. Actual battery life may vary by hardware or system settings, active applications, battery conditioning, etc.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad Thunderbolt 3 Dock Gen 2 - US

40AN0135US

Lenovo understands that modern business depends on a wide variety of notebooks and devices from different brands working seamlessly together to meet business needs. To deliver this experience, ThinkPad Thunderbolt 3 D...

## Recommended Services

BEST	4Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection) (5PSON73132)
BETTER	3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection) (5PSON73156)
GOOD	3Y Lenovo Support (Premier Support + Keep Your Drive) (5PSON73153)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference