


## 3.2–3.8kW 200–240V Single-Phase Metered PDU - 16 C13 & 4 C19 Outlets, C20/L6-20P Input, 10-ft. (3.05 m) Cord, 40 in. 0U Rack

MODEL NUMBER: PDUMV20HV-36



Single-phase PDU allows real-time current metering to prevent circuit overloads that could cause costly downtime as additional equipment is connected.

### Features

#### Single-Phase PDU Distributes and Monitors Network-Grade Power in Real Time

This metered PDU provides real-time local reporting of the total load level via its built-in digital current metering. Ideal for network IT applications, small computer rooms and other equipment rack applications, the PDUMV20HV-36 features 16 C13 and four C19 200–240V outlets for connecting equipment. Plug-lock insert sleeves are included to prevent connected cables from becoming accidentally dislodged. The switchless design helps prevent an accidental shutdown, which could lead to costly downtime.

#### Digital Load Meter Helps Prevent Potentially Expensive Overloads

A digital ammeter reports the total load for all connected equipment. Monitoring amperage helps ensure load levels remain well below maximum capacity with no danger of overload that could lead to costly downtime or damaged equipment. Maintaining proper load levels, even while adding new equipment, can keep your TCO (total cost of ownership) low.

#### Versatile Installation Options Give You Plenty of Choices

The 40-inch 0U PDU mounts vertically in an EIA-standard 19-inch rack using the included toolless mounting buttons or the included mounting brackets with user-supplied hardware. You may also use the brackets to secure the PDU to the underside of a counter with the addition of two user-supplied screws. Bolt-down retention brackets keep power cords organized and your rack free of clutter.

#### Compatible with a Variety of Input Cords to Fit Your Facility's Power Source

The PDU's C20 inlet accepts a variety of 16A international cordsets. An included 10-ft. (3.05 m) cord with NEMA L6-20P input plug connects to an AC power source, generator or protected UPS system to distribute power to connected loads.

### Highlights

- 16 C13 and 4 C19 200–240V outlets distribute AC power to connected equipment
- Digital ammeter for on-site real-time load monitoring helps prevent power overloads
- Switchless design helps prevent accidental shutdowns that can lead to costly downtime
- 10-ft. (3.05 m) detachable cord with L6-20P single-phase input connects to AC power source
- 40 in. 0U PDU with included mounting brackets installs in rack or under counter

### Applications

- Deliver network-grade power to high-density equipment in networking, telecom, security, audio/video and sound reinforcement applications
- Monitor power load in real time from all connected computers, switches, servers and other networking equipment

### Package Includes

- PDUMV20HV-36 3.2–3.8kW Single-Phase Metered PDU
- (20) Plug-lock insert sleeves
- C19 to L6-20P input cord, 10-ft. (3.05 m)
- Rack-mounting hardware
- Owner's manual

## Specifications



<b>OVERVIEW</b>	
UPC Code	037332255921
PDU Type	Metered
<b>INPUT</b>	
PDU Input Voltage	200; 208; 220; 230; 240
Recommended Electrical Service	20A 208/240V; 16A 230V
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
Input Connection Type	L6-20P detachable cordset, C20 inlet available
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Phase	Single-Phase
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
<b>OUTPUT</b>	
Output Capacity Details	3.84kW (240V), 3.68kW (230V), 3.52kW (220V), 3.33kW (208V), 3.2kW (200V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(16) C13; (4) C19
Output Nominal Voltage	200; 208; 220; 230; 240
Overload Protection	n/a
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Digital meter reports PDU output current in amps
Switches	n/a
<b>PHYSICAL</b>	
Form Factors Supported	0u vertical installation in equipment racks, plus under-counter and wallmount
Material of Construction	Aluminum
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	5.00 x 3.50 x 41.50
Shipping Weight (kg)	4.31
Unit Dimensions (hwd / cm)	101 x 5.7 x 9.5
Unit Dimensions (hwd / in.)	39.75 x 2.25 x 3.75
Unit Weight (kg)	2.36
Unit Weight (lbs.)	5.20



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>ENVIRONMENTAL</b>	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	0-95% non-condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to UL60950-1 (USA), CAN/CSA (Canada), NOM (Mexico), CE; Series Number (s) AGPD6674; Safety Standards (Canada); CAN/CSA-C22.2 No. 60950-1:2007 (2nd Ed) +A1:2011 +A2:2014; Safety Standards (U.S.) UL60950-1:2007 (2nd Ed)+A1 R10.14; Safety Standards (International) IEC60950-1:2005 (2nd Ed)+A1:2009+A2:2013
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>