


4-Port USB PCIe Card - 10Gbps USB 3.2 Gen 2 Type-A PCI Express Expansion Card with 2 Controllers - 4x USB-A - USB PCIe Add-On Adapter Card - Windows/Mac/Linux

Product ID: PEXUSB314A2V2



This PCIe USB 3.2 Gen 2 controller card installs into an available PCI-Express x4 slot in your computer and enables you to upgrade your current system by adding four SuperSpeed USB-A (10Gbps) ports. The card features dual ASM3142 controllers with up to 20 Gbps of total bandwidth shared across all 4 ports.

The controller card enables you to connect four USB-A Gen 2 (10 Gbps) devices to your desktop computer. The USB-A ports are ideal for connecting USB devices such as external hard drives and solid state drives or powering and syncing your mobile devices. The USB-A ports provides up to 4.5W (5V/0.9A) of power per USB port, and are backward compatible with USB 3.2 Gen 1 (5 Gbps), and USB 2.0 (480 Mbsp) devices.

Note: USB 3.2 Gen 2 (10 Gbps) is also known as USB 3.2 Gen 2 (10 Gbps), and USB 3.2 Gen 1 (5 Gbps) is also known as USB 3.2 Gen 1 and USB 3.2 (5 Gbps).

The USB 3.2 Gen 2 card features dual ASMedia ASM3142 host controllers that utilize x4 lanes of the PCIe 2.0 bus, making the card capable of speeds up to 10 Gbps on each port, and enabling fast access to high-performance devices like NVMe drives and SSDs. The controller cards support Multiple INs to reduce bandwidth loss when multiple devices are connected, even when connected through a USB Hub (Note: The USB hub must also support this feature). The card also supports UASP for improved performance with storage devices.

This add-on card includes a full-profile installation bracket ensuring you can install it into full-profile PCIe 2.0 x4 slots. For wide platform support the card is compatible with Windows, Linux and macOS. For hassle-free installation the drivers install automatically on computers running Windows 8 or higher. Works w/USB 3.2/3.0/2.0 devices

PEXUSB314A2V2 is backed by a StarTech.com lifetime warranty and free 24/5 multi-lingual North American based technical support. StarTech.com has been the IT professionals' choice for over 30 years.

Certifications, Reports and Compatibility



Applications

- Connect high-performance devices like NVMe drives and SSDs

Features

- **HIGH PERFORMANCE:** USB PCIe card with 4x USB-A ports up to SuperSpeed 10Gbps per port; Dual ASM3142 controllers with up to 20Gbps total bandwidth across 4 ports; USB 3.2 Gen 2; Upgraded version of our popular USB card PEXUSB314A2V
- **MAXIMIZED USB PERFORMANCE:** Multiple INs support for max bandwidth when using mixed-speed devices; USB Attached SCSI Protocol (UASP) for storage device, like SSDs, HDDs, NVMe drives and thumb drives
- **POWER:** USB PCIe expansion card with SATA power header has the option to provide supplemental power to the USB ports (if motherboard power is insufficient) providing up to 4.5W (5V@0.9A) per USB-A port
- **COMPATIBILITY:** USB PCIe adapter card for desktop PC installs in standard profile PCI-e 2.0 x4 slot; Supports Windows/Linux/macOS with auto driver install on Windows 8 & up; Works w/USB 3.2 Gen 1/2.0 devices
- **STARTECH.COM ADVANTAGE:** IT professionals' choice for over 30 years; This USB-A PCIe add-on card is backed for life by StarTech.com, including free 24/5 North America based multi-lingual tech support

Hardware

Warranty	Lifetime
Ports	4
Interface	PCI Express
Bus Type	USB 3.2 Gen 2 10Gbps
Card Type	Standard Profile
Port Style	Integrated on Card

Industry Standards USB 3.1 Specification Rev. 1.0USB Specification Rev. 2.0PCI Express Base Specification Rev. 2.0Intel xHCI Specification Rev. 1.1UASP (USB Attached SCSI Protocol) Rev. 1.0

Chipset ID ASMedia - ASM3142

ASMedia - ASM1812

Performance

Total USB Power Output 4.5W (5V @ 0.9A) nominal, per port - Ports trip before 2.1A (10.5W) for Over-Current Protection

Maximum Data Transfer Rate 10Gbps per port

Type and Rate USB 3.2 Gen 2 - 10 Gbit/s

UASP Support Yes

MTBF 40,000 Hours

Connector(s)

Connector Type(s) 1 - PCI Express x4

Internal Ports 1 - SATA Power (15 pin)

External Ports 4 - USB 3.2 Type-A (9 pin, Gen 2, 10Gbps)

Software

OS Compatibility Windows 7, 8, 8.1, 10, 11
 Windows Server 2012 R2, 2016, 2019, 2022
 macOS 10.13 to 10.15, 11.0, 12.0, 13.0
 Linux 3.5 and up - <i>LTS Versions only</i>

Special Notes / Requirements

System and Cable Requirements PCI Express enabled computer or server with a PCI Express x4 slot or higher (x8, x16)
 Optional SATA power connector

Note This card can share up to 20Gbps of bandwidth (up to 10Gbps, per port). However, the maximum throughput of the card is limited by the maximum throughput of the PCI-Express interface it's connected through
 The available bandwidth (10Gbps) is shared equally between the two ports.

Environmental

Operating Temperature	5C to 50C (41F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	20% ~ 80% RH

Physical Characteristics

Color	Black
Product Length	4.7 in [12.0 cm]
Product Width	5.9 in [15.0 cm]
Product Height	0.7 in [1.9 cm]
Weight of Product	4.4 oz [125.0 g]

Packaging Information

Package Quantity	1
Package Length	5.7 in [14.4 cm]
Package Width	8.1 in [20.7 cm]
Package Height	1.5 in [3.8 cm]
Shipping (Package) Weight	6.4 oz [180.0 g]

What's in the Box

Included in Package	1 - USB 3.1 Card
	1 - Quick-Start Guide
	1 - Full Profile Bracket (Installed)

***Product appearance and specifications are subject to change without notice.**