

Everyday scanning made easy

One-button simplicity

The beautifully simple iX1400 will digitize, process, and organize all your documents from one easy device. You don't need to know IT. You just need to press the blue button.

With no complex settings to configure, the iX1400 is up and running from the box in record time. Its one-touch scanning turns time-consuming chores into simple tasks at the push of a button. Just scan, save, and share.



Form and function

Designed by the world's leading scanner manufacturer, the iX1400 is compact and stylish enough to fit into most workspaces and can be by your side, wherever work takes you.

Using the ScanSnap Home software, simply and efficiently, create the type of files you want—searchable PDFs, and editable Word, Excel, and PowerPoint files. Extract data from receipts and business cards. Save them all to the places you want. And count on powerful search and retrieval of your scans.

The scanning experience you'll love

Out of the box, ready in minutes

The iX1400 is so easy to set up, anyone can do it. Just unbox, set up in minutes, and press the blue button to start enjoying one-touch scanning. Once setup is done, simply open the lid and the scanner powers up—it's ready to go.

Powerfully fast

Scan up to 50 sheets of single- or double-sided documents at a quick 40 sheets per minute. The two-sided (duplex) scanning feature will have you digitizing paperwork in half the time.



Quick Menu for instant file creation


The Quick Menu function allows you to instantly scan straight into the applications you know and use—and you can add more applications any time. Some other things Quick Menu lets you do:



- Scan images directly to a folder, email, or even a printer.
- Extract data from receipts and business cards into CSV files.
- Export scans to your favorite cloud storage locations.
- Create searchable PDFs, or instantly open your scan as a fully editable file in Word, Excel, or PowerPoint.

Industry-leading reliability

Using professional grade feeding technology and ultrasonic sensors, the iX1400 handles multi-page documents with ease. And you can set an alert to tell you if two or more pages are fed through the scanner at once—to make sure no page gets lost.



Instant, secure connection

No one wants to spend time on installation. The fuss-free USB 3.2 connector plugs straight into your computer.

Total document management



ScanSnap Home makes paperwork effortless


This all-in-one software brings together all your favorite functions to help you power through your scanning in no time. Easily manage, edit, and utilize scanned data from documents, receipts, business cards, photos, and more.



Documents are recognized and grouped by document type (receipts, photographs, business cards, etc.) and folders, tags, and keywords allow you to easily organize, search, and find information.

Automated Operation

A host of intelligent image processing functions are automatically done for you, so you can scan confidently without adjusting settings.



Compact, stylish, versatile

The sleek ScanSnap iX1400 fits right into a modern workspace, wherever you call your desk. The large ADF (Automatic Document Feeder) is perfect for A4-size documents and larger items that can be folded in half to scan.

Hassle-free receipt scanning

Effortlessly scan small documents (think receipts and business cards) with the Receipt Guide. It dramatically simplifies document loading and saves you time otherwise spent prepping and feeding.



Fujitsu industry-leading support keeps digital transformation projects on-time and on budget

- U.S. based support
- Specialized Teams
- Flexible service programs



Fujitsu Imaging Solutions provide superior engineering at the forefront of innovation through:

- Engineering Passion and Dedication
- Human Centric Design
- Worldwide Reliability

iX1400 Technical Specifications

Product name		iX1400
Scanner type		ADF (Automatic Document Feeder)/ Duplex
Scanning color mode		Color, Grayscale, Monochrome, Automatic (Color/Grayscale/Monochrome) ^{*1} (detection)
Image sensor		Color CIS x 2 (Front x 1, Back x 1)
Light source		3 Color LED (Red/Green/Blue)
Optical resolution		600 dpi
Scanning speed ^{*2} (A4 portrait)	Auto mode (Default) ^{*3}	Simplex/Duplex: 40 ppm
	Normal mode	Simplex/Duplex: 40 ppm (Color/Grayscale: 150 dpi, Monochrome: 300 dpi)
	Better mode	Simplex/Duplex: 40 ppm (Color/Grayscale: 200 dpi, Monochrome: 400 dpi)
	Best mode	Simplex/Duplex: 40 pp (Color/Grayscale: 300 dpi, Monochrome: 600 dpi)
	Excellent mode ^{*1}	Simplex/Duplex: 10 ppm (Color/Grayscale: 600 dpi, Monochrome: 1,200 dpi)
Document size	Normal scan ^{*4}	Minimum: 50.8 x 50.8 mm (2 x 2 in.) Maximum: 216 x 360 mm (8.5 x 14.17 in.)
	Manual scan	- ^{*4}
	Long paper scanning ^{*5}	3,000 mm (863 mm in 32-bit) ^{*6}
Paper weight (Thickness)		40 to 209 g/m ² (11 to 56 lb) A8 size or less: 128 to 209 g/m ² (34 to 56 lb) Cards: 0.76 mm or less (Compliant with the ISO7810 ID-1 type) (Includes embossed cards in landscape orientation)
ADF capacity ^{*7}		50 sheets (A4, 80 g/m ² or 20 lb)
Interface	USB	USB 3.2 Gen1x1 / USB 2.0 / USB 1.1 (Connector Type: Type-B) ^{*8}
Power requirement		AC 100 to 240 V, 50/60 Hz
Power consumption	Operating	17 W or less
	Sleep mode (USB connected)	1.5 W or less
Operation environment		Temperature: 5 to 35 °C (41 to 95 °F) Relative humidity: 20 to 80% (Non-condensing)
Dimensions (W x D x H) ^{*12}		292 x 161 x 152 mm (11.5 x 6.3 x 6.0 in.)
Device weight		3.2 kg (7.1 lb)
Environmental compliance		ENERGY STAR 3.0 [®] /RoHS
Multifeed detection		Overlap detection (Ultrasonic sensor), Length detection
Driver		ScanSnap Home (ScanSnap specific driver) • Windows [®] : Does not support TWAIN/ISIS [™] • macOS: Does not support TWAIN

¹ Available only when connecting to a computer. ² Scanning speeds may vary due to the system. ³ Scans will be made in "Best mode" if shorter sides are less than 105 mm and in "Better mode" if not. ⁴ A3 scans are possible with use of A3 carrier sheets. ⁵ Available in all modes except for "Excellent mode". ⁶ Indicated specifications apply when using ScanSnap Home. ⁷ Maximum capacity varies, depending upon paper weight. ⁸ Some computers do not recognize the ScanSnap when it is connected to a USB 3.2 Gen1x1/3.0 port. In this case, please use a USB 2.0 cable. ⁹ Availability of 5 GHz Wi-Fi may vary depending on region. ¹⁰ Access Point Connect Mode requires a Wi-Fi access point or router. ¹¹ 5 GHz Wi-Fi is not available with Direct Connect Mode. ¹² Excluding the stacker and other external attachments.

PFU Limited, a Fujitsu company, has determined that this product meets the ENERGY STAR[®] guidelines for energy efficiency. ENERGY STAR[®] is a registered trademark of the United States Environmental Protection Agency.

System Requirements

Windows^{*}

Operating systems		Windows ^{*10} (32-bit / 64-bit) ^{*1,2} Windows ^{*8.1} (32-bit / 64-bit) ^{*2} Windows ^{*7} (32-bit / 64-bit)
Hardware requirements ^{*3}	CPU ^{*4}	Intel [®] Celeron 1.8 GHz (2core) or higher (Recommended: Intel [®] Core [™] i5 2.5 GHz or higher)
	Memory capacity ^{*4}	2 GB or more (Recommended: 4 GB or more)
	Display resolution	1,024 x 768 pixels or more
	Disk capacity ^{*5,6}	3.8 GB or more of free hard disk space

^{*1} ScanSnap scanners do not run with Windows^{*10} ARM-based PCs. ^{*2} Operate Windows in desktop mode. ^{*3} The ScanSnap device may not work if the connected computer does not meet these requirements. ^{*4} Scanning speeds may drop if the recommended CPU, memory capacity and USB 1.1 requirements are not met. ^{*5} Indicated disk capacity requirements apply when downloading ScanSnap Home. ^{*6} .NET Framework 4.7 or later must be installed. If it is not installed, it is installed with ScanSnap Home. Up to 4.5 GB of disk space is required for the installation. *Please refer to the ScanSnap website for the latest support information of the driver and applications. Compatibility may differ depending on the software's version. *The system requirements may change depending on the support policies of the above system and third-party software.

Mac

Operating systems		macOS v10.12.4 or later
Hardware requirements ^{*1}	CPU ^{*2,3}	Intel [®] Core i5 1.4 GHz or higher (Recommended: Core i5 2.5 GHz or higher)
	Memory capacity ^{*3}	2 GB or more (Recommended: 8 GB or more)
	Display resolution	1,024 x 768 pixels or more
	Disk capacity	2.9 GB or more of free hard disk space

^{*1} The ScanSnap device may not work if the connected computer does not meet these requirements. ^{*2} The ScanSnap device also operates with Apple Silicon-based Mac computers. Please visit the ScanSnap website for latest support information. ^{*3} Scanning speeds may drop if the recommended CPU, memory capacity and USB 1.1 requirements are not met. *Compatibility may differ depending on software versions. Please visit the ScanSnap website for latest information on driver and application support. *The system requirements may change depending on the support policies of the above system and third-party software.

Software

Windows [*]	Mac
ScanSnap Home ^{*1}	
ScanSnap Manager ^{*2}	
Kofax Power PDF Standard ^{*3,4}	Kofax Power PDF Standard for Mac ^{*3,4}
ABBYY FineReader for ScanSnap [™]	

^{*1} ScanSnap Home installation requires a computer and Internet. Activation is also necessary for software use. Please visit the company website for download information. <https://scansnap.fujitsu.com/g-support/en>. ^{*2} ScanSnap Manager V7.1 and later is required. ^{*3} Please refer to the included license certificate to download the software. ^{*4} Kofax Power PDF is not included with the iX1400.

Service Program & Options

Service Program & Options		Part Number
ScanSnap Bag	Protects the scanner from dust and scratches	PA03951-0651
Document Carrier Sheet (5 pack)	Transparent sleeves for scanning A3, small or damaged documents	PA03360-0013
Photo Carrier Sheet (3 Pack)	Transparent sleeves for scanning photographs and postcards	PA03770-0015
Cleaning Wipes	ScanSnap cleaning wipes (24 pack)	PA03950-0419
ScanAid Consumable Kit	Includes 1x Pick Roller and 1x Brake Roller. Estimated Life up to 200K scans	CG01000-277701
Depot Mail-in Repair (iX1400)	3-year scanner contract provides mail-in unit repair that includes spare parts, labor, and one-way shipping to customer	SIX1400-DEPW5DY-3

Ready to start scanning?

To learn more, visit us at www.us.fujitsu.com/fcpa
Or contact us at (888) 425-8228

1250 East Arques Avenue, Sunnyvale, CA 94085

V12108DSIX1400M



©2021 Fujitsu Computer Products of America, Inc. Fujitsu and the Fujitsu logo are registered trademarks of Fujitsu Limited. All text, graphics, trademarks, logos contained herein related to Fujitsu, PFU, or Fujitsu Computer Products of America, Inc. ("FCPA") are owned, controlled or licensed by or to FCPA with all rights reserved. All other text, graphics, trademarks, service marks and logos used herein are the copyrights, trademarks, service marks or logos of their respective owners.