Think Vision M15 62CAUAR1US

Product

ThinkVision M15

Machine Type

62CA

Region

LA, NA

Display Size

15.6"

View Area

344.16x193.59 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.1793x0.1793 mm

Dot / Pixel Per Inch

141 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

6ms (Extreme Mode)/14ms (Normal Mode)

Refresh Rate

60 Hz

Brightness

250 nits

Contrast Ratio

1000:1

Color Gamut

45% NTSC

Anti-glare

Yes

Multiple Input

2 x USB 3.1 Type-C (DP1.2 Alt Mode)

USB Port

1 x USB 2.0 (1 by USB Type-C)

Camera

None

Microphone

None

Speaker

None

Power Consumption (Typical / Maximum)

8W / 9.5W

Power Adapter

External

Stand

Tilt, Height Adjust Stand

Color

Raven Black

Side Bezel Width

7.3 mm

Dimensions with Stand (HxWxD)

360.0x108.4x235.5 mm

Weight (Including Stand)

3.73lb / 1.69kg

Monitor Cable

USB Type-C to Type-C

ENERGY STAR

Yes

TCO

None

EPEAT

Silver

Low Blue Light / Eye Comfort / Eyesafe Display

Low Blue Light

Base Warrantv

3-year

Operating System Support

Support Windows 7, Windows 10

Sync Technology

None

CPU / Platform / Tiny Support

None / None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

EAN/UPC/JAN

0195713404266

Announce Date 2021-04-28

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



https://psref.lenovo.com

Visit psref website for the latest version of Product specifications Reference. © Lenovo, 2021. All rights reserved.



ThinkVision M15

DISPLAY

Panel Size

15.6-inch

Screen Dimensions

360.0 mm x 234.0 mm

Panel Type

In-Plane Switching

Active Area

344.16 mm x 193.59 mm

Backlight

WLED

Aspect Ratio

16:9

Resolution

1920 x 1080

Pixel Pitch

0.1793 mm x 0.1793 mm

Dot/Pixel Per Inch (DPI/PPI)

141

Viewing Angle (H x V@CR 10:1)

178° / 178°

Response Time

6ms (Extreme Mode)

14ms (Normal Mode)

Refresh Rate

60 Hz

Brightness (typical)

250 cd/m²

Contrast Ratio (typical)

1000:1

Dynamic Contrast Ratio (typical)

3M:1

Color Gamut

45% NTSC (CIE 1931)

Color Support (typical)

16.7 Million

Anti-glare

Yes

CONNECTIVITY

Video Signal

2 x USB Type-C 3.2 Gen1 (DP1.2 Alt Mode)

USB Hub

Yes

USB Upstream

1 x USB 2.0 (1 by USB Type-C)

USB Downstream

1 x USB 2.0 (1 by USB Type-C)

SPECIAL FEATURE

Software

Lenovo ThinkColour (Lenovo Display Control Center)⁴

Others

Height Adjustment

POWER

Power Consumption (typical/max) 8W / 9.5W

Power Consumption Sleep/Off Mode

< 0.3W

Power Consumption Switch-off Mode

< 0.3W

Energystar Power Consumption (P_{on}/E_{TEC}) 5W / 19kWh

Power Supply

External

USB Type-C Power Delivery (W)

up to 65 W³

Voltage Required

DC 5/9/15/20 V

MECHANICAL

Tilt Angle (front/back)

0° / 90°

Lift (Max range)

10 mm

VESA Mount Capability

Yes (2 screws holes, 100 mm)

Kensington Lock Slot

Yes

Cable Management

Yes

Bezel Color

Raven Black

Bezel Width (side)

7.3 mm

Bezel Width (top/bottom)

7.3 / 31.9 mm

DIMENSIONS

Size Packed (D x H x W, mm/inch)

407.9 x 75.9 x 279.9 mm 16.06 x 2.99 x 11.02 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)

235.5 x 360.0 x 108.4 mm 9.27 x 14.17 x 42.67 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position) 245.5 x 360.0 x 108.4 mm

9.66 x 14.17 x 42.67 inches

Weight Packed (kg/lbs.)

1.69 kg / 3.73 lbs.

0.86 kg / 1.90 lbs.1

Weight Unpacked (kg/lbs.)

WHAT'S IN THE BOX

1 x M15 Monitor

1 x Pair of Clips

1 x Sleeve

1 x USB Type-C to Type-C cable (1 m) Quick Setup Guide

CERTIFICATION

ENERGY STAR Certification

Yes

CCC Yes

> **EPEAT** Silver

RoHS (EU 2002/95/EC)

Yes

Windows Certification

Windows 7, Windows 10

China Energy Efficiency Standard Tier 2

.0. 2

TÜV Rheinland Low Blue Light

TÜV Rheinland Flicker Free













¹Actual weight may vary due to components, manufacturing process and options. ² USB Type-C* and USB-C* are registered trademarks of USB Implementers Forum. ³Listed as maximum capacity of power delivery. Actual capacity of power delivery may vary depending upon devices connected or monitor configuration and may decline with downstream USB ports connected or higher brightness setting. ⁴This software can only be used with Windows 10.

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.1 Gen 1; 10 Gbit/s for USB 3.1 Gen 2 & 20 Gbit/s for USB 3.2.

© 2021 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.









