



msi

GRAPHICS CARD

GeForce RTX™ 3060 Ti VENTUS 2X 8G OCV1 LHR



SPECIFICATIONS

Model Name	GeForce RTX™ 3060 Ti VENTUS 2X 8G OCV1 LHR
Graphics Processing Unit	NVIDIA® GeForce RTX™ 3060 Ti
Interface	PCI Express® Gen 4
Cores	4864 Units
Core Clocks	Boost: 1695 MHz
Memory Speed	14 Gbps
Memory	8GB GDDR6
Memory Bus	256-bit
Output	DisplayPort x 3 (v1.4a) HDMI x 1 (Supports 4K@120Hz as specified in HDMI 2.1)
HDCP Support	Y
Power consumption	200 W
Power Connectors	8-pin x 1
Recommended PSU (W)	650 W
Card Dimension(mm)	235 x 124 x 42 mm
Weight (Card / Package)	685 g / 1041 g
DirectX Version Support	12 API
OpenGL Version Support	4.6
Maximum Displays	4
VR Ready	Y
G-SYNC™ technology	Y
Adaptive Vertical Sync	Y
Digital Maximum Resolution	7680 x 4320

FEATURES



Afterburner

Take full control with the most recognized and widely used graphics card overlocking software in the world.



Dual Fan

Two fans and a huge heatsink ensure a cool and quiet experience for you.




Custom PCB

The custom PCB has been engineered with hardened circuits and optimized trace routing for performance and reliability.




TORX FAN 3.0

The award-winning MSI TORX Fan 3.0 design creates high static pressure and pushes the limits of thermal performance.



Thermal Padding

An abundance of thermal pads use any chance for additional heat transfer directly from the components.



Zero Frozr


Zero Frozr is the calm before the storm, keeping fans still and maintaining silence until cooling is needed.



MSI Center

The exclusive MSI Center software lets you monitor, tweak and optimize MSI products in real-time.

CONNECTIONS



1. DisplayPort
2. HDMI

1 2