

Tripp Lite

1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

USB-C Dock, Dual Display - 4K 60 Hz HDMI, USB 3.2 Gen 1, USB-A Hub, GbE, Memory Card, 100W PD Charging, Gray

MODEL NUMBER: U442-DOCK8G-GG











USB-C docking station with PD Charging connects 2 HDMI displays, USB-A peripherals and Ethernet to your Chromebook, Windows laptop or tablet.

Features

USB-C Docking Station Turns Your Laptop into a Workstation

This USB-C dock with PD Charging expands the potential of your Windows laptop, Chromebook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for transmitting 4K video and digital audio to two large displays, adding a thumb drive and other USB peripherals, connecting to a wired Gigabit Ethernet network, and powering and charging a PD Charging-compliant mobile device, all at the same time

Supports USB-C DisplayPort Alternate Mode for Converting Audio/Video Signals

By connecting the built-in USB-C cable to a source device that supports USB DisplayPort (DP) Alt Mode, you can output 4K video and digital audio to an HDMI monitor, television or projector without installing special software drivers.

Transmits 4K Video to 2 HDMI Displays Simultaneously

Two HDMI outputs each support 4K video resolutions up to 3840 x 2160 at 60 Hz with multi-channel sound, 36-bit Deep Color and 4:4:4 chroma subsampling. You can display the image from the host computer on both monitors, extend your host desktop across both with different windows open on each, or combine both into one large display as a video wall. Connect both monitors in Extended (4K at 30 Hz under MST/Windows) or Mirror (4K at 60 Hz under SST/Mac) mode. *Note:* When connecting a DP 1.4 Alt Mode host, the maximum HDMI resolution is 4K at 60 Hz for one monitor and 4K at 30 Hz for two. When connecting a DP 1.2 Alt Mode host, the maximum HDMI resolution is 4K at 30 Hz for one monitor and 1080p at 60 Hz for two, due to bandwidth limitation.

USB Ports Connect Keyboards, Thumb Drives and Other Peripherals

Two USB-A hub ports accept USB peripherals, such as flash drives, mice, keyboards and printers. They support fast USB 3.2 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with earlier USB generations. One dedicated port also supports 5V 1.5A (7.5W) of charging power dedicated to fast-charging your mobile device. *Note: Host must support USB OTG (USB On-the-Go)*.

PD Charging Port Charges the Connected Notebook, Tablet or Other Device

The USB-C port supports Power Delivery (PD) 3.0 charging of the connected PD Charging-compliant device. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to

Highlights

Converts audio/video signals from sources supporting USB-C DisplayPort Alt ModeSupports UHD resolutions up to 4K @ 60 Hz (4:4:4) for crystal-clear videoPower Delivery port supports 20V 5A (100W) power output for charging host deviceUSB-A and memory card ports allow connection of flash drives and other peripheralsConnects you to a wired Gigabit Ethernet network when Wi-Fi is unavailable

Applications

- Play 4K video from your laptop or PC on 2 HDMI displays
- Extend or mirror your desktop image across multiple displays at the same time
- Transfer data between your host computer and a USB-enabled thumb drive or external hard drive
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Access a wired Gigabit Ethernet network in a location with no or spotty Wi-Fi

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device(s) with HDMI input
- Multi-Stream Transport (MST) required to achieve extended dual displays; typically, Windows systems support MST
- Single-Stream Transport (SST) required to achieve mirrored dual displays; typically, Mac systems support SST

Package Includes

- U442-DOCK8G-GG USB-C Dock, Dual Display, Gray
- Owner's manual



20V 5A (100W). **Note**: 15W is dedicated to USB ports with remaining 85W available for PD Charging. This port does not support Quick Charge (QC).

Accesses a Wired Gigabit Ethernet Network

The RJ45 port offers access to a Gigabit Ethernet network when Wi-Fi is unavailable or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Allows External Memory Access

The memory card slots support Micro SD and SD/MMC cards for transferring data to and from your connected computer, laptop or tablet. Both card slots can be used at the same time.

Built-In USB-C Cable Attaches in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately

The plug-and-play USB-C dock is specifically designed for use with Windows laptops, Chromebooks and other devices equipped with a USB-C or Thunderbolt 3 port. It requires no extra software to be downloaded or installed and no external power. It fits into a purse, backpack or laptop bag for multiport convenience wherever you go.

Specifications

-		
OVERVIEW		
UPC Code	037332261298	
Product Type	Docking Station	
Technology	HDMI; USB 3.x	
Host Connector	USB C (MALE)	
VIDEO		
Number of Monitors Supported	2	
Video Ports	(2) HDMI (FEMALE)	
Video Ports Details	HDCP 1.4; HDCP 2.2	
Resolutions Supported	3840 x 2160 @60Hz (Single)3840 x 2160 @30Hz (Dual Extended)	
Max Supported Video Resolution	3840 x 2160 @60Hz (Single); 3840 x 2160 @30Hz (Dual Extended)	
Extended Mode	Yes	
Extended Mode Details	Dual 3840x2160 @ 30 Hz under MST mode (Windows System) Extended	
Mirror Mode	Yes	
Mirror Mode Details	Dual 3840*2160@60Hz under SST mode (Mac System) Mirrored	
Max Supported Color Depth	36-bit Deep Color	
Chroma Sub Sampling	4:2:2; 4:4:4	
DATA		





Data Ports	(2) USB A (FEMALE)	
Data Ports Details	(2) USB-A - USB 3.2 Gen 1 (5 Gbps)	
NETWORK		
Network Ports	RJ45 (FEMALE)	
STORAGE		
Card Slots	MICRO SD (FEMALE); SD (FEMALE)	
INPUT		
Built-In Cable Length (ft.)	0.4	
Built-In Cable Length (m)	0.12	
Built-In Cable Length (in.)	4.72	
Bus Powered	Yes	
BATTERY		
Battery Charging (5V/1.5A Port)	Yes	
POWER		
USB Power Delivery (PD) Charging Support	Yes	
USB Power Delivery (PD) Charging Specification	100W; 3.0	
USER INTERFACE, ALERTS & CON	TROLS	
LED Indicators	RJ45 Port: White (Connection), Orange (Activity)	
CHARGING		
Total Charging Watts	100	
Charging Ports / Amps	(1) 1.5A; (1) 5A	
PHYSICAL		
Color	Black; Gray	
Material of Construction	Aluminum, ABS	
Cable Jacket Material	TPE	
Cable Jacket Rating	VW-1	
Unit Dimensions (hwd / in.)	4.33 x 0.45 x 2.32	
Unit Packaging Type	Вох	
Unit Weight (lbs.)	0.2	



Unit Weight (kg)	0.09	
ENVIDONMENTAL		
Operating Temperature Penge	22 to 442°E (0 to 4E°C)	
Operating Temperature Range	32 to 113°F (0 to 45°C)	
Storage Temperature Range	14 to 158°F (-10 to 70°C)	
Operating Humidity Range	10% to 85% RH, Non-Condensing	
Storage Humidity Range	5% to 90% RH, Non-Condensing	
Power Provided to Connected Device(s)	USB-A: 5V/1.5A (7.5W), USB-C: 20V/5A (100W)	
COMMUNICATIONS		
Network Compatibility	1 Gbps (Gigabit)	
CONNECTIONS		
Ports	8	
Side A - Connector 1	USB C (MALE)	
Side B - Connector 1	(2) HDMI (FEMALE)	
Side B - Connector 2	(2) USB A (FEMALE)	
Side B - Connector 3	USB C (FEMALE)	
Side B - Connector 4	MICRO SD (FEMALE); SD (FEMALE)	
Side B - Connector 5	RJ45 (FEMALE)	
Connector Plating	Nickel	
FEATURES & SPECIFICATIONS		
Over Current Protection	Y	
HDCP Specification	1.4; 2.2	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)	
Driver Required	No	
Recommended Category Cable	Cat5e/6/6a	
Full Duplex Support	Yes	
Suspend Mode Support	Yes	
Remote Wakeup Support	Yes	
Quick Charge Compliant	No	
SD Card Specification	Micro SD; SD	
STANDARDS & COMPLIANCE		
Certifications	RoHS, REACH, CE, FCC	
TAA Compliant Option	N	
· ·		



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies