

Product data sheet

Specifications



APC Smart-UPS Ultra On-Line,
2200VA, Lithium-ion, Rack/Tower
1U, 120V, 5x 5-20R, 1x L5-20R
NEMA outlets, SmartConnect,
Extended runtime, W/rail kit

SRTL2K2RM1UC

Overview

Lead Time Usually in Stock

Main

Main Input Voltage	120 V 125 V
Product Or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	120 V 125 V
Main Output Voltage	120 V
Other Output Voltage	120 V 125 V
Kw Rating	1950 W
Rated Power In Va	2200 VA
Input Connection Type	NEMA 5-20P
Output Connection Type	5 NEMA 5-20R 1 NEMA L5-20R
Number Of Rack Unit	1U
Cable Length	8 ft (2.44 m)
Number Of Cables	1
Battery Type	Li-Ion (Lithium Ion)
Provided Equipment	RJ45 Cable USB cable Country-specific detachable power cord Rack Mounting brackets Rack Mounting support rails Installation guide Warranty card

Complementary

Software Package SmartConnect software for remote power monitoring feature availability varies by terms of use

Batteries & Runtime

Run Time	View Runtime Graph
Typical Recharge Time	1.5 h
Rbc Quantity	1

Battery Voltage	50 V
Battery Charge Power (Watts)	448 W
Extendable Run Time	1
Replacement Battery	APCRBC173-LI 

General

Redundant	No
-----------	----

Physical

Color	Silver grey
Height	1.69 in (43 mm)
Width	17.01 in (432 mm)
Depth	22.05 in (560 mm)
Net Weight	35.05 lb(US) (15.9 kg)
Mounting Preference	No preference
Mounting Mode	Rack-mounted with kit Tower-mounted with kit
Two Post Mountable	1
Usb Compatible	Yes

Input

Input Frequency	50/60 Hz
-----------------	----------

Output

Max Configurable Power (Watts)	1950 W
Output Frequency (Sync To Mains)	50/60 Hz +/- 3 Hz sync to mains
Crest Factor	3 : 1
Topology	On-Line
Waveform Type	Sine wave
Bypass Type	Internal Bypass (Automatic and Manual)
Maximum Configurable Power In Va	2200 VA

Conformance

Product Certifications	UL/cUL listed FCC
Standards	UL 1778 CSA C22.2 No.107.3-05 FCC Part 15 class A

Environmental

Ambient Air Temperature For Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	5...113 °F (-15...45 °C)

Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0...50000 ft (0.00...15240.00 m)
Acoustic Level	55 dB
Ip Degree Of Protection	IP20

Communications & Management

Control Panel	Multi-function LCD status and control console
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off (Epo)	Yes
Communication Port Support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use

Ordering and shipping details

Gtin	731304435556
-------------	--------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.95 in (278.2 mm)
Package 1 Width	22.20 in (564 mm)
Package 1 Length	30.08 in (764 mm)
Package 1 Weight	53.3 lb(US) (24.18 kg)

Contractual warranty

Warranty	5 years repair or replace
-----------------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

[Learn more about Green Premium >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile [End of Life Information](#)

Technical illustration

Dimensions

