

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

www.tripplite.com

5-Port Unmanaged Industrial Gigabit Ethernet Switch - 10/100/1000 Mbps, DIN/Wall Mount

MODEL NUMBER: NGI-U05











Industrial-grade switch expands Ethernet connectivity to factory floors and other environments with space constraints and wide temperature ranges.

Features

5-Port Unmanaged Gigabit Ethernet Switch Connects Your Devices to a LAN

This space-saving Tripp Lite switch transmits data over a Gigabit Ethernet network. Five auto-negotiating 10/100/1000 Mbps ports send data only to the devices designated to receive it, which improves the efficiency and potential throughput of the network.

Ruggedized Metal Housing Built to Last in Harsh Environments

The compact NGI-U05 adds 10/100/1000 Mbps Gigabit Ethernet capacity to your industrial and commercial applications, such as factory floors, warehouse operations and other environments with space constraints and wide temperature ranges. The industrial-grade high-strength case withstands vibration, shock and free fall. It can also operate in extreme temperatures ranging from -40 degrees to 167 degrees Fahrenheit.

Unmanaged Switch Requires Little to No Configuration

Quickly connect your network devices with little to no configuration. LEDs indicate when the switch is powered on and which Ethernet ports are showing activity. The NGI-U05 supports MAC address autolearning and auto-aging for efficient routing, as well as automatic MDI/MDI-X crossover detection for plugand-play functionality. IEEE 802.3x flow control allows smooth transmission of large files.

Flexible Mounting Options

The NGI-U05 may be DIN mounted using the pre-installed rail clip, which mounts firmly to any standard 35 mm DIN rail. It may also be wall mounted vertically or horizontally using the rear mounting holes. A 3-pin 9–48VDC terminal block supplies power input. Device power must be supplied by LPS (Limited Power Source) circuit.

TAA-Compliant for GSA Schedule Purchases

The NGI-U05 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

Highlights

- 5 auto-negotiable 10/100/1000 Mbps RJ45 ports connect devices over a LAN
- Industrial-grade switch supports operating temperature range of -40° to 167°F
- Easy-to-read LEDs indicate connection and activity status for all Ethernet ports
- Plug-and-play operation with no software or configuration required before use
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

Expand reliable Gigabit Ethernet connectivity to factory floors and outdoor environments with space constraints and wide temperature ranges

Package Includes

- NGI-U05 5-Port Unmanaged Industrial Gigabit Switch
- DIN rail-mounting clip (preinstalled)
- Wall-mounting bracket (preinstalled)
- Owner's manual





OVERVIEW	
UPC Code	037332265838
INPUT	
Maximum Input Amps Details	Maximum of 0.5A DC. The device power shall be supplied by SLPS (Limited Power Source)
Voltage Compatibility (VDC)	From 9~48
Power Source	3-Pin Terminal Block
USER INTERFACE, ALERTS & CO	DNTROLS
LED Indicators	1- Power ON/OFF (GREEN), 2- 100Mbps(GREEN) for Ethernet speed 10/100Mbps & Data Transmitting/Receiving, 3- 1000 (GREEN) for Ethernet speed 1000Mbps & Data Transmitting/Receiving
PHYSICAL	
Primary Form Factor	Din-Rail; Wall-mount
Color	Black
Material of Construction	Aluminum casing
Included Mounting Accessories	Υ
Unit Dimensions (hwd / in.)	4.3 x 0.9 x 2.91
Unit Weight (kg)	0.20
Unit Weight (lbs.)	0.44
ENVIRONMENTAL	
Storage Temperature Range	-40°F to 185°F (-40°C to 85°C)
Relative Humidity	5% to 95% (Non-Condensing)
Operating Temperature	-40°F to 167°F (-40°C to 75°C)
Power Consumption (Watts)	3.00
Fans (Type/Quantity)	Fanless
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
Network Compatibility Details	Auto-negotiable
Switching Capacity	10Gbps
Switching Capacity Details	1Gbps Per Port with Full Duplex
CONNECTIONS	
RJ45 Ports	5
RJ45 Ports Detail	5x 10/100/1000BASE-T





SFP Uplink Ports	0	
PoE Supported Ports	0	
Network Switch Ports	(5) 10/100/1000 (RJ45)	
FEATURES & SPECIFICATIONS		
MAC Addresses	2000	
Jumbo Frames	9000	
Console Port	No	
MAC Auto Learning	Yes	
RMON	No	
SNMP	No	
Storm Control	No	
DHCP Snooping	No	
Auto MDI/MDIX Crossover Detection	Yes	
STANDARDS & COMPLIANCE		
Certifications	Compliant Standards: IEEE 802.3 10Base-T; IEEE 802.3u 100Base-TX; IEEE 802.3x Flow control; IEEE 802.3 Auto-Negotiation	
Approvals	CE, FCC, RoHS, REACH	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies