




## 10" Android-powered Touch High-Traffic Kiosk eTILE-X 10

The eTILE-X 10 is an Android-powered kiosk, purpose-built for high-touch use and harsh environments like QSR, retail, and room booking - commercial and industrial environments that are otherwise unsuitable for consumer tablets. Its secure, consolidated set-up includes Power-over-Ethernet (PoE) support - using a single cable for both power and a consistent LAN connection.

### The eTILE-X 10 features:

- 10" Touch LCD Panel with 1280 x 800 (16:10) Resolution
- Built-in PoE or use included AC adapter
- Tamper Proof Design with Port Cover (concealed I/O ports and built-in cable management)
- 10-point Capacitive Touch
- VESA mount compatible (75 x 75)

# eTILE-X 10



Model name		eTILE-X 10	
Housing Material		IP Metal design	
Dimensions	W x H x D (mm)	255 x 172 x 29 mm	
	W x H x D (inch)	10.04 x 6.77 x 1.14 inch	
Weight		0.89kg / 1.96lbs	
CPU		Rockchip RK3288 Quad Core Cortex™-A17 up to 1.8GHz	
Chipset / OS		CPU built-in / Android 8.1	
Memory	Channels	Single Channel (built-in 2GB)	
	Type	DDR3	
	Data Rate	1333 MHz	
	Max Memory	2GB	
Graphics		ARM® Mali-T760 (integrated)	
Front Panel	Resolution	1280 x 800 (16:10)	
	Max Brightness	250 nits	
	Panel Type	VA	
	Viewing Angle	85/85/85/85	
	Response Time	25ms	
	Contrast Ratio	800:1	
	Touch	PCT supports 10 points	
Wi-Fi / Bluetooth		802.11b/g/n – Bluetooth 4.0	
Audio	Type	3.5mm Earphone + Mic	
	Channel	1.5W speaker x 2	
LAN		1Gbps Ethernet	
Storage		16M eMMC	
Front Camera		x 1 (2MP)	
Panel Control Button	Power Button		x 1
	Brightness Up		x 1
	Brightness Down		x 1
	Volume Up		x 1
	Volume Down		x 1
	Home Button		x 1
System Panel I/O	DC Jack		x 1 (12V)
	HDMI Out Port		x 1 (mini Type)
	USB 2.0 Port		x 2 (USB2.0) x 1 (Micro USB, OTG)
	USB 3.0 Port		-
	RJ45 LAN Jack		x 1 - PoE 802.3at
	Audio Set	Line-Out	x 1
		Mic-in	-
	Others		RS232 RX/TX through USB x 1, SD Card x 1
IP/IK Grade		IP65 (front panel)	
Adapter		12V / 1.5A AC Adapter	
Input Voltage		AC 100 ~ 240V	
Warranty		1 Year	
<b>Environment</b>			
MTBF		15,000 hrs	
Operating Temperature		0 ~ 40°C (32 ~ 104°F)	
Storage Temperature		-20 ~ 60°C (-4 ~ 140°F)	
Relative Humidity		90% RH (40°C Non-Condensing)	

Supports Android



AOPEN America  
San Jose,  
USA

\*Please note that product specifications are subject to change without notice

v1.0