VSEVEN



USB-C Male to DisplayPort 1.4 Male 32.4 Gbps 8K/4K UHD

V7USBCDP14-2M

SKU: CB55388

Connect your USB-C enabled device to a DisplayPort monitor or display with just one cable. Supports UHD 8K Resolution and a 32.4 GBPS bandwidth giving you an enhanced imaging experience. Works with almost all operating systems and is designed to be plug and play for use on various devices including desktop computers, laptops, tablets and other mobile devices. Triple shielded, high grade PVC jacket construction for excellent performance. Compact and durable design eliminates the need for adapters and other cabling to connect to your display or monitor.

- Ultra crisp image delivery for your display or monitor
- Clutter free, extended reach connection. Connectivity with only one cable
- Hassle free setup, simple plug and play connectivity with no need for additional cables or adapters
- Triple shielding aluminum, mylar foil, braid provides excellent RF and EMI shielding. Corrosion resistant connectors and strain relief for optimal signal transfer and durability.
- Quality manufacturing process in our ISO certified facilities and backed by V7 warranty

General

Sku: CB55388 Model: V7USBCDP14-2M EAN: 0662919114720 Warranty: 1 year Compliance: CE, FCC, RoHS, UKCA, WEEE Country Of Origin: Vietnam Package Type: Polybag

Color Color: Black

Package Dimensions

Package Dimensions (L/W/H): 6.3 x 8.27 x 0.39 in (160 x 210 x 10 mm) Shipping Weight: 0.03 kg (0.07 lbs)

Product Dimensions

Product Weight: 0.027 kg (0.06 lbs)

Technical

Cable Jacket: PVC Maximum Resolution: 7680 x 4320 Conductor: Tin Plated Copper Cable Length: 2m/6.6ft Conductor Size: 34AWG Shielding: Aluminum Mylar foil with Braid Standard: DisplayPort 1.4 Connectors: DisplayPort, USB C Frequency: 30 Hz Connector 1: USB-C Male Connector 2: DisplayPort Male Data Transfer Rate: 32.4 Gbps

The data in this publication is for illustration purposes only and does not necessarily represent standards or specifications which must be met by V7. Design and specifications are subject to change without prior notice. Trademarks belong to their respective owners. No responsibility assumed and all liability for damages resulting from use of this information or for any errors or omissions, are disclaimed. Measurement standards and testing conditions, as per manufacturer definitions, are available on request. Last Updated: September 23, 2021 10:03 Page 1