

The cost effective Planar® PLN2400 24" widescreen Full HD LED backlit LCD monitor features a borderless design, high display to body ratio, wide viewing angles, HDMI and VGA inputs, and 100x100 VESA pattern. The Planar PLN2400 fits seamlessly into home and office environments.



PLN2400 (-01)

24" LCD Monitor

SPECIFICATION	DETAIL
Product Name	PLN2400
Planar Part Number	998-1330-01
Viewable Size	23.8" diagonal (20.75" horizontal x 11.67" vertical)
Aspect Ratio	16:9
Contrast Ratio (typ)	1000:1
Viewing Angle (typ)	178° Horizontal and 178° Vertical (Specified at CR>10:1)
Response Time (typ)	6 ms (GTG)
Brightness (Typical)	250 cd/m ²
Display Type	Edge-Lit LED LCD
Display Resolution	1920 x 1080, full HD
Tilt Range	-5° to +15°
Palette	16.7 million colors
Pixel Pitch	0.2745 mm
Refresh Rate	48-75Hz (60Hz recommended)
Dimensions (W x H x D)	21.3" x 16.2" x 8.3" (539.78 mm x 411.61mm x 210 mm)
Dimensions without Stand	21.3" x 12.7" x 1.6" (539.78 mm x 322.06 mm x 40 mm)
Panel Depth	1.6" (40 mm)
Display Weight	7.8 lb (3.7 kg), 7.2 lbs (3.25 kg) without base & stand
Shipping weight	9.5 lb (4.3 kg)
Video Inputs	HDMI, VGA
HDCP	Yes

External Connections	D-sub 15-pin, 19-pin HDMI
Compatibility	PC and Mac® (adapter may be required for Mac)
Power Supply	Internal
Power Consumption (max)	22W typical (<0.5W standby)
Power Requirements	AC 100/240 VAC
Operating Temperature	5° to +40°C (41° to 104°F)
Humidity	10 - 90% RH (non-condensing)
Mount	Built-in 100 mm VESA, back
Product Approvals	FCC-B, CE, UL/cUL, RoHS
Recommended Usage	Up to 16 hours per day
Service and Support	3-Year Customer First [™] Warranty featuring FREE 2-Day Advance Replacement (US only). Please see warranty document for more details and for replacement procedures outside the US.
Options / Features	Wide viewing angle, Discreet branding, Nearly Borderless bezel, Anti-glare coating, Multi-language display, On screen display (OSD), Kensington® Security Slot
Blue Light Reduction	Yes
Flicker Free	Yes
In the Box	PLN2400 23.8" LED LCD Monitor, HDMI Cable, Power Cord, User's Guide
UPC	8 10069 81031 7

For more information, please visit www.planar.com Specifications are subject to change without notice. Specification Report Date: 5/2/2022 © Copyright 2022 Planar Systems, Inc. All rights reserved