

## Power Extension Cord, C19 to C20 - Heavy-Duty, 20A, 250V, 12 AWG, 15 ft. (4.6 m), Black

MODEL NUMBER: P036-015



C19 to C20 20A heavy-duty extension cable connects high-output devices with C19/C20 power connectors, including blade server chassis.

### Features

#### 20A C20-to-C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection

This heavy-duty extension cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a server, router, network switch or blade server enclosure to a UPS system or PDU. It can also replace or upgrade the standard power cord provided by the device's manufacturer. The 15-foot (4.6-meter) length allows you great flexibility in placing equipment with respect to the power outlet.

## Specifications

OVERVIEW	
UPC Code	037332266804
Device Compatibility	Server; Router; Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

### Highlights

- Recommended for powering servers, routers and other high-output network devices
- 15 ft. length allows great flexibility in placing devices in relationship to AC outlet
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge supports high power levels required for larger equipment

### Package Includes

P036-015 C19 to C20 Heavy-Duty Extension Cord, 15 ft. (4.6 m), Black

Cable Jacket Rating	FT2; VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	11mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm <sup>2</sup> )	3.31
Cable Length (ft.)	15
Cable Length (m)	4.57
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	10% to 65% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C19
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	REACH; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.