



## Rugged, convertible Chromebook built for education

Learning happens everywhere with the rugged HP Chromebook x360 11 G4 EE, featuring a versatile 360° hinge that suits student learning styles. Boost productivity with the latest Intel® Celeron® processor<sup>[2]</sup>, reliable connectivity, and long battery life.



### **Immersive 360° multi-modal learning**

Engage student senses on a Chromebook with a flexible 360° hinge. Easily interact and complete activities and tasks comfortably in laptop, tablet, tent, or stand mode.

### **Designed for reliability. Engineered for durability.**

Say goodbye to downtime from damage with a full-skirted anchored keyboard that resists picking, minor spills up to 350 ml (11.8 oz), and dust. This Chromebook can withstand drops up to 122 cm<sup>[5]</sup> and undergoes MIL-STD 810H<sup>[7]</sup> and HP education testing.<sup>[6]</sup>

### **Performance and productivity for education**

Quickly access videos, assignments, and more in crowded wireless networks with the latest Intel® Celeron® processor<sup>[2]</sup>, plenty of memory, and Wi-Fi 6<sup>[8]</sup>—powered by Chrome OS. Keep students productive with long battery life and fast recharging.

## **Featuring**

### **Simplify deployments**

Get a low-maintenance experience with the automatic software updates and virus protection of the Chrome OS. <sup>[1]</sup>

### **Universal connectivity and charging with USB-C™**

Use the USB-C™ port to access and charge your USB-C™ accessories from your Chromebook™ or charge your Chromebook™ from any USB-C™ adapter.

### **Enhanced design elements**

Help prevent degradation, water intrusion, and tampering with a keyboard that resists picks, minor spills, and key removal.

### **Apps and content for expanded learning**

Take learning in new directions with access to the Google Play™ Store and Android™ apps, which include thousands of instantly shareable and easily manageable innovative education apps. <sup>[1]</sup>

## Specifications

<b>Operating system</b>	Chrome OS™ 64
<b>Processor family</b>	Intel® Celeron® processor
<b>Processor</b>	Intel® Celeron® N5100 (up to 2.8 GHz burst frequency, 4 MB L3 cache, 4 cores) <sup>[6,7]</sup>
<b>Memory</b>	8 GB LPDDR4x-4266 MHz RAM (onboard)
<b>Internal Storage</b>	64 GB eMMC
<b>Optical drive</b>	Not included
<b>Graphics</b>	Integrated
<b>Graphics (integrated)</b>	Intel® UHD Graphics
<b>Display</b>	11.6" diagonal, HD (1366 x 768), touch, IPS, anti-glare, 220 nits, 45% NTSC <sup>[6,7]</sup>
<b>Display size (diagonal)</b>	11.6"
<b>Audio</b>	HD audio, dual speakers, dual array microphones
<b>Minimum dimensions (W x D x H)</b>	29.5 x 20.5 x 2.3 cm
<b>Minimum dimensions (W x D x H)</b>	11.61 x 8.07 x 0.9 in
<b>Weight</b>	Starting at 1.51 kg <i>(Weight will vary by configuration.)</i>
<b>Weight</b>	Starting at 3.33 lb <i>(Weight will vary by configuration.)</i>
<b>Keyboard</b>	Full-size island-style, spill and pick resistant keyboard
<b>Pointing device</b>	Clickpad with multi-touch gesture support
<b>Ports</b>	2 SuperSpeed USB Type-C® 5Gbps signaling rate (USB Power Delivery, DisplayPort™ 1.4); 2 SuperSpeed USB Type-A 5Gbps signaling rate; 1 headphone/microphone combo
<b>Expansion slots</b>	1 microSD <i>(Supports SD, SDHC, SDXC.)</i>
<b>Wireless</b>	Intel® Wi-Fi 6 AX201 (2x2) and Bluetooth® 5 combo
<b>Power</b>	HP Smart 45 W USB Type-C™ adapter <sup>[12]</sup>
<b>Battery type</b>	HP Long Life 2-cell, 47 Wh Li-ion polymer
<b>Battery weight</b>	0.48 lb
<b>Battery weight</b>	220 g
<b>Sustainable impact specifications</b>	Low Halogen; Outside box and corrugated cushions are 100% sustainably sourced and recyclable
<b>Security management</b>	Nano Security lock slot; Google Titan C
<b>Software included</b>	Chrome Education Upgrade (Sold separately); HP Classroom Manager (Sold separately) <sup>[9,10]</sup>
<b>UPC number</b>	196786015823
<b>Manufacturer Warranty</b>	1 year (1/1/0) limited warranty includes 1 year of parts and labor. No on-site repair. Terms and conditions vary by country. Certain restrictions and exclusions apply. <sup>[14]</sup>

## Top Recommended Displays, Accessories and Services

---

### Docking Stations

HP USB-C Travel Hub G2	7PJ38AA
------------------------	---------

---

### Backpacks

HP Prelude Pro 15.6-inch Recycled Backpack	1X644AA
--	---------

---

### Cases

HP Prelude Pro 15.6-inch Recycled Top Load	1X645AA
--	---------

---

### Keyboard and Mouse Kits

HP Wired Desktop 320MK Mouse and Keyboard	9SR36AA
---	---------

---

### Mice

HP Comfort Grip Wireless Mouse	H2L63AA
--------------------------------	---------

---

### Power Adapters

HP 45W USB-C LC Power Adapter	1MZ01AA
HP 65W USB-C Power Adapter	1HE08AA
HP 45W USB-C G2 Power Adapter	1HE07AA

---

### Headsets

HP Stereo USB Headset G2	428K6AA
HP Stereo 3.5mm Headset G2	428K7AA

---

### Personal Systems Commercial Care Pack Services

HP 3 year Pickup and Return Notebook Hardware Support	UQ990E
HP 3 year Pickup and Return w/Accidental Damage Protection Notebook Hardware Support	UQ996E

---

### Personal Systems Hardware Support Onsite Service

HP 3 year Next Business Day Response Onsite w/Accidental Damage Protection NB HW Supp	UQ994E
---	--------

## Messaging Footnotes

- [1] Internet access required and sold separately. Some apps may require purchase.
- [2] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.
- [5] 122 cm test on plywood and 76 cm test on concrete. Drop test is not a guarantee of future performance under these test conditions. Any accidental damage requires an optional HP Accidental Damage Protection Care Pack.
- [6] Test results are not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.
- [7] MIL-STD testing is not intended to demonstrate fitness for U.S. Department of Defense contract requirements or for military use. Test results are not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.
- [8] Wireless access point and Internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 (802.11ax) is backwards compatible with prior 802.11 specs. The specifications for Wi-Fi 6 are draft specifications and are not final. If the final specifications differ from the draft specifications, it may affect the ability of the notebook to communicate with other 802.11ax WLAN devices. Only available in countries where 802.11ax is supported.

## Technical Specifications Footnotes

- [6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.
- [7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.
- [9] HP Classroom Manager is sold separately. Control and device locking from the teacher's desktop requires purchase of HP Classroom Manager.
- [10] Chrome Education Upgrade requires one-time setup, subscription, Google Admin Console, and your organization's domain. Please see <https://support.google.com/a/answer/60216>.
- [12] Recharges up to 90% within 90 minutes when the system is off or in standby mode when used with the power adapter provided with the notebook. After charging has reached 90% capacity, charging will return to normal. Charging time may vary +/-10% due to System tolerance.
- [14] HP Care Packs are sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit [www.hp.com/go/cpc](http://www.hp.com/go/cpc). HP services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.

---

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Celeron and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. © 2020 Google LLC All rights reserved. Google and the Google Logo are registered trademarks of Google LLC.

