

## PERFORMANCE

### Processor

Intel® Core™ i5-1245U, 10C (2P +8E) / 12T, P-core 1.6 / 4.4GHz, E-core 1.2 / 3.3GHz, 12MB

### Graphics

Integrated Intel Iris® Xe Graphics

### Chipset

Intel SoC Platform

### Memory

8GB Soldered LPDDR4x-4266

### Memory Slots

Memory soldered to systemboard, no slots, dual-channel (8GB or 16GB model)

### Max Memory

8GB soldered memory, not upgradable

### Storage

256GB SSD M.2 2242 PCIe® 4.0x4 NVMe® Opal2

### Storage Support

One drive, up to 256GB M.2 2242 SSD

### Card Reader

MicroSD Card Reader

### Optical

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC5682I codec

### Speakers

Stereo speakers, 2W x2, optimized with Waves MaxxAudio®

### Camera

FHD 1080p with Privacy Shutter

### Microphone

2x, Array

### Battery

Integrated 57Wh

### Power Adapter

65W USB-C® Slim (2-pin)

## DESIGN

### Display

14" FHD (1920x1080) IPS 250nits Anti-glare

### Touchscreen

None

### Keyboard

Backlit, English

### Case Color

Abyss Blue

### Case Material

PC + ABS (Top), PC + ABS (Bottom)

### Dimensions (WxDxH)

325.4 x 217 x 19.83 mm (12.81 x 8.54 x 0.78 inches)

### Weight

Starting at 1.56 kg (3.44 lbs)

## SOFTWARE

### Operating System

Chrome OS

### Bundled Software

None

## CONNECTIVITY

### Ethernet

None

### WLAN + Bluetooth®

Intel AX211 Wi-Fi® 6E, 2x2 + BT5.2

### WWAN

None

### SIM Card

None

### NFC

None

### Standard Ports

- 2x USB 3.2 Gen 2
- 1x HDMI®, up to 4K/60Hz
- 1x microSD card reader
- 1x Headphone / microphone combo jack (3.5mm)

### Optional Ports (configured)

2x ThunderBolt 4

### Docking

Various docking solutions supported via Thunderbolt™ or USB-C.

For more compatible docking solutions, please visit [Docking for ThinkPad® C14 Gen 1 Chromebook](#)

### Monitor Cable

None

## SECURITY & PRIVACY

### Smart Card Reader

None

### Security Chip

Google Security Chip H1

### Fingerprint Reader

Touch Style

### Physical Locks

Kensington® Nano Security Slot, 2.5 x 6 mm

### Other Security

Camera privacy shutter

## MANAGEABILITY

### System Management

Intel® vPro Enterprise

## SERVICE

### Base Warranty

1-year, Depot

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications

- EPEAT™ Gold
- ENERGY STAR® 8.0
- ErP Lot 3
- TCO Certified 9.0
- RoHS compliant

### Mil-Spec Test

MIL-STD-810H military test passed

## MODEL

**TopSeller** : Yes **Announce Date** : 2022-06-24

**EAN / UPC / JAN** : 196801812543 **End of Support** : N/A



## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo 65W Standard AC Adapter (USB Type-C)- US/Can/Mex

4X20M26268

This Lenovo 65W Standard AC Adapter (USB Type-C) Power Adapter offers fast, efficient charging at home, in the office, or on the go. This power adapter is compatible with ThinkPad USB-C enabled Notebook and Tablet.

## Recommended Services

BEST	4Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + International Upg) (5PS0N73132)
BETTER	3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + International Upg) (5PS0N73156)
GOOD	3Y Lenovo Support (Premier Support + Keep Your Drive + International Upg) (5PS0N73153)

For a full list of accessories and services, please visit: <https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference