

Cat6a 10G Snagless Molded UTP Ethernet Cable (RJ45 M/M), PoE, White, 50 ft. (15.2 m)

MODEL NUMBER: N261-050-WH



Ethernet cable with Power over Ethernet (PoE) connects critical components, such as servers, switches, routers and hubs, in high-density 10G networks.

Features

Cat6a Cable Ideal for Your High-Density 10 Gigabit Ethernet Network

This Cat6a 10G Ethernet cable with RJ45 connectors is recommended for connecting network components like printers, computers, copiers, routers, servers, modems, hubs and switches in high-density data centers and network closets. Designed for fast transmission and excellent signal quality, the N261-050-WH ensures peak performance throughout your LAN.

Supports Power over Ethernet to Save You Money and Give You More Installation Choices

Because this Cat6a cable supports PoE, it can supply the power to operate compatible PoE devices, such as security cameras, VoIP telephones, point-of-sale kiosks and access control devices. This saves you the expense and effort of purchasing, connecting and installing individual power supplies for each device. It also helps you install PoE devices in areas far away from AC outlets, such as poles or ceilings.

Snagless RJ45 Male Connectors Add Extra Protection

The RJ45 connectors' snagless design protects the locking tabs from being damaged or broken off during installation. The contacts feature 50-micron gold plating to help ensure the most accurate signal transfer possible, improving near-end crosstalk (NEXT) performance to 500 MHz.

White Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The cable has a white PVC jacket, which is easy to identify quickly in a crowded patch panel or switch and helps prevent the cable from becoming accidentally disconnected.

Premium Construction for Superior Performance

Manufactured from 24 AWG copper wire, the four-pair stranded cable is rated for speeds up to 10 Gbps. Integral strain relief gives the unshielded cable extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

Specifications

OVERVIEW

Highlights

- Cat6a UTP Ethernet cable rated for high-speed 10 Gbps communications
- Supports PoE to save you expense and effort of powering PoE devices individually
- Allows installation of PoE devices in hard-to-reach areas or away from AC outlets
- Snagless RJ45 connectors prevent tabs from being damaged during installation
- White jacket permits fast, easy identification in a crowded switch or patch panel

Package Includes

N261-050-WH Cat6a 10G Snagless Molded UTP Ethernet Cable (RJ45 M/M), PoE, White, 50 ft. (15.2 m)



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

UPC Code	037332277558
Technology	Cat6a
PHYSICAL	
Color	White
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	СМ
Cable Shielding	UTP
Cable Outer Diameter (OD)	6.0mm
Number of Conductors	4
Conductor Material	Stranded Copper
Conductor Gauge	24 AWG
Wire Type	Stranded
Wire Gauge (AWG)	24
Cable Length (ft.)	50
Cable Length (m)	15.24
Cable Length (in.)	600
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range COMMUNICATIONS	5% to 85% RH, Non-Condensing
	5% to 85% RH, Non-Condensing 500 MHZ
COMMUNICATIONS	
COMMUNICATIONS Bandwidth per TIA Standard	500 MHZ
COMMUNICATIONS Bandwidth per TIA Standard Maximum Bandwidth as Tested	500 MHZ 600 MHZ
COMMUNICATIONS Bandwidth per TIA Standard Maximum Bandwidth as Tested Network Compatibility	500 MHZ 600 MHZ 10 Gbps
COMMUNICATIONS Bandwidth per TIA Standard Maximum Bandwidth as Tested Network Compatibility IEEE Standards Supported	500 MHZ 600 MHZ 10 Gbps
COMMUNICATIONS Bandwidth per TIA Standard Maximum Bandwidth as Tested Network Compatibility IEEE Standards Supported CONNECTIONS	500 MHZ 600 MHZ 10 Gbps 802.3; 802.3an
COMMUNICATIONS Bandwidth per TIA Standard Maximum Bandwidth as Tested Network Compatibility IEEE Standards Supported CONNECTIONS PoE Capability	500 MHZ 600 MHZ 10 Gbps 802.3; 802.3an 15.4W (802.3af); 30W (802.3at)
COMMUNICATIONS Bandwidth per TIA Standard Maximum Bandwidth as Tested Network Compatibility IEEE Standards Supported CONNECTIONS PoE Capability Side A - Connector 1	500 MHZ 600 MHZ 10 Gbps 802.3; 802.3an 15.4W (802.3af); 30W (802.3at) RJ45 (MALE)



[
Contact Plating	Gold
Connector Type	Molded; Snagless
Wiring Configuration	EIA/TIA 568B
FEATURES & SPECIFICATIONS	
IP68 Rated	No
Snagless Connector	Yes
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); IEEE 802.3 10Base-T; IEEE 802.3af PoE; IEEE 802.3an 10GBase-T; IEEE 802.3at PoE+; REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies