

Tripp Lite
1111 W. 35th Street

Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

5.8kW 208/240V Single-Phase ATS/Monitored PDU - 16 C13, 2 C19 & 1 L6-30R Outlets, Dual L6-30P Inputs, 10 ft. Cords, 2U, TAA

MODEL NUMBER: PDUMNH30HVAT2











ATS PDU allows real-time current metering and remote power monitoring to help prevent circuit overloads and ensure proper load balance.

Features

Single-Phase 30A 208V/240V ATS PDU Distributes and Monitors Network-Grade Power in Real Time

This monitored PDU provides real-time remote monitoring of voltage, frequency and load levels via its built-in network interface. Ideal for network IT applications, small computer rooms and other equipment rack applications, the PDUMNH30HVAT2 features 16 C13, 2 C19, and NEMA L6-30P outlets for connecting equipment. Dual 10-foot (3.1-meter) power cords with NEMA L6-30P inputs connect to separate primary and secondary mains circuits, backup generators, UPS systems or utility power grids, including out-of-phase sources.

Switches from Primary to Secondary Power Source in Milliseconds

Dynamic solid-state automatic transfer switching (ATS) allows the PDU to switch to the secondary source within 1-5 milliseconds, should the primary source fail or become unstable, to ensure your connected equipment operates without interruption. An on-board ATS processor constantly evaluates the power quality of both input sources. It prevents switching if the secondary source is unavailable or of lower quality than the primary source.

Built-In LX Platform Network Management Card Allows Remote Access 24/7

The Java-free HTML5-based WEBCARDLX network interface enables full remote access for PDU status monitoring and email notifications via secure web browser, SNMP, telnet or SSH. The latest version of PowerAlert Device Manager (PADM20) provides enhanced remote management capabilities, including customizable dashboard graphs to fit user preferences. The PADM20 upgrade and Tripp Lite's PowerAlert Element Manager (PAEM) form a powerful tool for expanding maintenance functions in large installations, including firmware update checks and backup and restoration of device configurations.

Digital Load Meter Helps Prevent Potentially Expensive Overloads

A digital ammeter reports the total load for all connected equipment in amps and kilowatts. Monitoring capacity helps ensure load levels remain well below maximum capacity levels with no danger of overload that could lead to costly downtime or damaged equipment. Maintaining proper load levels, even while adding new equipment, can keep your TCO (total cost of ownership) low. Current monitoring provides 1% billing grade accuracy.

Highlights

- Built-in HTML5-based LX Platform interface allows you 24/7 remote access
- Enables redundant A/B power option for single-corded network devices
- Digital meter for real-time voltage, amp and load monitoring helps prevent overloads
- Dual 10 ft. cords with NEMA L6-30P inputs connect to separate power sources
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- PDUMNH30HVAT2 5.8kW Single-Phase ATS/Monitored PDU
- Configuration cable, USB-A to USB Micro-B
- Rack-mounting hardware
- Installable plug-retention sleeves
- Cable ties
- Owner's manuals



Mounts into 2U of Rack Space or on a Wall

Use the included mounting hardware to install the all-metal housing into 1U of space in an EIA-standard 19-inch rack. You may also use the mounting brackets to secure the PDU to a wall or under a counter.

TAA-Compliant for GSA Schedule Purchases

The PDUMNH30HVAT2 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

| OVERVIEW | | |
|-----------------------------------|---|--|
| UPC Code | 037332261434 | |
| PDU Type | Auto-Transfer Switch; Local Metered; Monitored | |
| INPUT | | |
| PDU Input Voltage | 200; 208; 240 | |
| Recommended Electrical Service | 30A 208V | |
| Maximum Input Amps | 30 | |
| Maximum Input Amps Details | Agency de-rated to 24A continuous | |
| PDU Plug Type | (2) NEMA L6-30P | |
| Input Phase | Single-Phase | |
| Input Cord Details | Set of two inputs connect to separate PRIMARY and SECONDARY power sources | |
| Input Cord Length (ft.) | 10 | |
| Input Cord Length (m) | 3.05 | |
| ОИТРИТ | | |
| Output kW Capacity (kW) | 5.8 | |
| Output Capacity Details | 5kW (208/240V), 4.8kW (200V) total capacity / 30A max (Agency de-rated to 24A), 24A max per L6-30R outlet; 20A max per breakered outlet bank; 16A max per C19 outlet; 12A max per C13 outlet | |
| Frequency Compatibility | 50 / 60 Hz | |
| Output Receptacles | (16) C13; (2) C19; (1) L6-30R | |
| Output Nominal Voltage | 200; 208; 240 | |
| Overload Protection | Includes two 20A output circuit breakers; Breaker 1 controls the upper row of 9 outlets (8 C13, 1 C19); Breaker 2 controls the lower row of outlets (8 C13, 1 C19); L6-30R outlet is unbreakered | |
| USER INTERFACE, ALERTS & CONTROLS | | |
| Front Panel LCD Display | Digital display reports output amps in 4 separately metered loading segments (BANK 1: Outlets #1-9; BANK 2: Outlets #10-18; BANK 3: Outlet #19), whole-PDU output kW load level and input voltage on primary and secondary input lines, and IP address. Temp and Humidity will display if optional Envirosense2 modules are attached. | |
| Front Panel LEDs | Front panel LEDs confirms amp / kilowatt / voltage reporting information along with active primary and secondary input source status | |



| Switches | ENTER and MODE switches toggle the digital display to show output amps (Banks 1-4), total kW output and input voltage (primary, secondary), and IP address. |
|--------------------------------------|---|
| SURGE / NOISE SUPPRESSION | |
| Automatic Shut-Off | No |
| PHYSICAL | |
| Material of Construction | Metal |
| Form Factors Supported | 2U rackmount |
| Minimum Required Rack Depth (cm) | 40.64 |
| Minimum Required Rack Depth (inches) | 16 |
| PDU Form Factor | Horizontal (2U) |
| Shipping Dimensions (hwd / in.) | 7.80 x 16.70 x 20.20 |
| Shipping Weight (kg) | 7.85 |
| Unit Dimensions (hwd / in.) | 3.5 x 17.5 x 12.5 |
| Unit Dimensions (hwd / cm) | 8.8 x 44.4 x 31.7 |
| Unit Weight (lbs.) | 13.7 |
| Unit Weight (kg) | 6.21 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 0C ~ 40C (32F ~ 104F) |
| Storage Temperature Range | -30°C to +50°C (-22°F to +122°F) |
| Relative Humidity | 5-95% non condensing |
| Operating Elevation (ft.) | 0-10,000 |
| Operating Elevation (m) | 0-3000 |
| COMMUNICATIONS | |
| PowerAlert Software | LX Platform Interface: PowerAlert Device Manager |
| Communications Cable | Micro-USB- to-USB A configuration/console Access cable |
| Network Monitoring Port | RJ45 Network port, Micro-USB Configuration port, USB A port supports a variety of Envirosense2 environmental and control modules. See Accessories>Management Hardware section for more information about these modules. |
| SNMP Compatibility | Yes |
| Network Compatibility | 10 Mbps; 100 Mbps (Fast Ethernet) |
| Network Speed Details | 10 / 100 |
| Communications Interface | (1) DB9 Serial; (1) Micro-USB; (1) Pre-installed network card; (1) RJ45 Network; (1) USB-A |
| FEATURES & SPECIFICATIONS | |
| High Availability PDU Features | Auto-Transfer Switching |



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

| STANDARDS & COMPLIANCE | | |
|--|---|--|
| Certification & Compliance | UL 60950-1; FCC Part 15 Class A (USA); NOM (Mexico); RoHS | |
| WARRANTY | | |
| Product Warranty Period (Worldwide) | 2-year limited warranty | |

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies