

## SEAL GLOW 2 WATERPROOF KEYBOARD BACKLIT MAGNETIC BACKING

Model: S106G2M, SW106G2M

Seal Glow 2 Waterproof Backlit Keyboards with Magnetic Backing from Seal Shield have a 100% waterproof & dishwasher-safe rating that is IP68-certified and designed to withstand industrial-grade disinfectants & cleaners. Quiet Touch™ LED backlit characters provide non-intrusive visibility assistance & easy location in darker settings with a full-size numeric keypad for easy entry of numbers. Laser-etched keycaps enhance durability and product longevity throughout regular and vigorous cleaning. Features a Gold-Plated USB Quick Connect™ cable for easy pluc

## **FEATURES:**



100% Waterproof, Dishwasher-Safe, & Fully Submersible



Fully Sealed Silicone Keyboard is IP68-Certified



Gold Coated USB Quick Connect Cable with Seal Cap™ USB Protector



Full-Size Numeric Keypad, Magnetic Backing, & Laser Etched Keycaps



Designed to Withstand Industrial-Grade Disinfectants & Cleaners



LED Backlit Illuminated Characters with Magnetic Backing



UV Reinforced Key Caps



Compact Footprint



S106G2M



SW106G2M

#### ADVANCED CLEANING CAPABILITIES

· Dishwasher-Safe

Compatible with Spray & Wipe Disinfectant Products:

- · Clorox Healthcare®
- · Lysol®
- · PDI Products
- · Bleach, Ethanol, IPA, Quats, Citric Acid, & Hydrogen Peroxide, and Other Industrial-Grade Cleaners and Disinfectants





# SEAL GLOW 2 WATERPROOF KEYBOARD BACKLIT MAGNETIC BACKING

Model: S106G2M, SW106G2M

### **TECHNICAL DATA:**

Compatibility:	Windows®
Key Layout:	103 US Language
Net Dimensions:	15.15 x 5.43 x 0.78 in (38.5 x 13.8 x 2 cm)
Net Weight:	0.99 lbs (0.450 kg)
Gross Weight:	1.34 lbs (0.610 kg)
Cable Length:	6in(15cm) Quick Connect™ with USB Extension Cable
Connection Type:	Gold Plated USB
Key Switch Type:	Carbon point activation with Tactile Feedback
Key Switch Force:	150 ±15 gf
Key Switch Life Cycle:	Greater than 10 Million keystrokes
Keycaps Imaging Type:	Laser Etched
Operating Current:	100mA
Operating Voltage:	+ 5VDC ± 5%
Total Key Travel:	0.063 ± 0.0196 in (1.6 ± 0.5 mm)
Storage Temperature:	-5° - 140° F (-20° to 60° C)
EMI - RFI:	Conforms to FCC Rules for Class B Device
Waterproof/Dustproof Ratings:	IP68, NEMA 4X
Approvals/Certifications:	RoHS, WEEE, CE, FCC, ICES-003, RCM, REACH, Cal Prop 65



Copyright© 2022, Seal Shield, LLC. All rights reserved. All other trademarks and trade names are those of their respective owners

Limited 2-Year Warranty