

2XC

Clamp Base Dual Monitor Mount

Amer Mounts' 2XC dual monitor stand is designed for 13" to 27" display monitors with VESA pattern of 75x75mm or 100x100mm, each arm supports a maximum weight of 10kg. Each arm is fully and independently adjustable. The monitors can be rotated 360° for landscape or portrait orientation, freely adjust tilt 125° and swivel 180° to find the right viewing angle and optimal ergonomic position.

Features:

- Easy Installation: simple assembly with interchangeable C-clamp or grommet bases
- Detachable VESA Plates: quickly attach or remove your monitors
- Cable Management: clips included for routing wires



Specifications

VESA Support:	• 75x75/100x100	Arm Span:	• 735mm
Monitor Size:	• 13" ~ 27"	Pole Height:	• 450mm
Monitor Weight:	• 10Kg(22lbs)	Clamp Type:	• C-clamp with dual locks
Monitor Quantity:	• 2	Grommet Install:	• Available
Tilt:	• +90°~-90°	Wire Management:	• External Clips
Swing:	• 360°	Material:	• Steel & Aluminum
Rotate:	• 360°	Unit Weight:	• 4.6 Kg
Pole Diameter:	• 35mm	Surface Finish:	• Powder Coating
		Color:	• Black

Warranty and Support

Warranty: 1 Year

Support: Free technical support (phone/email)

www.amer.com / www.amermounts.com

sales@amer.com
 1-800-262-9703

Specifications subject to change without notice. Errors and omissions excepted. All trademarks are properties of their respective owners.

Revision 1.00