

## PERFORMANCE

### Processor

Intel® Core™ i5-10500 (6C / 12T, 3.1 / 4.5GHz, 12MB)

### Graphics

Integrated Intel UHD Graphics 630

### Chipset

Intel Q470 Chipset

### Memory

1x 8GB SO-DIMM DDR4-2666

### Memory Slots

Two DDR4 DIMM slots, dual-channel capable

### Max Memory

Up to 64GB DDR4-2933

### Storage

256GB SSD M.2 2280 PCIe® 3.0x4 NVMe® Opal

### Optane™ Memory

None

### Storage Support

Up to three drives, 2x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 2TB each
- M.2 SSD up to 1TB
- Optional Intel Optane Memory, M.2

### Card Reader

None

### Optical

DVD±RW

### Audio Chip

High Definition (HD) Audio, Realtek® ALC233 codec

### Speakers

3Wx2

### Camera

FHD 1080p

### Microphone

2x, Array

### Power Supply

150W 89% Adapter

## DESIGN

### Display

23.8" FHD (1920x1080) IPS Anti-glare 250nits 72% NTSC, Touch

### Touchscreen

10-point Multi-touch

### Keyboard

USB Traditional Keyboard, Black, English

### Mouse

USB Calliope Mouse, Black

### Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

### Case Color

Black

### Stand

UltraFlex IV Stand

### Carry Handle

None

### Dust Filter

None

### Mounting

VESA mount

### Form Factor

AIO (23.8 inches)

## CONNECTIVITY

### Ethernet

Integrated 100/1000M

### WLAN + Bluetooth®

Intel AX201 11ax, 2x2 + BT5.1, vPro

### Rear Ports

- 4x USB 3.2 Gen 1 (one supports Smart Power On)
- 1x DisplayPort™
- 1x Ethernet (RJ-45)

### Optional Rear Ports (configured)

None

### Right Ports

- 2x USB 3.2 Gen 2
- 1x USB-C® 3.2 Gen 1 (5V/3A charging)
- 1x headphone / microphone combo jack (3.5mm)

### Monitor Cable

None

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0, TCG certified

### Fingerprint Reader

No fingerprint reader

### Physical Locks

Kensington® Security Slot™, 3 x 7 mm

### Kensington Cable Lock

None

### Chassis E-Lock

None

### Chassis Intrusion Switch

None

### Other Security

ThinkShutter camera cover

## MANAGEABILITY

### System Management

Intel® vPro

## SERVICE

### Base Warranty

3-year, Onsite

### Included Upgrade

None

## CERTIFICATIONS

### Green Certifications

- ErP Lot 3
- TCO Certified 8.0
- TCO edge
- RoHS compliant

### Other Certifications

TÜV Rheinland® Low Blue Light

### Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Fungus, Solar Radiation)

## SOFTWARE

### Operating System

Windows® 11 DG Windows 10 Pro 64, English

### Bundled Software

None

## MODEL

TopSeller : Yes

Announce Date : 2022-10-11

EAN / UPC / JAN : 196803183054

End of Support : 2027-01-04

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

## Recommended Services

BEST	4Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + International Upg) (5PS0N73191)
BETTER	4Y Lenovo Support (Premier Support + Keep Your Drive + International Upg) (5PS0N73243)
GOOD	3Y Premier Support upgrade from 3Y Onsite (5WS0V08537)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference