


## 40/100/400G Multimode 50/125 OM4 Fiber Optic Cable (Duplex SN-PC to Duplex LC-PC M/M), LSZH, Magenta, 2 m (6.6 ft.)

MODEL NUMBER: **N823L-02M-MG**



40/100/400 GbE Ethernet cable supports high bandwidths necessary for next-gen cloud services, hyperscale data centers and telecom carriers.

### Features

#### 40/100/400 GbE Cable Supports High Bandwidths for High-Density Data Networking

The N823L-02M-MG is a premium multimode fiber optic cable that supports 400 Gb Ethernet speeds for transmitting data and voice signals over short distances. As the amount of traffic in data networks grows, so does the need for next-generation devices and fiber cables to support much higher bandwidths in hyperscale, edge, enterprise and colocation data center interconnect (DCI) applications where density and speed are both very important. This OM4 cable is an ideal choice for 400 Gb Ethernet applications. It is also backward compatible with 40 Gb and 100 Gb networks, so you can future-proof your current application for an eventual upgrade to 400 Gb.

#### Compact SN Connector Designed for the Latest OSFP/QSFP-DD Transceivers

One cable end features an SN connector, which is four times smaller than the standard duplex LC connector on the other end. The SN connector provides individual and independent duplex fiber support for an OSFP/QSFP-DD transceiver. The push/pull boot encourages dense vertical stacking within a crowded patch panel or switch and makes the cable easy to install or remove with just one hand. The switchable SN/PC duplex end lets you make quick polarity changes in the field without tools or the need to re-terminate the connectors.

#### Magenta-Colored Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The OM4-rated cable has a magenta jacket to identify it as multimode in a crowded patch panel or switch and prevent it from becoming accidentally disconnected. The round low-smoke zero-halogen (LSZH) jacket limits the amount of toxic smoke emitted in case of combustion, making it suitable for poorly ventilated areas.

### Highlights

- Duplex SN connector optimized for the latest 400 Gb OSFP/QSFP-DD transceivers
- Space-saving SN plug is 4x smaller than duplex LC for easier cable management
- Switchable SN connectors allow polarity conversion without tools or re-termination
- Backward compatible with 40/100 Gb networks to facilitate future-proofing
- Magenta LSZH jacket allows fast, easy identification in a crowded switch or patch panel

### Package Includes

N823L-02M-MG 40/100/400G Multimode 50/125 OM4 Fiber Cable, Magenta, 2 m (6.6 ft.)

## Specifications

OVERVIEW	
UPC Code	037332274632



Technology	Multimode
Optical Mode	OM4
Mode Type	Multimode
<b>PHYSICAL</b>	
Cable Jacket Color	Magenta
Connector Color	Aqua; White
Cable Jacket Material	LSZH
Cable Jacket Rating	OFNR
Cable Outer Diameter (OD)	1.60MM
Clad Diameter (microns)	125.0
Core Diameter (microns)	50.0
Primary Coating Diameter (microns)	245.0
Number of Fibers	2
Cable Length (ft.)	6.6
Cable Length (m)	2.01
Cable Length (in.)	78.7
Minimum Bend Radius	20MM (DYNAMIC); 10MM (STATIC)
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 TO 140 F (-10 TO 60 C)
Storage Temperature Range	14 TO 140 F (-10 TO 60 C)
Operating Humidity Range	5% TO 85% RH, NON-CONDENSING
Storage Humidity Range	5% TO 85% RH, NON-CONDENSING
<b>COMMUNICATIONS</b>	
Network Compatibility	1 Gbps (Gigabit); 10 Gbps; 25 Gbps; 40 Gbps; 100 Gbps; 400 Gbps
Wavelength	1300nm; 850nm
Attenuation @ 850NM	3.5dB
Attenuation @ 1300NM	1.5dB
Insertion Loss	<0.20dB
<b>CONNECTIONS</b>	
Side A - Connector 1	SN DUPLEX (MALE)
Side B - Connector 1	LC DUPLEX (MALE)
Endface Polish	PC
Switchable Polarity	Yes



<b>FEATURES &amp; SPECIFICATIONS</b>	
Push/Pull Tabs	No
Optical Port	LC; SN
Breakout	No
Trunk	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 1651
Product Compliance	RoHS; CE (Europe); REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>