

PERFORMANCE**Processor**

Intel® Core™ i5-10400T (6C / 12T, 2.0 / 3.6GHz, 12MB)

Graphics

Integrated Intel UHD Graphics 630

Chipset

Intel B560

Memory

2x 4GB SO-DIMM DDR4-2666

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Max Memory

Up to 16GB DDR4-3200

Storage

256GB SSD M.2 2242 PCIe® NVMe®

Optane™ Memory

None

Storage Support

Up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 2TB
- M.2 SSD up to 1TB

Card Reader

None

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC274-CG codec

Speakers

3Wx2 + 5W, JBL® Brand

Camera

5.0MP + IR

Microphone

2x, Array

Power Supply

120W 89% Adapter Black

DESIGN**Display**

23.8" FHD (1920x1080) IPS 250nits, Touch

Touchscreen

10-point Multi-touch

Keyboard

Calliope Wireless Keyboard, Black, English

Mouse

Calliope Wireless Mouse, Black

Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

Case Color

Graphite Grey

Stand

AIO Stand

Wireless Charger

Wireless Charger

Pen

No support

Form Factor

AIO (23.8 inches)

Dimensions (WxDxH)

541.2 x 185 x 437.79 mm (21.3 x 7.28 x 17.23 inches)

Weight

7.23 kg (15.93 lbs)

CONNECTIVITY**Ethernet**

Integrated 100/1000M

WLAN + Bluetooth®

11ac, 2x2 + BT5.0

Rear Ports

- 2x USB 2.0
- 3x USB 3.2 Gen 2
- 1x HDMI®-out 1.4
- 1x HDMI-in 1.4
- 1x Ethernet (RJ-45)
- 1x headphone / microphone combo jack (3.5mm)
- 1x power connector

SERVICE**Base Warranty**

1-year, Mail-in

Included Upgrade

None

CERTIFICATIONS**Green Certifications**

- ErP Lot 3 and Lot 7
- RoHS compliant

SOFTWARE**Operating System**

Windows® 11 Pro 64, English

Bundled Software

None

MODEL

TopSeller : No

EAN / UPC / JAN : 196118417042

Lenovo

PSREF

Product Specifications
Reference

intel

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.



Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference