



Rugged, flexible design and Chrome simplicity

The HP Fortis x360 Chromebook helps push possibilities with reliable performance in a ruggedized[1], flexible design. Essential features, a 360-degree hinge and the simple, secure Chrome OS enable productivity and interactivity for a more personalized, comfortable experience, while built-in features from HP provide durability for day-to-day peace of mind.



Four versatile use modes

Jump between tasks with ease and type, write, or draw comfortably in laptop, tablet, tent, or stand mode.

Engineered for durability

Rugged design undergoes MIL-STD 810[1], HP Total Test Process[3], drop testing[4], and resists spills and dust.

Easily meet online

Easily connect and collaborate with others in dense wireless networks using fast, reliable Wi-Fi 6[2] connectivity.

Featuring

Simplify deployments

Get a low-maintenance experience with the automatic software updates and virus protection of the Chrome OS. [5]

Universal connectivity and charging with USB-C™

Use the USB-C™ port to access and charge your USB-C™ accessories from your Chromebook™ or charge your Chromebook™ from any USB-C™ adapter.

Apps and content for expanded learning

Take learning in new directions with access to the Google Play™ Store and Android™ apps, which include thousands of instantly shareable and easily manageable innovative education apps. [5]

Specifications

Operating system	Chrome OS™
Processor family	Intel® Celeron® processor
Processor	Intel® Celeron® N4500 (up to 2.8 GHz burst frequency, 4 MB L3 cache, 2 cores, 2 threads) ^[6,7]
Memory	4 GB LPDDR4x-4266 MHz RAM (onboard)
Internal Storage	32 GB eMMC
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics
Display	29.5 cm (11.6") diagonal, HD (1366 x 768), touch, IPS, BrightView, 220 nits, 50% NTSC
Display	11.6" diagonal, HD (1366 x 768), touch, IPS, BrightView, 220 nits, 50% NTSC ^[7,8,9]
Display size (diagonal)	29.5 cm (11.6")
Display size (diagonal)	11.6"
Audio	HD audio, dual speakers, dual array microphones
Minimum dimensions (W x D x H)	29.5 x 20.53 x 2.09 cm
Minimum dimensions (W x D x H)	11.61 x 8.08 x 0.82 in
Weight	Starting at 1.47 kg (Weight will vary by configuration. Does not include power adapter.)
Weight	Starting at 3.24 lb (Weight will vary by configuration. Does not include power adapter.)
Keyboard	Spill resistant, full-size, Chrome keyboard with skirt anchored keycaps
Pointing device	Clickpad with multi-touch gesture support, taps enabled as default
Camera	720p HD camera; 5 MP camera
Ports	2 SuperSpeed USB Type-C® 5Gbps signaling rate (USB Power Delivery, video and data support); 2 SuperSpeed USB Type-A 5Gbps signaling rate; 1 Stereo headphone/microphone combo jack
Wireless	Intel® Wi-Fi 6 AX201 (2x2) and Bluetooth® 5.2 wireless card, non-vPro®
Power	45 W USB Type-C™ adapter
Battery type	HP Long Life 2-cell, 47 Wh Li-ion polymer
Battery weight	0.42 lb
Battery weight	190 g
Sustainable impact specifications	Low Halogen; Bulk packaging available; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; 2% post-consumer recycled plastic
Security management	Nano Security lock slot; Google Titan C; Zero Touch Enrollment (optional) ^[12,18]
Software included	Chrome Education Upgrade (Sold separately); HP Classroom Manager (Sold separately) ^[10,11]
UPC number	(ABA) 197192618110; (ABL) 197192618127
Manufacturer Warranty	HP Services offers 1-year limited warranties and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty except for Long Life batteries which will have same 1-year or 3-year limited warranty as the platform. Refer to http://www.hp.com/support/batterywarranty/ for additional battery information. Onsite service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: http://www.hp.com/go/cpc . ^[15]

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

- [1] MIL-STD testing is not intended to demonstrate fitness for U.S. Department of Defense contract requirements or for military use. Test results are not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.
- [2] Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 (802.11 ax) is backwards compatible with prior 802.11 specs.
- [3] HP Total Test Process testing is not a guarantee of future performance under these test conditions. Accidental damage requires an optional HP Accidental Damage Protection Care Pack.
- [4] 122 cm test on plywood and 76 cm test on concrete. Drop test is not a guarantee of future performance under these test conditions. Any accidental damage requires an optional HP Accidental Damage Protection Care Pack.
- [5] Internet access required and sold separately. Some apps may require purchase.

Technical Specifications Footnotes

- [6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.
- [7] Burst frequency performance varies depending on hardware, software and overall system configuration.
- [8] Actual brightness will be lower with touchscreen or Sure View.
- [9] Resolutions are dependent upon monitor capability, and resolution and color depth settings.
- [10] HP Classroom Manager is sold separately. Control and device locking from the teacher's desktop requires purchase of HP Classroom Manager.
- [11] Chrome Education Upgrade requires one-time setup, subscription, Google Admin Console, and your organization's domain. Please see <https://support.google.com/a/answer/60216>.
- [12] Lock is sold separately.
- [15] HP Care Packs are sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit <http://www.hp.com/go/kpc>. HP services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.
- [18] Zero Touch Enrollment is sold separately.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Celeron, Pentium and Intel vPro are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. © 2023 Google LLC All rights reserved. Google and the Google Logo are registered trademarks of Google LLC.

